
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	MIN	MAX.	in (mm)	B in (mm)	in (mm)	in (mm)	E in (mm)	F in (mm)	G in (mm)	H in (mm)	in (mm)	MAX. PANEL THICKNESS	MIN. LOOP TENSILE Ibs (n)	CROSS- SECTION	WEIGHT 100 pcs 1bs (g)
BP2S	.06 (1.5)	2.00 (51)	.052 (1.3)	.185 (4.7)	.300 (7.6)	.385 (9.8)	.320 (8.1)	8.5 (216)	.315 (8.0)	.255 (6.5)	.37 (9.4)	.125 (3.2)	50 (222)	STANDARD	.35 (160)

									DIMENSIC	NS IN PARENTHESIS ARE	E IN METRIC UN	IITS	
									PANDUIT CORP. TINLEY PARK, ILLINOIS				
									DOME-TOP Barb Ty LOCKING PUSH MOUNT TIE				
									DIMENSION	THERWISE SPECIFIED, NAL TOLERANCES ARE: 1(2.5)(.XXX) ± .020(.51) 02(.5)ANGLES ±	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJE		
									DRAWN BY SLB	MAT'L;	scale NONE		
4	9/12/05	JABO		CLEANED UP EXTRA LINES IN VIEW	BT-0286	4			DATE 5-13-04	NYLON 6.6	DRAWING NO.	DWG	
REV	DATE	ву	снк	DESCRIPTION	ECN -	R	CUST	SUP	SLB		BT-0286	SIZE	