

Safety Data Sheet

according to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012.
Issue date: 5/11/2017 Revision date: 8/26/2022 Version: 2.0

SECTION 1: Identification**1.1. Identification**

Product form : Mixture
Product name : X-1047

1.2. Recommended use and restrictions on use

Use of the substance/mixture : Corrosion inhibitor

1.3. Supplier**Supplier**

CONTINENTAL PRODUCTS, INC.
#6 Midwest Drive, P.O. Box 338
Pacific, MO 63069 - USA
T 636-257-4449
kdb@contprod.com

1.4. Emergency telephone number

Emergency number : CHEMTREC: 800-424-9300

SECTION 2: Hazard(s) identification**2.1. Classification of the substance or mixture****GHS US classification**

Not classified

2.2. GHS Label elements, including precautionary statements**GHS US labeling**

No labeling applicable

2.3. Other hazards which do not result in classification

No additional information available

2.4. Unknown acute toxicity (GHS US)

Not applicable

SECTION 3: Composition/Information on ingredients**3.1. Substances**

Not applicable

3.2. Mixtures

Name	Product identifier	%
Zinc oxide (ZnO)	CAS-No.: 1314-13-2	1 - 5

*Chemical name, CAS number and/or exact concentration have been withheld as a trade secret

Safety Data Sheet

according to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012.

SECTION 4: First-aid measures

4.1. Description of first aid measures

First-aid measures after inhalation	: Not a normal route of exposure. If symptoms develop, remove to fresh air. Get medical attention if condition worsens.
First-aid measures after skin contact	: If skin irritation occurs: Wash skin with plenty of water. Obtain medical attention if irritation persists.
First-aid measures after eye contact	: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. This compound contains abrasive particles. If eye irritation persists: Get medical advice/attention.
First-aid measures after ingestion	: Do not induce vomiting without medical advice. Never give anything by mouth to an unconscious person. Get medical advice/attention if you feel unwell.

4.2. Most important symptoms and effects (acute and delayed)

Symptoms/effects after inhalation	: Not a normal route of exposure.
Symptoms/effects after skin contact	: May cause skin irritation. Symptoms may include redness, drying, and cracking of the skin.
Symptoms/effects after eye contact	: May cause eye irritation. Symptoms may include discomfort or pain, excess blinking and tear production, with possible redness and swelling.
Symptoms/effects after ingestion	: May be harmful if swallowed. May cause gastrointestinal irritation, nausea, vomiting and diarrhea.

4.3. Immediate medical attention and special treatment, if necessary

Symptoms may be delayed. In case of accident or if you feel unwell, seek medical advice immediately (show the label where possible).

SECTION 5: Fire-fighting measures

5.1. Suitable (and unsuitable) extinguishing media

Suitable extinguishing media	: Dry chemical. Foam. Carbon dioxide.
Unsuitable extinguishing media	: Do not use water jet.

5.2. Specific hazards arising from the chemical

Fire hazard	: Products of combustion may include, and are not limited to: oxides of carbon.
-------------	---

5.3. Special protective equipment and precautions for fire-fighters

Protection during firefighting	: Keep upwind of fire. Wear full fire fighting turn-out gear (full Bunker gear) and respiratory protection (SCBA).
--------------------------------	--

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

General measures	: Use personal protection recommended in Section 8. Isolate the hazard area and deny entry to unnecessary and unprotected personnel.
------------------	--

6.1.1. For non-emergency personnel

No additional information available

6.1.2. For emergency responders

No additional information available

6.2. Environmental precautions

Prevent entry to sewers and public waters.

Safety Data Sheet

according to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012.

6.3. Methods and material for containment and cleaning up

- For containment : Absorb and/or contain spill with inert material (sand, vermiculite or other appropriate material), then place in suitable container. Do not flush into surface water or sewer system. Wear recommended personal protective equipment.
- Methods for cleaning up : Sweep or shovel spills into appropriate container for disposal.

6.4. Reference to other sections

For further information refer to section 8: "Exposure controls/personal protection".

SECTION 7: Handling and storage

7.1. Precautions for safe handling

- Precautions for safe handling : Avoid contact with skin and eyes. Avoid breathing dust/fume/gas/mist/vapors/spray. Do not swallow. Handle and open container with care. When using do not eat, drink or smoke.
- Hygiene measures : Wash contaminated clothing before reuse. Always wash hands after handling the product.

7.2. Conditions for safe storage, including any incompatibilities

- Storage conditions : Keep out of the reach of children. Keep container tightly closed.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

X-1047	
No additional information available	
Zinc oxide (ZnO) (1314-13-2)	
USA - ACGIH - Occupational Exposure Limits	
Local name	Zinc oxide
ACGIH OEL TWA	2 mg/m ³ (respirable particulate matter)
ACGIH OEL STEL	10 mg/m ³ (respirable particulate matter)
Remark (ACGIH)	TLV® Basis: Metal fume fever
Regulatory reference	ACGIH 2021
USA - OSHA - Occupational Exposure Limits	
Local name	Zinc oxide
OSHA PEL (TWA) [1]	5 mg/m ³ (fume) 15 mg/m ³ (total dust) 5 mg/m ³ (respirable fraction)
Regulatory reference (US-OSHA)	OSHA Annotated Table Z-1
USA - IDLH - Occupational Exposure Limits	
IDLH	500 mg/m ³
USA - NIOSH - Occupational Exposure Limits	
NIOSH REL (TWA)	5 mg/m ³ (dust and fume)
NIOSH REL (STEL)	10 mg/m ³ (fume)
NIOSH REL (Ceiling)	15 mg/m ³ (dust)

Safety Data Sheet

according to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012.

8.2. Appropriate engineering controls

Appropriate engineering controls : Ensure good ventilation of the work station.
Environmental exposure controls : Avoid release to the environment.

8.3. Individual protection measures/Personal protective equipment

Hand protection:

None required.

Eye protection:

Safety glasses or goggles are recommended when using product.

Skin and body protection:

Wear suitable protective clothing

Respiratory protection:

None required.

Other information:

Handle in accordance with good industrial hygiene and safety procedures. Do not eat, drink or smoke when using this product.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Solid
Appearance	: Paste. Thick grease.
Color	: Gray
Odor	: No data available
Odor threshold	: No data available
pH	: No data available
Melting point	: No data available
Freezing point	: No data available
Boiling point	: No data available
Flash point	: > 260 °C (> 500 °F)
Relative evaporation rate (butyl acetate=1)	: No data available
Flammability	: Not flammable.
Vapor pressure	: No data available
Relative vapor density at 20 °C	: No data available
Relative density	: No data available
Solubility	: No data available
Partition coefficient n-octanol/water	: No data available
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosion limits	: No data available
Explosive properties	: No data available
Oxidizing properties	: No data available

9.2. Other information

No additional information available

Safety Data Sheet

according to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012.

SECTION 10: Stability and reactivity**10.1. Reactivity**

No dangerous reactions known under normal conditions of use.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

10.4. Conditions to avoid

Heat.

10.5. Incompatible materials

None known.

10.6. Hazardous decomposition products

May include, and are not limited to: oxides of carbon.

SECTION 11: Toxicological information**11.1. Information on toxicological effects**

Acute toxicity (oral) : Not classified
 Acute toxicity (dermal) : Not classified
 Acute toxicity (inhalation) : Not classified

Zinc oxide (ZnO) (1314-13-2)

LD50 oral rat	> 5000 mg/kg
LD50 dermal rat	> 2000 mg/kg body weight Animal: rat, Guideline: OECD Guideline 402 (Acute Dermal Toxicity)
LC50 inhalation rat	> 5700 mg/m ³ (Exposure time: 4 h)

Skin corrosion/irritation : Not classified
 Serious eye damage/irritation : Not classified
 Respiratory or skin sensitization : Not classified
 Germ cell mutagenicity : Not classified
 Carcinogenicity : Not classified
 Reproductive toxicity : Not classified
 STOT-single exposure : Not classified
 STOT-repeated exposure : Not classified
 Aspiration hazard : Not classified
 Viscosity, kinematic : No data available
 Symptoms/effects after inhalation : Not a normal route of exposure.
 Symptoms/effects after skin contact : May cause skin irritation. Symptoms may include redness, drying, and cracking of the skin.
 Symptoms/effects after eye contact : May cause eye irritation. Symptoms may include discomfort or pain, excess blinking and tear production, with possible redness and swelling.
 Symptoms/effects after ingestion : May be harmful if swallowed. May cause gastrointestinal irritation, nausea, vomiting and diarrhea.

Safety Data Sheet

according to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012.

SECTION 12: Ecological information**12.1. Toxicity**

Ecology - general : Very toxic to aquatic life with long lasting effects.

Zinc oxide (ZnO) (1314-13-2)

LC50 - Fish [1]	1.55 mg/l (Exposure time: 96 h - Species: Danio rerio [static])
-----------------	---

12.2. Persistence and degradability**X-1047**

Persistence and degradability	Not established.
-------------------------------	------------------

12.3. Bioaccumulative potential**X-1047**

Bioaccumulative potential	Not established.
---------------------------	------------------

12.4. Mobility in soil

No additional information available

12.5. Other adverse effects

Other information : No other effects known.

SECTION 13: Disposal considerations**13.1. Disposal methods**

Product/Packaging disposal recommendations : Dispose in a safe manner in accordance with local/national regulations.

SECTION 14: Transport information

Not regulated for transport

14.2. UN proper shipping name

Proper Shipping Name (DOT) : Not applicable

14.3. Transport hazard class(es)**DOT**

Transport hazard class(es) (DOT) : Not applicable

14.4. Packing group

Packing group (DOT) : Not applicable

14.5. Environmental hazards

Other information : No supplementary information available.

14.6. Special precautions for user

Special transport precautions : Do not handle until all safety precautions have been read and understood.

Safety Data Sheet

according to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012.

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. US Federal regulations

All components of this product are listed, or excluded from listing, on the United States Environmental Protection Agency Toxic Substances Control Act (TSCA) inventory.

15.2. International regulations

No additional information available

15.3. US State regulations

California Proposition 65 - This product does not contain any substances known to the state of California to cause cancer, developmental and/or reproductive harm

SECTION 16: Other information

According to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012.

Issue date : 05/11/2017
Revision date : 08/26/2022
Other information : None.
Prepared by : Nexreg Compliance Inc.
www.Nexreg.com



Indication of changes:

SDS update.

Safety Data Sheet (SDS), USA

Disclaimer: We believe the statements, technical information and recommendations contained herein are reliable, but they are given without warranty or guarantee of any kind. The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. It is the user's responsibility to satisfy oneself as to the suitability and completeness of this information for the user's own particular use.