TX6[™] Category 6 U/UTP Copper Cable



specifications

Category 6 cable shall exceed ANSI/TIA-568.2-D Category 6 component Standard. The conductors shall be 24 AWG construction with FEP/ polyolefin insulation. The copper conductors shall be twisted in pairs and covered by a low smoke, flame-retardant (CMP) PVC jacket.



| TX6 Category 6 U/UTP Copper Cable | | |
|-----------------------------------|--------------|--|
| Plenum: | PUP6C04**-WZ | |
| Cable Prep Tools | | |
| Wire snipping tool: | CWST | |
| Wire stripping tool: | CJAST | |

*For standard cable colors, add suffix BU (Blue), WH (White), RD (Red), OR (Orange), YL (Yellow), GR (Green), VL (Violet), IG (International Gray), or BL (Black). Visit www.panduit.com for connectivity components.

technical information

| Electrical performance: | Certified channel performance in a 4-connector configuration up to 100m and meets ANSI/TIA-568.2-D Category 6 Standard at swept frequencies up to 250 MHz |
|-------------------------|--|
| | Certified component performance up to 100m and meets the component requirements of ANSI/TIA-568.2-D Category 6 component standard at swept frequencies up to 250 MHz |
| Conductors/insulators: | 24 AWG solid copper covered by FEP/polyolefin insulation |
| Insulation diameter: | 0.034"–0.046" (0.86mm–1.16mm) |
| Flame rating: | NFPA 262 and CSA FT-6 |
| PoE compliance: | Meets IEEE 802.3af, IEEE 802.3at, and IEEE 802.3bt for PoE applications |
| Installation tension: | 25 lbf (110 N) maximum |
| Temperature rating: | 32°F to 122°F (0°C to 50°C) during installation -4°F to 167°F (-20°C to 75°C) during operation |
| Cable jacket: | Low smoke, flame-retardant PVC |
| Cable diameter: | 0.230" (5.8mm) nominal |
| Cable weight: | Plenum - 27 lbs./1000' (12.2kg/305m) |
| Packaging: | 1000' (305m) in an easy payout carton |
| | Package tested to ISTA Procedure 1A |

key features and benefits

| Third party tested: | Cable has been tested as part of the Category 6 U/UTP Copper Cabling System by an independent laboratory and complies with the electrical channel requirements of the following Standard: ANSI/TIA-568.2-D Category 6 |
|---|--|
| Guaranteed channel performance above the Standards: | Industry leading guaranteed channel performance exceeding the TIA/ISO Standards with headroom guaranteed |
| Descending length cable markings: | Easy identification of remaining cable reduces installation time and cable scrap |
| Tested beyond the Standards: | Cable has been characterized to 550 MHz, 300 MHz above the Standard |
| Reelex [™] packaging: | Compact carton ensures proper performance and provides quick installation |

applications

Interoperable and backward compatible, the TX6 Cabling System provides design flexibility to protect network investments well into the future. With certified performance to the ANSI/TIA-568.2-D Category 6 and ISO 11801 Class E Standards, this system will support the following applications:


- Ethernet 10BASE-T, 100BASE-T (Fast Ethernet), 1000BASE-T (Gigabit Ethernet), 10GBASE-T (10 Gigabit Ethernet over limited distances as specified in the industry 10GBASE-T standards)
- 155 Mb/s ATM, 622 Mb/s ATM, 1.2 Gb/s ATM
- Token Ring 4/16

TX6[™] Category 6 U/UTP Copper Cable

additional specifications

| Mechanical Test | | |
|---------------------------------------|-------------------|--|
| Ultimate Breaking Strength | >90 lbf (400 N) | |
| Minimum Bend Radius | 4x cable diameter | |
| Electrical Test | | |
| Nominal Velocity of Propagation (NVP) | 67% | |
| Operating Voltage, Maximum | 80 V | |

cable construction



WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty



For more information Visit us at www.panduit.com Contact Customer Service by email: cs@panduit.com or by phone: 800.777.3300

© 2023 Panduit Corp. ALL RIGHTS RESERVED. COSP541-WW-ENG 6/2023