# QuickNet<sup>™</sup> Copper Cabling Systems

Quick Deployment for High-Density Data Center Applications



building a smarter, unified business foundation Connect. Manage. Automate.

### Panduit's Unified Physical Infrastructure (UPI)

A unified approach to physical and logical systems architecture is imperative for solutions to fully address the need for availability, agility, integration, and security.

Panduit has developed the industry's most comprehensive and holistic approach to a Unified Physical Infrastructure and can help enterprises align, converge, and optimize critical systems – communication, computing, control, power, and security – to build a smarter, unified business foundation.

### **Unified Physical Infrastructure**



## Benefits of a Pre-Terminated Cabling System

Your network drives the critical data, voice, video, and security applications required to support your business. A pre-terminated cabling system simplifies the delivery of those network services by providing reliable infrastructure components assembled and tested in a factory-controlled environment.

An end-to-end pre-terminated cabling system is an ideal solution for data centers especially when time for traditional cable installation, termination, and testing is limited. Pre-terminated cable assemblies offer a simple plug-n-go solution for links between LAN switches, servers, patch panels, and zone distribution areas, for new installations or to enable easy additions to current infrastructure.



## Advantages of the Panduit<sup>®</sup> QuickNet<sup>™</sup> Copper Cabling System

As part of the complete QuickNet<sup>™</sup> Solution, the Panduit<sup>®</sup> QuickNet<sup>™</sup> Copper Cabling System is a custom pre-terminated cabling solution, designed to meet unique structured cabling requirements. Fast and simple to install, this high-density solution provides consistent network reliability and reduces initial on-site rework. This leading-edge system delivers ensured performance for the lowest total cost of ownership.

## **Quick Network Deployment**

Pre-terminated cabling systems can be installed in 75% less time than field-termination methods, eliminating the need for on-site bundling, terminating, and testing. Moves, adds, and changes can be made immediately by existing on-site network professionals, increasing productivity relative to traditional field installations. This is critical for areas that require high security and limited access, as changes to the network can be made without scheduling outside personnel.

### Mitigates Risks – Quality, Reliability, Performance and Security

The QuickNet<sup>™</sup> Cabling System mitigates risk in the areas of the quality, reliability, and performance of the installed system, as well as site security during installation. Quality and reliability of the installed system are ensured through the use of authentic Panduit components that are assembled and tested in Panduit's factory-controlled environment, and performance is ensured by the 100% testing of each finished assembly. Site security risks are minimized due to the significantly reduced installation time, which means fewer installers and less time spent by them on-site.

## **Provides a Re-Deployable Asset**

Each QuickNet<sup>™</sup> assembly is labeled with length and unique serial number information so it can be easily catalogued and tracked as a network asset, and as such, can quickly and easily be redeployed to address changing network needs.

### Why Specify Panduit® QuickNet<sup>™</sup> Copper Cabling System?

- Quick Deployment
  75% Faster
- Ease of Installation Plug-n-Go Solution
- Improved Reliability
  100% Factory Performance Tested
- Unified Copper and Fiber Solution
  Copper and Fiber in the
  Same Patch Panels
- High Performing Cabling System Category 6A and Category 6, UTP and Shielded
- Standard Lengths Stocked Immediate Availability
- Custom Assemblies Available For Unique Requirements
- "Green" Solution 80% Less Packaging Waste

## **A Foundation of Excellence**

### **Innovative Design**

The Panduit<sup>®</sup> QuickNet<sup>™</sup> Copper Cabling System incorporates innovative design features.

- Built-in release mechanism on QuickNet<sup>™</sup> Pre-Terminated Cassettes enables simple installation and removal with one hand
- 48-port (1 RU) high-density angled patch panels and PatchRunner<sup>™</sup>
- Vertical Cable Managers quadruple rack density for reduced real estate costs
- QuickNet<sup>™</sup> Adapter snaps in and out of QuickNet<sup>™</sup> Patch Panels and accepts all Mini-Com<sup>®</sup> Modules to provide flexibility and scalability for changing network requirements
- QuickNet<sup>™</sup> Plug Pack Assemblies facilitate quick and easy connection and disconnection of cables to a variety of switches, reducing time and cost associated when installing and maintaining structured cabling links
- Staggered cable lengths ensure proper bend radius control and an aesthetic solution
- Jack modules, cable, and patch cords are tuned to each other to deliver maximum channel performance and network reliability

### **World-Class Quality**

QuickNet<sup>™</sup> Copper Cabling System components are manufactured to strict ISO quality procedures.

- QuickNet<sup>™</sup> Cable Assemblies are 100% performance tested to TIA or ISO electrical permanent link specifications (test report shipped with each assembly)
- Each assembly has a unique serial number for future traceability
- Giga-TX<sup>™</sup> Jack Modules undergo more than 90 additional quality checks for assured performance

## World-Class Service and Support

At Panduit, we respond quickly to customer needs and deliver exceptional service levels globally.

- Global sales and technical support teams work together to ensure the optimum solution is provided to meet your requirements
- Short lead times and custom configurations keep your project on schedule
- Design tools facilitate customization and allow flexibility when designing the structured cabling infrastructure



Integrated release tab enables easy installation and removal of 6-port pre-terminated cassette.

Shielded cassettes provide seamless self bonding for shielded cable assemblies.

4

## **Elements of the System**

### **QuickNet<sup>™</sup> Cable Assemblies**


- Offer UTP Category 6 Cabling and UTP/STP Category 6A Cabling (plenum, riser, LSZH, and CM fire ratings)
- Pre-bundled with six cables for easy installation
- Available in lengths from 10 to 295 feet (one foot increments) or 3 meter to 90 meters (half meter increments) and different cable colors for redundant path applications
- Multiple termination types including pre-terminated cassettes, jack modules, modular plugs, plug packs, and/or unterminated options
- Shielded die cast cassette utilizes direct bonding, eliminating external bonding requirement

## **QuickNet<sup>™</sup> Angled and Flat Patch Panels**

- Accept Quicknet<sup>™</sup> Pre-Terminated Cassettes, which snap in and out with one hand for quick installation
- Available in 24-port (1 RU) standard density and 48-port (1 RU) high-density configurations
- Angled design allows cable to flow to each side of the rack and eliminates the need for horizontal cable managers by enabling patch cords to be routed directly into vertical cable managers
- Proper identification of each port with pre-printed numbers above each port; vertical numbering from top to bottom of panel is also available for high density switch applications

## **QuickNet<sup>™</sup> Patch Panel Accessories**

- Patch panel adapter accepts Mini-Com<sup>®</sup> Modules for UTP, fiber optic, and audio/video applications
- Blank patch panel adapter reserves space for future use while promoting proper airflow and cooling
- Adapters and blanks easily snap in and out of QuickNet<sup>™</sup> Patch Panels



QuickNet<sup>™</sup> Plug Packs allow multiple cables to be installed simultaneously with one hand for speed of deployment in switch applications.



**24-port, flat modular patch panel,** populated with pre-terminated shielded cassettes with shielded jack modules.



**48-port, angled modular patch panel,** populated with pre-terminated cassettes with UTP jack modules.



Patch panel blank



Patch panel adapter, populated with copper, fiber, and audio video modules

5

## **Data Center Applications**



QuickNet<sup>™</sup> Jack-to-Plug Cable Assemblies are ideal for cross-connect applications

The QuickNet<sup>™</sup> Copper Cabling System is integrated with the Panduit<sup>®</sup> StructuredGround<sup>™</sup> System to optimize network performance

For the full Panduit product offering, request Panduit  $^{\circ}$  Pan-Net  $^{\circ}$  Network Solutions Catalog: SA-NCCB51.

QuickNet<sup>™</sup> Copper and Fiber Cabling Systems are compatible with PanZone<sup>®</sup> Enclosures and Boxes for zone cabling applications



QuickNet<sup>™</sup> Cassettes snap in and out of QuickNet<sup>™</sup> Patch Panels allowing quick and reliable installation in server applications

> Bundled QuickNet<sup>™</sup> Cable Assemblies are easily routed in Wyr-Grid<sup>®</sup> Overhead Cable Tray Routing System, FiberRunner<sup>®</sup> Cable Routing System, or GridRunner<sup>™</sup> Underfloor Cabling Routing System

QuickNet<sup>™</sup> Cassettes snap in and out of QuickNet<sup>™</sup> Patch Panels allowing easy access for moves, adds, and changes in switch or server applications

QuickNet<sup>™</sup> Plug Pack termination option minimizes network downtime during switch installation and maintenance

### Environmental Benefits of the QuickNet<sup>™</sup> Copper Cabling System

#### QuickNet<sup>™</sup> installations are more "Green" than traditional installations:

- 80% Less Packaging Waste
- No Termination Scrap Material or Debris to Clean Up
- QuickNet<sup>™</sup> Assemblies are Reusable

## **A Commitment to Green**

As a global manufacturer, Panduit has embraced lean and sustainable thinking as a core value by designing solutions and facilities that are good for the environment and for business. The QuickNet<sup>™</sup> Copper Cabling System supports this commitment by significantly reducing the amount of product packaging waste as compared to traditional field-termination installations, and by providing cabling assemblies which are inherently redeployable and reusable.

**Typical Waste from** 



**Traditional Installation** 




QuickNet<sup>™</sup> Installation

## **Permanent Link Performance**


The Panduit<sup>®</sup> QuickNet<sup>™</sup> Copper Cabling System exceeds the applicable permanent link requirements for Category 6A and Category 6 transmission over twisted-pair cabling. Each assembly is 100% performance tested at the factory. A Fluke\* Linkware test report accompanies each cable assembly and will also be archived by Panduit. Because the cable assemblies are 100% factory tested, the time and cost associated with on-site field testing are eliminated. The QuickNet<sup>™</sup> Copper Cabling System provides risk mitigation and guaranteed performance by providing cable assemblies with a factory product warranty.

Permanent Link Compliance is tested for the following parameters:

- Insertion Loss (IL)
- Return Loss (RL)
- Near-End Crosstalk (NEXT)
- Power Sum Near-End Crosstalk (PSNEXT)
- Equal Level Far-End Crosstalk (ELFEXT)
- Power Sum Equal Level Far-End Crosstalk (PSELFEXT)



## QuickNet<sup>™</sup> Cable Assembly Ordering Information for North America



Example – The above part number is a 10 foot QuickNet<sup>™</sup> Cable Assembly constructed of Category 6A, UTP, plenum cable (blue) with a pre-terminated cassette (blue jacks installed) on each end.

#### 1 – Q = QuickNet<sup>™</sup>

#### 2 - Performance Level

- B = Category 6 Enhanced UTP
- C = Category 6 UTP
- E = Category 6A (TX6A<sup>™</sup> 10Gig<sup>™</sup>) Shielded
- X = Category 6A (TX6A-SD<sup>™</sup> 10Gig<sup>™</sup>) UTP MaTriX
- Z = Category 6A (TX6A<sup>™</sup> 10Gig<sup>™</sup>) UTP MaTriX

#### 3 - Flame/Smoke Rating

- R = Riser or P = Plenum
- 4 Cable Color
- B = Blue or W = White

#### 5 – Termination End 1

- C = Cassette
- J = Jack modules
- P = Modular plugs
- K = Jack modules staggered right
- L = Jack modules staggered left
- Q = Modular plugs staggered right
- S = Modular plugs staggered left

#### 6 - Termination End 1 Color Options **Jack Module Color Options**

- B = Blue, E = Electric Ivory, G = Green,
- H = Off White, I = International Gray,
- L = Black, O = Orange, R = Red, V = Violet,
- W = White, Y = Yellow
- Shielded Jack Modules, chose option
- L (all Shielded Jack Modules are Black)

#### Modular Plug and Unterminated Color Options

X = No color option available, all modular plugs are clear

#### 7 – Termination End 2

- A = Plug pack (6-pack)
- R = Recessed plug pack (6-pack)
- C = Cassette
- J = Jack modules
- P = Modular plugs
- K = Jack modules staggered right
- L = Jack modules staggered left
- Q = Modular plugs staggered right
- S = Modular plugs staggered left
- U = Unterminated
- O = Unterminated with cassette and jack modules
- for on-site termination
- 8 Termination End 2 Color Options

#### **Jack Module Color Options**

- B = Blue, E = Electric Ivory, G = Green,
- H = Off White, I = International Gray,
- L = Black, O = Orange, R = Red, V = Violet,
- W = White, Y = Yellow
- Shielded Jack Modules, chose option
- L (all Shielded Jack Modules are Black)

#### **Plug Pack Color Options**

- B = Blue, W = White, R = Red, L = Black
- **Recessed Plug Pack Color Options**
- S = Silver

#### Modular Plug and Unterminated Color Options

X = No color option available, all modular plugs are clear

#### 9 - Assembly Options

- P = Pulling eye
  - X = No assembly options requested

#### 10 - Custom Labeling\*

- L = Custom assembly label
- C = Custom cable labels
- B = Custom assembly and cable labels
- X = No custom labels requested

#### 11 - Assembly Length\*\*

10' to 295' (one foot increments)

\*Custom cable assembly labels are available up to eighteen characters; individual cable labels are available up to fifteen characters. \*\*For cable assemblies constructed of Category 6A (TX6A-SD<sup>™</sup> 10Gig<sup>™</sup>) UTP MaTriX Copper Cable, the maximum length is 196 ft. (60m). All connectivity is wired T568B. Category 6 Enhanced Performance level utilizes Panduit® TX6500<sup>™</sup> Category 6 UTP Cable. Permanent link test results shipped with each cable assembly.

## **Termination Options**



**UTP Cassette** 









**UTP Modular Plugs** 

Shielded Cassette



## $\textbf{QuickNet}^{\scriptscriptstyle{\text{TM}}}$ Patch Panels, Accessories, and Patch Cords

Std.

Pkg.

No. of

Rack

Std.

Ctn. Qty.

10

10

10 10

10

10

10

10

10

10

10 10 10

10

100

	Part Number	Description	Spaces^	Qty.	
	QuickNet <sup>™</sup> Angle	d Patch Panels		-	
	QAPP24BL	24-port, angled patch panel.	1	1	
	QASP24BL	24-port, all metal angled patch panel which accepts QuickNet <sup>™</sup> Pre-Terminated Shielded Cassettes and Patch Panel Adapters.	1	1	
QAPP48HDBL	QAPP48HDBL	48-port, high-density angled patch panel.	1	1	
	QAPP48HDVNSBL	48-port, high-density angled patch panel with pre-printed vertical numbering on each port for switch applications.	1	1	
	QASP48HDBL	48-port, all metal angled patch panel which accepts QuickNet <sup>™</sup> Pre-Terminated Shielded Cassettes and Patch Panel Adapters.	1	1	
QPP48HDBL	QuickNet <sup>™</sup> Flat Patch Panels				
	QPP24BL	24-port, flat patch panel.	1	1	
	QSP24BL	24-port, all metal patch panel which accepts QuickNet <sup>™</sup> Pre-Terminated Shielded Cassettes and Patch Panel Adapters.	1	1	
	QPP48HDBL	48-port, high-density flat patch panel.	1	1	
QPPABL	QPP48HDVNSBL	48-port, high density flat patch panel with pre-printed vertical numbering on each port for switch applications.	1	1	
	QSP48HDBL	48-port, all metal patch panel which accepts QuickNet <sup>™</sup> Pre-Terminated Shielded Cassettes and Patch Panel Adapters.	1	1	
	Patch Panel Adap	oter			
QPPBBL	QPPABL	6-port, patch panel adapter accepts Mini-Com <sup>®</sup> UTP, fiber optic, and audio/video modules.	_	1	
	Patch Panel Blan	k			
ے۔۔۔۔ SRB19BLY	QPPBBL	Reserves space for future use and promotes proper airflow and cooling.	_	1	
SHDIBDLI	Strain Relief Bar				
	SRB19BLY	Cable strain relief bar extends 2" off of the rack to support cables in patch panels.	_	1	
ALE CONTRACTOR	Label Kit				
	QPPLC24	Label/label cover kit for 24-port QuickNet <sup>™</sup> Patch Panels. Each kit contains four labels and four clear label covers per bag.	_	1	
QPPN6BU	Plug Packs				
	QPPN6++	QuickNet <sup>™</sup> Plug Pack accepts six RJ45 modular plugs.	_	1	
and the second se	QPPN8++	QuickNet <sup>™</sup> Plug Pack accepts eight RJ45 modular plugs.	_	1	
	QPPNR6S	QuickNet <sup>™</sup> Recessed Plug Pack accepts six RJ45 modular plugs.	-	1	
and the second s	Plug Pack Acces				
	QPPRT	Removal tool allows individual cables to be removed from plug pack without disruption of other network connections.	_	1	
QPPLD6-X	QPPLD6-X	Lock-in device prevents unauthorized removal of cables from the plug pack.		10	
	^One rack space = 1.75	i" (44.45mm).			

^One rack space = 1.75" (44.45mm). ++Available in BU (Blue), BL (Black), RD (Red), or WH (White). Recessed version, part number QPPR6S, is silver.



Part Number	Part Description
Patch Cords	
UTP6A*	Category 6A UTP CM patch cord with TX6 <sup>™</sup> PLUS Modular Plugs on each end.
UTP6ASD*	Category 6A-SD UTP CM patch cord with TX6 <sup>™</sup> PLUS Modular Plugs on each end.
STP6X*	Category 6A shielded LSZH/CM patch cord with TX6 <sup>™</sup> PLUS Shielded Modular Plugs on each end.
UTPSP*Y	Category 6 UTP CM patch cord with TX6 <sup>™</sup> PLUS Modular Plugs on each end.

\*Represents multiple foot lengths and multiple colors. Contact customer service for additional information.

> visit www.panduit.com/quicknet 11

## **Real-World Solutions**

With a proven reputation for excellence and innovation, Panduit and our partners work with you to overcome challenges and implement real-world solutions that create a competitive business advantage. Panduit offers the broadest range of solutions, from data centers and intelligent buildings to manufacturing operations, to help you build a **smarter, unified business foundation.** 

### **Technology Leadership**

Panduit develops innovative physical infrastructure solutions that meet the rapidly changing needs of our clients, from hardware and software to advisory services. This commitment is supported by investment in advanced research, solutions-focused product development, world-class manufacturing, and collaboration with customers at the forefront of technology.

#### **Partner Ecosystem**

Our best-in-class partner ecosystem offers a comprehensive portfolio of services that span the project lifecycle, from planning and design to delivery, deployment, maintenance, and operation. Panduit business partners – distributors, and certified architects, consultants, engineers, designers, system integrators, and contractors – are qualified to help you achieve your objectives and realize predictable and measurable results.

#### **Strategic Alliances**

Panduit cultivates long-term strategic alliances with industry leaders, including Cisco Systems, EMC, IBM, and Rockwell Automation, to develop, optimize, and validate solutions for our customers. This investment in people and resources helps solve our customers' greatest business challenges.

#### **Global Business Commitment**

Panduit is committed to delivering a consistently high level of quality and service the world over. With a presence in more than 100 countries, local Panduit sales representatives and technical specialists offer guidance and support that bring value to your business. Our global supply chain, which includes manufacturing, customer service, logistics, and distribution partners, provides prompt response to your inquiries and streamlines delivery to any worldwide destination.

#### **Sustainability**

With a commitment to environmental sustainability, Panduit develops and implements solutions that protect, replenish, and restore the world in which we live. This commitment is demonstrated by Panduit's LEED Gold certified World Headquarters, leveraging the Unified Physical Infrastructure<sup>SM</sup> approach to enable convergence of critical building systems to drive energy efficiency and ongoing operational improvement.

### Harness the power of your Enterprise Network

Call or visit us online, we can show you how.

> Panduit Corp. World Headquarters Tinley Park, IL 60487

cs@panduit.com US and Canada: 800.777.3300 Europe, Middle East, and Africa: 44.208.601.7200 Latin America: 52.33.3777.6000 Asia Pacific: 65.6305.7575

#### www.panduit.com

