

APPLICATION FOR OSHPD PREAPPROVAL

OF MANUFACTURER'S CERTIFICATION (OPM) APPLICATION #: OPM-0116-13								
OSHPD Preapproval of Manufacturer's Certification (OPM)								
ype: ⊠ New □ Renewal □ Update to Pre-CBC 2013 OPA Number:								
Manufacturer Information								
Manufacturer: Panduit Corporation								
Manufacturer's Technical Representative: Nathan Gleghorn								
Mailing Address: _412 Rockwell Court, Burr Ridge, Illinois 60527								
Telephone: 708-532-1800 x84249 Email: NAGL@panduit.com								
Product Information								
Product Name: 2 Post Cable Management Rack OS DO								
Product Type: 2 post rack OPM-0116-13								
Product Model Number: R2P, R2PS, R2P6S								
General Description: 2 post rack with 45 rack spaces for support of standard 19-inch components.								
DATE: 04/07/2015								
Applicant Information								
Applicant Company Name: Panduit Corporation								
Contact Person: Robert Fritz								
Mailing Address: 412 Rockwell Court, Burr Ridge, Illinois 60527								
Telephone: 708-532-1800 x84346 Email: RLFR@panduit.com								
I hereby agree to reimburse the Office of Statewide Health Planning and Development review fees in accordance with the California Administrative Code, 2013.								
Signature of Applicant: Robert 2 3 refg Date: 06/04/2014								
Title: Senior Manager Engineering Company Name: Panduit Corporation								

"Access to Safe, Quality Healthcare Environments that Meet California's Diverse and Dynamic Needs"





OFFICE USE ONLY



OFFICE OF STATEWIDE HEALTH PLANNING AND DEVELOPMENT FACILITIES DEVELOPMENT DIVISION

Registered Design Professional Preparing Engineering Recommendations						
Company Degenkolb Engineers Name:						
Name: Adrian M. Nacamuli California License Number: S 4857						
Mailing Address: 1300 Clay Street, 9 th Floor, Oakland, California 94612						
Telephone: 510-250-1216 Email: nacamuli@degenkolb.com						
OSHPD Special Seismic Certification Preapproval (OSP)						
 □ Special Seismic Certification is preapproved under OSP-(Separate application for OSP is required) □ Special Seismic Certification is not preapproved 						
Certification Method(s)						
☐ Testing in accordance with: ☐ ICC-ES AC156 ☐ FM 1950-10 ☐ Other* (Please Specify):						
*Use of criteria other than those adopted by the California Building Standards Code, 2013 (CBSC 2013) for component supports and attachments are not permitted. For distribution system, interior partition wall, and suspended ceiling seismic bracings, test criteria other than those adopted in the CBSC 2013 may be used when approved by OSHPD prior to testing. BY: Jeffrey Y. Kikumoto Analysis						
Experience Data DATE: 04/07/2015						
Combination of Testing, Analysis, and/or Experience Data (Please Specify):						
List of Attachments Supporting the Manufacturer's Certification						
 ☐ Test Report ☐ Other(s) (Please Specify): 						
OFFICE USE ONLY – OSHPD APPROVAL VALID FOR CBC 2013 ONLY						
Signature:						
Print Name: Jeffrey Kikumoto						
Title: SSE						
Condition of Approval (if applicable):						

"Access to Safe, Quality Healthcare Environments that Meet California's Diverse and Dynamic Needs"

Page 2 of 2



OPM 0116 - 13

DEGENKOLB ENGINEERS

235 Montgomery Street, Suite 500 San Francisco, CA 94104 415.392.6952 *Phone* 415.981.3157 *Fax* www.degenkolb.com

PANDUIT 2 POST CABLE MANAGEMENT RACK

MODELS R2P, R2PS, R2P6S

GENERAL NOTES

- 1. THIS OSHPD PREAPPROVAL OF MANUFACTURER'S CERTIFICATION (OPM) IS BASED ON THE CBC 2013. THE DEMAND (DESIGN FORCES) FOR USE WITH THIS OPM SHALL BE BASED ON THE CBC 2013.
- 2. PRE-APPROVED DESIGN AND MATERIALS CONFORM WITH THE 2013 EDITION OF THE CALIFORNIA BUILDING CODE. DETAILS WITHIN THIS APPROVAL MAY BE USED ANYWHERE IN THE STATE OF CALIFORNIA WHERE $\rm S_{DS} \le 2.0$
- 3. SEISMIC FORCES ON EQUIPMENT DETERMINED PER THE 2013 CBC & ASCE 7-10. ALL LOADS BELOW ARE FACTORED LOADS THAT SHALL BE USED FOR STRENGTH DESIGN.
- 4. EQUIPMENT MAY BE MOUNTED TO AN ELEVATED SLAB AT ANY FLOOR USING THE THROUGH BOLT CONDITION OR TO A NORMAL WEIGHT CONCRETE SLAB ON GRADE. THE MINIMUM REQUIRED SLAB PROPERTIES ARE AS FOLLOWS:

SLAB ON GRADE	ELEVATED SLAB			
THICKNESS ≥ 5" fc ≥ 3000 PSI NORMAL WEIGHT CONCRETE PROVIDE 8" MIN DISTANCE TO ANY OPENINGS, THE EDGE OF SLAB, OTHER ANCHORS OR ATTACHMENTS TO SLAB 6-1/2" MIN SPACING	CONCRETE ON METAL DECK fc ≥ 3000 PSI NORMAL OR SAND LIGHT-WEIGHT CONCRETE SEE FIGURE ON PAGE 2 FOR MINIMUM STEEL DECK REQUIREMENTS			

- 5. THE FACTORS USED TO CALCULATE THE SEISMIC DEMANDS ARE THE FOLLOWING:
- a. $S_{DS} \le 2.0$, ap = 2.5, Rp = 6.0, lp = 1.5, Ω o = 2.5,

WHERE $z/h \le 1$ WHERE z/h = 0

i. Fp = 1.50 Wp ii. Fp = 0.90 Wp iii. Ev = 0.40 Wp

iii. Ωo Fp, = 3.75 Wp iii. Ωo Fp, = 2.25 Wp (FOR ANCHORAGE TO CONCRETE)

- 6. THE STRUCTURAL ENGINEER-OF-RECORD (S.E.O.R.) OR PRINCIPAL-IN-CHARGE OF A PROJECT SPECIFIC SITE IS RESPONSIBLE FOR THE FOLLOWING:
- a. VERIFY THAT THE ATTACHMENTS ARE A MINIMUM 8" FROM ANY OPENINGS OR EDGES.
- b. VERIFY THAT THE ATTACHMENTS ARE A MINIMUM 6-1/2" FROM ANY NEW OR EXISTING ANCHORS.
- c. DESIGN ANY SUPPLEMENTARY MEMBERS TO WHICH THE UNIT IS ATTACHED, TO SUPPORT WEIGHTS AND FORCES SHOWN. VERIFY THE ADEQUACY OF ANY EXISTING MEMBERS AND THEIR ATTACHMENTS FOR THE FORCES EXERTED ON THEM BY THE UNIT IN ADDITION TO ALL OTHER LOADS AND FORCES.
- d. VERIFY THAT THE INSTALLATION IS IN CONFORMANCE WITH THE 2013 CBC AND WITH THE DETAILS SHOWN IN THIS PRE-APPROVAL. VERIFY THAT THE EQUIPMENT'S ACTUAL WEIGHT, CG LOCATION, ANCHOR LOCATIONS, DETAILS AND THE MATERIAL AND GAGE OF THE UNIT WHERE ATTACHMENTS ARE MADE AGREE WITH THE INFORMATION SHOWN IN THIS PRE-APPROVAL.
- e. STRUCTURAL ENGINEER-OF-RECORD (S.E.O.R.) OR PRINCIPAL-IN-CHARGE OF A SITE SPECIFIC PROJECT SHALL EVALUATE THE ATTACHMENT FOR CONDITIONS THAT VARY FROM THIS PRE-APPROVAL.
- 7. THIS OPM COVERS ONLY THE SUPPORTS AND ATTACHMENTS OF THE UNIT TO THE STRUCTURE.
- 8. EXPANSION OR WEDGE ANCHORS INTO CONCRETE: HILTI KB-TZ (ICC ESR-1917). INSTALL ANCHORS IN ACCORDANCE WITH THE ICC REPORT AND MANUFACTURER'S RECOMMENDATIONS. TEST AT LEAST 50% OF ANCHORS NO SOONER THAN 24 HOURS AFTER INSTALLATIONS. TESTS SHALL BE CONDUCTED IN THE PRESENCE OF THE SPECIAL INSPECTOR AND A REPORT OF THE TEST RESULTS SHALL BE SUBMITTED TO OSHPD. TEST PER ONE OF THE FOLLOWING METHODS:
- a. DIRECT PULL TENSION TEST. ANCHOR IS ACCEPTABLE IF NO MOVEMENT IS OBSERVED FOR A MINIMUM OF 15 SECONDS AT THE TEST LOAD GIVEN IN TABLE ON THE FOLLOWING PAGE. MOVEMENT MAY BE DETERMINED WHEN THE WASHER UNDER THE NUT BECOMES LOOSE.
- b. TORQUE WRENCH TEST: TEST ANCHORS TO THE REQUIRED TORQUE LOAD GIVEN IN TABLE ON THE FOLLOWING PAGE WITHIN THE LIMIT OF ONE-HALF TURN OF THE NUT.

PAGE 1 OF 6



OPM 0116 - 13

DEGENKOLB ENGINEERS235 Montgomery Street, Suite 500
San Francisco, CA 94104

San Francisco, CA 94104 415.392.6952 *Phone* 415.981.3157 *Fax* www.degenkolb.com

PANDUIT 2 POST CABLE MANAGEMENT RACK


MODELS R2P, R2PS, R2P6S

GENERAL NOTES

ANCHOR TEST LOAD VALUES								
ANCHOR DIAMETER (IN)	EMBED hef (IN)	TENSION LOAD (LBS)	TORQUE LOAD (FT-LB)	CONCRETE TYPE	MINIMUM EDGE DISTANCE	MINIMUM SPACING		
5/8"	3-1/8"	3,134	60	NORMAL WEIGHT	12"	6-1/2"		
3/8"	2"	SEE NOTE a	25	SAND LIGHT-WEIGHT	12"	11"		

a. TEST 3/8" EXPANSION ANCHORS USING THE TORQUE WRENCH TEST METHOD PER MANUFACTURER'S RECOMMENDATION AND AS DESCRIBED IN PAGE 1 OF 6


- 18. CENTER OF GRAVITY (C.G.) WEIGHT IS A MAXIMUM. THIS PREAPPROVAL ENCOMPASSES ALL WEIGHTS UP TO THE MAXIMUM SHOWN.
- 19. EQUIPMENT MANUFACTURER MUST DESIGN UNIT TO MAKE C.G. EQUAL OR LESS THAN THE C.G. HEIGHT DIMENSION SHOWN ON THE TABLE ON PGE 4 OF 6
- 20. WHEN INSTALLING DRILLED-IN ANCHORS IN EXISTING NON-PRESTRESSED REINFORCED CONCRETE, USE CARE AND CAUTION TO AVOID CUTTING OR DAMAGING THE EXISTING REINFORCING BARS. WHEN INSTALLING THEM INTO EXISTING PRESTRESSED CONCRETE (PRE- OR POST-TENSIONED) LOCATE THE PRESTRESSED TENDONS BY USING A NON-DESTRUCTIVE METHOD PRIOR TO INSTALLATION. EXERCISE EXTREME CARE AND CAUTION TO AVOID CUTTING OR DAMAGING THE TENDONS DURING INSTALLATION. MAINTAIN A MINIMUM CLEARANCE OF ONE INCH BETWEEN THE REINFORCEMENT AND THE DRILLED-IN ANCHOR.



- 10. CONTRACTOR OR SEOR MUST VERIFY ANCHOR SPACING TO ADJACENT EQUIPMENT ANCHORS. SPACING TO EXISTING ANCHORS IS TO BE GREATER THAN 8".
- 11. ALL MISCELLANEOUS STEEL SHALL CONFORM TO THE FOLLOWING, UNLESS OTHERWISE NOTED: DATE: 04/07

BOLTS A307 GR. A. PLATE WASHER ASTM A36

- 12. THE TABLE ON PAGE 3 SHOWS THE MOST CRITICAL FORCES CALCULATED FOR THE SUPPORT AND ATTACHMENT DESIGN.
- 13. FOR THE SUPPORT AND ATTACHMENT DESIGN, THE MOST CRITICAL LOAD COMBINATION IS (0.9 0.2 Sds) D \pm
- 14. WHEN z / h = 0, THE DESIGN FORCES FOR THE EXPANSION ANCHORS INTO CONCRETE WERE SCALED UP BY Ω_0 AS REQUIRED BY ASCE 7-10, SUPPLEMENT NO. 1, TABLE 13.6-1.
- 15. Tult + q IS THE FORCE DEMAND IN THE ANCHOR INCLUDING EFFECTS OF PRYING
- 16. THE TABLE ON PAGE 4 SHOWS THE PROPERTIES OF THE DIFFERENT MODELS CONSIDERED IN THIS SUBMITTAL.
- 17. WHERE q = 0 AS INDICATED ON THE TABLE OF PAGE 3, EITHER THE SUPPORT AND ATTACHMENT MECHANISM IS GOVERNED BY THE CAPACITY OF THE BASE BRACKET OR THE FITTING HAS SUFFICIENT STIFFNESS AND STRENGTH TO DEVELOP THE FULL BOLT AVAILABLE TENSILE STRENGTH AND ELIMINATE PRYING ACTION AS DESCRIBED IN THE FOURTEENTH EDITION OF THE AISC STEEL CONSTRUCTION MANUAL



NOTES

- 1. PROVIDE 8" MINIMUM DISTANCE TO EDGE OF SLAB, OPENINGS OR OTHER ATTACHMENTS
- 2. SEE NOTES ON PAGE 6 OF 6

MINIMUM STEEL DECK REQUIREMENTS

PAGE² OF 6




OPM 0116 - 13


DEGENKOLB ENGINEERS 235 Montgomery Street, Suite 500 San Francisco, CA 94104 415.392.6952 Phone 415.981.3157 Fax www.degenkolb.com


PANDUIT 2 POST CABLE MANAGEMENT RACK

MODELS R2P, R2PS, R2P6S



ELEVATED SLAB





SLAB ON GRADE

	•		Z/h = 0 TE: 04/07/2015				z / h ≤ 1			
	SELF-WEIGHT	ANGLE 0	LOAD RATING	Tult	q ^a	Vult ^a	LOAD RATING	Tult	q q	Vult ^a
PART NUMBER	(LBS)	(DEGREES)	(LBS)	(LBS)	(PRYING FORCE) (LBS)	(LBS)	(LBS)	(LBS)	(PRYING FORCE) (LBS)	(LBS)
R2P	28	70	300	990	0 (SEE NOTE 6)	75	550	3,000	0(SEE NOTE 7)	220
R2PS	53	70	250	900	60 (SEE NOTE 6)	70	250	1,530	0(SEE NOTE 7)	115
R2P6S	57	60	350	900	60 (SEE NOTE 6)	90	350	1,520	0(SEE NOTE 7)	155

a. FINAL DEMAND FORCES FOR ANCHORAGE TO CONCRETE TO INCLUDE OVERSTRENGTH FACTOR (Ωo). SEE NOTE 4 BELOW.

NOTES:

- 1. z IS THE HEIGHT IN THE STRUCTURE OF THE POINT OF ATTACHMENT OF THE COMPONENT WITH RESPECT TO THE BASE OF THE STRUCTURE.
- 2. h IS THE AVERAGE ROOF HEIGHT.
- 3. THE LOAD RATING IS IN ADDITION TO THE SELF-WEIGHT AT THE CONDITION UNDER CONSIDERATION; (Wp = SELF-WEIGHT + LOAD RATING)
- 4. THE DESIGN FORCES Tult, q AND Vult ON THE TABLE ABOVE ARE AT STRENGTH LEVEL AND ARE NOT AMPLIFIED BY Ωo. FINAL DEMAND FORCES FOR ANCHORAGE TO CONCRETE TO INCLUDE OVERSTRENGTH FACTOR Ωo.
- 5. Θ IS THE ANGLE AT WHICH Fp GENERATES THE LARGEST TENSILE FORCE DEMAND IN THE ANCHORS
- 6. THE BASE BRACKET HAS ENOUGH STIFFNESS AND STRENGTH TO DEVELOP THE FULL BOLT AVAILABLE TENSILE STRENGTH, BUT INSUFFICIENT STRENGTH TO PREVENT PRYING ACTION AT PART NUMBERS R2PS AND R2P6S
- 7. THE SUPPORT AND ATTACHMENT CAPACITY IS GOVERNED BY THE FLEXURAL CAPACITY OF THE BASE BRACKET

PAGE³ OF 6



OPM 0116 - 13

RACK UPRIGHT

BASE BRACKET EACH

SIDE


CHANNELS BY

PANDUIT


DEGENKOLB ENGINEERS
235 Montgomery Street, Suite 500
San Francisco, CA 94104
415.392.6952 *Phone*415.981.3157 *Fax*www.degenkolb.com

PROFESSIONAL M. AGCHERAL M. AG

PANDUIT 2 POST CABLE MANAGEMENT RACK MODELS R2P, R2PS, R2P6S



- 1. SEE TABLE ON PAGE 3 OF 6 FOR WEIGHTS APPLIED AT C.G.
- 2. ALL HOLES THROUGH STEEL FOR BOLTS SHALL BE STANDARD SIZE HOLES PER AISC 14TH EDITION, TABLE J3.3 (BOLT DIAMETER + 1/16")
- 3. ALL HOLES THROUGH ALUMINUM SHALL BE THE BOLT DIAMETER + 1/16".



ISOMETRIC VIEW

C.G.

PAGE 4 OF 6

I

HCG




OPM 0116 - 13

DEGENKOLB ENGINEERS

235 Montgomery Street, Suite 500 San Francisco, CA 94104 415.392.6952 Phone 415.981.3157 Fax www.degenkolb.com

PANDUIT 2 POST CABLE MANAGEMENT RACK

MODELS R2P, R2PS, R2P6S



NOTES:

- 1. FOR FORCE DEMANDS AND GEOMETRIC PROPERTIES SEE PAGES 3 AND 4 RESPECTIVELY.
- 2. ALL HOLES THROUGH STEEL FOR BOLTS SHALL BE STANDARD SIZE HOLES PER AISC 14TH EDITION, TABLE J3.3 (BOLT DIAMETER + 1/16")

PAGE 5 OF 6




OPM 0116 - 13

DEGENKOLB ENGINEERS235 Montgomery Street, Suite 500

235 Montgomery Street, Suite 50 San Francisco, CA 94104 415.392.6952 *Phone* 415.981.3157 *Fax* www.degenkolb.com

PANDUIT 2 POST CABLE MANAGEMENT RACK

MODELS R2P, R2PS, R2P6S



TOP ANGLES PARALLEL TO METAL DECK FLUTES

SEE NOTE 2

SEE NOTE 2

TOP ANGLES PERPENDICULAR TO METAL DECK FLUTES

PAGE 6 OF 6