# **TX6A<sup>™</sup> Category 6A Shielded F/UTP Outside Plant (OSP) Copper Cable**



## specifications

Category 6A OSP cable shall meet the IEC 61156-5 and ANSI/TIA-568.2-D Category 6A component Standards. The conductors shall be 23 AWG with foamed polyethylene insulation. The cable shall have a gel-filled construction to prevent moisture migration in underground and wet applications and a wide temperature range for extreme weather environments. The copper conductors shall be twisted in pairs, separated by a pair separator, covered with an overall foil shield and a UV-resistant and abrasion-resistant polyethylene (PE) jacket. **Product is to be used in duct and conduit installations only. Not to be used in aerial or direct burial installations.** 



## technical information

Electrical performance:	Certified channel performance in a 4-connector configuration up to 100m and exceeds ISO 11801 Class EA and ANSI/TIA-568.2-D Category 6A Standards for supporting 10GBASE-T transmission over twisted-pair cabling systems as part of the TX6A Copper Cabling System.
	Certified component performance up to 100m and exceeds the IEC 61156-5 and ANSI/TIA-568.2-D Category 6A standards for supporting 10GBASE-T transmission over twisted-pair cabling
Conductors/insulators:	23 AWG solid copper insulated with foamed polyethylene
Standards compliance:	ISO 11801 Class EA, IEC 61156-5 Category 6A, ANSI/TIA-568.2-D Category 6A, IEC 60794-1-2F5 Method B Water Penetration Requirement
Flame rating:	EN50575: Euroclass Fca
PoE compliance:	Meets IEEE 802.3af, IEEE 802.3 at, and IEEE 802.3bt for PoE applications
Insulation tension:	25 lbf (110N) maximum
Temperature rating:	-40°F to 176°F (-40°C to 80°C) during operation 32°F to 122°F (0°C to 50°C) during installation
Cable jacket:	Black UV- and abrasion-resistant polyethylene (PE)
Cable diameter:	0.323" (8.2mm) nominal
Cable weight:	71 lbs./1000' (32 kg/305m)
Packaging:	1000' (305m) reel Package tested to ISTA procedure 1Al

#### key features and benefits

Bulk packaging:	Ensures proper performance and provides quick installation	
Descending length cable markings:	Print legend contains markings from 1000' to 0'	
Robust design:	Shielding protects against environmental elements that can cause electrical performance failures	
Flooding compound:	Waterproof gel prevents moisture migration and water ingress	

#### applications

TX6A OSP Shielded Copper Cable is a component of the TX6A Copper Cabling System. This end-to-end system provides a cost-effective media for ensuring the most challenging network bandwidth needs are easily met today and tomorrow. Businesses are placing increased reliance on their networks to efficiently pass vital and time sensitive information throughout their enterprise.

- Key applications include:
   10GBASE-T Ethernet
  - 10GBASE-1 Ethernet
     1000BASE T Cigabit Ethernet
  - 1000BASE-T Gigabit Ethernet
    10/100BASE-T Etherne
  - Broadband Video
  - POE, POE+, POE++

PRODUCT IS TO BE USED IN DUCT AND CONDUIT INSTALLATIONS ONLY. NOT TO BE USED IN AERIAL OR DIRECT BURY APPLICATIONS.


TX6A Shielded Copper Cable		
Foot lengths:	PFO6XO4BL-CEG	
Mini-Com® TX6A™ 10Gig Shielded Jack Module		
Jack module:	CJS6X88TGY	
TX6A™ 10Gig™ Shielded Patch Cords		
Meters:	STP6X4MIG	
Feet:	STP6X4MIG	
Mini-Com® Angled All Metal Shielded Modular Patch Panels		
24-port, 1 RU:	CPA24BLY	
48-port, 1 RU:	CPA48HDBL	
48-port, 2 RU:	CPA48BLY	
Cable Prep Tools		
Wire snipping tool:	CWST	
Wire stripping tool:	CJAST	

Country of Origin, China: PFO6X04BL-CEG

## additional specifications

Mechanical Test			
Ultimate Breaking Strength	>400 N (90 lbf)		
Minimum Bend Radius	8x Cable Diameter		
Electrical Test			
Nominal Velocity of Propagation (NVP)	65% nominal		
Operating Voltage, Maximum	80V		

#### cable construction



Dimensions are in inches. [Dimensions in brackets are metric].

#### WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty



For more information Visit us at www.panduit.com Contact Customer Service by email: cs@panduit.com or by phone: 800.777.3300

© 2023 Panduit Corp. ALL RIGHTS RESERVED. COSP424-WW-ENG 6/2023