



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO	PACKAGE QTY	MAX BUNDLE DIAMETER MTRTH TOOL
MRS6H-L4	50	6.0" [152.4]



FULLY ROUNDED EDGES ALONG STRAP BODY  
SECTION A - A  
SCALE 4:1

- NOTES:
1. APPLICATION TOOLS - MTRTH
  2. MINIMUM LOOP TENSILE STRENGTH - 400 LBS. (1780 NEWTONS) WHEN TESTED ON A 1.5" MANDREL.
  3. BRACKETS [ ] DENOTE DIMENSIONS IN MILLIMETERS, AND ARE SHOWN FOR REFERENCE ONLY
  4. MATERIAL: CORROSION RESISTANT STEEL, PER ASTM A240/A240M AND ASTM A666.

#	DATE	BY	CHK	APR	DESCRIPTION	ECN
03	3-11-19	JEH	SKB	JADE	WAS: (D) MAX BUNDLE DIAMETER MTRT TOOL.	043980/02
02	3-5-19	JEH	SKB	JADE	(C) REMOVED +/- .02 TOLERANCE. +/- .02 TOLERANCE IS LISTED IN THE TITLE BLOCK. ADDED AISI TO THE MATERIAL SPEC. MATERIAL SPEC WAS 304 STAINLESS STEEL. ADDED NOTE 4.	043980/01
01	1-29-19	JEH	JADE	JADE	WAS: (A) [5.6], (B) [0.31]	043980
00	11-29-18	JEH	SKB	JADE	RELEASED. REMOVED FROM DRAWING N41227BS_DC	042782

TITLE		<b>MRS6H-L4, METAL TIE - HEAVY RETAINED TENSION - 360° RADIAL SEAL</b>		
ITEM REVISION NAME		CUSTOMER DRAWING		
DATASET FILE NAME		N41329BS/03		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		<b>PANDUIT</b>		
.x ± .03 [.8] .xxx ± .010 [.25] .xx ± .02 [.5] ANGLES ± 2°				
DRAWN BY		DATE	CHK	SCALE
JAMB		6/07	EJD	2:1
DRAWING NUMBER:		SHT 1 OF 1		
N41329BS_DC		A		