






THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
3. REFERENCE TIA-568-C.O. FOR DETAILS ON METHOD A CONNECTIVITY.
4. MATERIALS:
A. FRONT PANEL: STEEL
B. BOX AND LID: ALUMINUM
C. ADAPTERS: COMPOSITE PLASTIC
5. CASSETTE WEIGHT: 39.0oz (1100.0g)
6. DIMENSIONS IN BRACKETS ARE METRIC
7. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2011/65/EC ON THE RESTRICTIONS OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.





ISOMETRIC VIEW

							TITLE HDQ SERIES FIBER OPTIC ANGLED CASSETTES FOR CISCO 32 PORTS (64 FIBERS)					
							CUSTOMER DRAWING					
							ITEM REVISION NAME 12F193AF/00					
							DATASET FILE NAME 12F193AF_DC/00B					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .010 [0.3] .XX ± .03 [0.8] ANGLES ±			MATERIAL: SEE NOTES		
01	09-24-13	SAT	YMG		RELEASED TO PRODUCTION	12F193AF-DC	 THIRD ANGLE PROJECTION			DRAWING NUMBER: 12F193AF-DC		
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 3	SIZE A
							SAT	05-15-13	YMG	NONE		

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

TABLE 1 - HDQ SERIES FIBER OPTIC CASSETTE - MPO TO LC 10 GbE 1RU ANGLED PROFILE; 64-FIBER CISCO LABELING	
PART NUMBER	DESCRIPTION
METHOD A	
F1ACXN-6408-10S	OM3 FIBER; 8-FIBER MPO TO DUPLEX LC
F1ACXO-6408-10S	OPTIMIZED OM3 FIBER; 8-FIBER MPO TO DUPLEX LC
F1ACZN-6408-10S	OM4 FIBER; 8-FIBER MPO TO DUPLEX LC
F1ACZO-6408-10S	OPTIMIZED OM4 FIBER; 8-FIBER MPO TO DUPLEX LC
MODIFIED METHOD A, PAIR FLIPPED	
F1ACXN-6408-10F	OM3 FIBER; 8-FIBER MPO TO DUPLEX LC
F1ACXO-6408-10F	OPTIMIZED OM3 FIBER; 8-FIBER MPO TO DUPLEX LC
F1ACZN-6408-10F	OM4 FIBER; 8-FIBER MPO TO DUPLEX LC
F1ACZO-6408-10F	OPTIMIZED OM4 FIBER; 8-FIBER MPO TO DUPLEX LC

							TITLE HDQ SERIES FIBER OPTIC ANGLED CASSETTES FOR CISCO 32 PORTS (64 FIBERS)					
							CUSTOMER DRAWING					
							ITEM REVISION NAME 12F193AF/00					
							DATASET FILE NAME 12F193AF_DC/00B					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .010 [0.3] .XX ± .03 [0.8] ANGLES ±				MATERIAL: SEE NOTES SHEET 1	
							 THIRD ANGLE PROJECTION				DRAWING NUMBER: 12F193AF - DC	
01	09-24-13	SAT	YMG		RELEASED TO PRODUCTION	12F193AF-DC						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY SAT	DATE 05-15-13	CHK YMG	SCALE NONE	SHT 2 OF 3	SIZE A

