TX6[™] U/UTP Outside Plant (OSP) Copper Cable



specifications

Category 6 OSP cable shall meet the ANSI/TIA-568.2-D and IEC 61156-5 Category 6 component Standards. The conductors shall be 23 AWG construction with polyolefin insulation. The cable shall have a gel-filled construction to prevent moisture migration in underground and wet applications and a wide temperature range for extreme weather environments. The copper conductors shall be twisted in pairs, separated by a pair separator and covered with a UV-resistant and abrasion-resistant polyethylene (PE) jacket. Product is to be used in duct and conduit installations only. Not to be used in aerial or direct burial applications.



technical information

Electrical Performance:	Certified channel performance in a 4-connector configuration up to 100m and exceeds ANSI/TIA-568.2-D Category 6 and ISO 11801 Class E standards at swept frequencies up to 250 MHz	
	Certified component performance up to 100m and exceeds the component requirements of ANSI/TIA-568.2-D and IEC 61156-5 Category 6 component standards at swept frequencies up to 250 MHz	
Conductors/insulators:	23 AWG solid copper insulated with polyolefin	
Standards compliance:	ANSI/TIA-568.2-D Category 6 and ISO 11801 Class E; IEC 60794-1-2F5 Method B Water Prevention Requirement EN50575: Euroclass Fca	
Installation tension:	25 lbf (110 N) maximum	
Temperature rating:	-22°F to 140°F (-30°C to 60°C) during installation	
	-40°F to 176°F (-40°C to 80°C) during operation	
Cable jacket:	Black UV-resistant and abrasion-resistant polyethylene (PE)	
Cable diameter:	0.262" (6.7mm) nominal	
Cable weight:	0.262" (6.7mm) nominal	
Packaging:	1000' (305m) on a reel	

key features and benefits

Robust design	Protects against environmental elements that can cause electrical performance failures	
Flooding compound	Waterproof gel prevents moisture migration	
Reel	Ensures proper performance and provides quick installation	
Descending length cable markings	Easy identification of remaining cable reduces installation time and cable scrap	

applications

TX6 U/UTP OSP Copper Cable is a component of the TX6 UTP Copper Cabling System. This end-toend system provides Gigabit Ethernet performance with usable bandwidth beyond 250 MHz. With certified performance to the ANSI/TIA-568.2-D Category 6 and ISO 11801 Class E Standards, this system will support the following applications:

- Ethernet 10BASE-T
- 100BASE-T (Fast Ethernet)
- 1000BASE-T (Gigabit Ethernet)

PRODUCT IS TO BE USED IN DUCT AND CONDUIT INSTALLATIONS ONLY. NOT TO BE USED IN AERIAL OR DIRECT BURIAL APPLICATIONS.

TX6 UTP Copper Cable

OSP: PUO6C04BL-CEG

Mini-Com® TX6 PLUS UTP Jack Module

Jack module: CJ688TGIW*

TX6 PLUS UTP Patch Cords – CM

Foot lengths: UTPSP3^Y

Meter lengths: UTPSP1^AMY

DP6[™] PLUS Punchdown Patch Panels

Angled, 24-port, 1 RU: DPA24688TGY Angled, 48-port, 1 RU: DPA48688TGY

 Flat, 12-port:
 DP12688TGY

 Flat, 24-port, 1 RU:
 DP24688TGY

 Flat, 48-port, 2 RU:
 DP48688TGY

Mini-Com[®] Flush Mount Modular Patch Panels

Angled, 24-port, CPPA24FMWBLY 1 RU:

Angled, 48-port, 1 RU:

Flat, 24-port, 1 RU: CPPA24FMWBLY

CPPA48FMWBLY

Flat, 48-port, 2 RU: CPPA48FMWBLY

Termination and Cable Prep Tools

Termination tools: EGJT or TGJT
Conductor CWST

snipping tool: Conductor stripping tool:

....

CJAST

*To designate a color, add suffix IW (Off White), EI (Electric Ivory), IG (International Gray), WH (White), BL (Black), OR (Orange), RD (Red), BU (Blue), GR (Green), YL (Yellow), or VL (Violet).


Country of Origin, China: PUO6C04BL-CEG

TX6™ U/UTP Outside Plant (OSP) Copper Cable

additional specification

Mechanical Test			
Ultimate Breaking Strength	>90 lbf (400 N)		
Minimum Bend Radius	4 × Cable Diameter		
Electrical Test			
Nominal Velocity of Propagation (NVP)	67% nominal		
Operating Voltage, Maximum	80 V		

cable construction



WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575

PANDUIT JAPAN Tokyo, Japan Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020



For a copy of Panduit product warranties, log on to www.panduit.com/warranty