


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



2

1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT. 2. DIMENSIONS IN [] ARE METRIC. 3. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF ROHS (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE ROHS TECHNICAL ADAPTATION COMMITEE. 1. THE CT-2931/STBT BATTERY OPERATED TOOLS ARE DESIGNED TO CRIMP WITH PANDUIT CRIMP DIES. 2. CRIMPS PANDUIT COPPER AND ALUMINUM COMPRESSION CONNECTORS USING PANDUIT CRIMPING DIES. GO TO www.panduit.com FOR MORE INFORMATION. 3. THIS TOOL CAN OPERATE WITH BLUE TOOTH TECHNOLOGY TO CONNECT TO THE I-PRESS PHONE APP TO MONITOR CRIMP PERFORMANCE. THE CT-2931/STBT TOOL KIT INCLUDES: BATTERY OPERATED 12 TON HYDRAULIC CRIMP TOOL RECHARGEABLE BATTERIES (MAKITA LI-ION 18VDC, 4Ah) MAKITA BATTERY CHARGER - 120VAC (WITH US PLUG CONFIGURATION) TECHNICAL INFORMATION: 1. TOOL WEIGHT (INCLUDING BATTERY) 15.9 LBS. [7.2 kg] 2. DIMENSIONS (INCLUDING BATTERY) 16.8" L × 12.8" H× 3.0" W [428 L × 324 H × 76 W] mm 3. CRIMPING FORCE 12 TONS [108 kN] 4. A COPY OF OPERATION MANUAL AND ACCESSORY INFORMATION CAN BE FOUND AT: www.panduit.com. DIMENSIONS IN [BRACKETS] ARE IN MILLIMETERS. ALL DIMENSIONS ARE FOR REFERENCE ONLY. Δ PART NUMBER CT-2931/STBT TITLE

CT-2931/STBT, Customer Drawing, 12 Ton, Next Generation Crimp Tool

CUSTOMER DRAWING					
EM REVISION NAME					
	00828	EBX/01	×		
TASET FILE NAME					
00828EBX_DC/01				PANDU	
F			IRD ANGLE OJECTION		
TERIAL				DRAWING NUMBER	
AS NOTED				00828EBX_DC	
AWN BY	DATE	СНК	SCALE		SIZE
BJPU	11-24-21	JEH	NONE	SHEET 1 OF 1	В
1					