TX6A[™] 10Gig[™] Shielded Patch Cords



SPECIFICATIONS

Category 6A/Class EA, S/FTP patch cords shall be constructed of 26 AWG shielded twisted pair stranded copper cable with an enhanced performance shielded modular plug at each end. Patch cord cable shall be offered in multiple colored S/FTP cable for design flexibility with a black strain relief boot on each modular plug. All patch cords shall be compatible with both T568A and T568B wiring schemes.



TECHNICAL INFORMATION

Category 6A/ISO 11801 Class E _A channel and component performance:	Exceeds all ANSI/TIA-568.2-D Category 6A and ISO 11801 Class EA standards for all frequencies up to 500 MHz◊	
FCC and ANSI compliance:	Meets ANSI/TIA-1096-A requirements (formerly FCC Part 68); contacts plated with 50 microinches of gold for superior performance	
IEC compliance:	Meets IEC 60603-7	
PoE compliance:	Rated for 2500 cycles with IEEE 802.3af / 802.3at and 802.3bt type 3 and type 4	
c(UL)us compliance:	UL 1863 approved	
RoHS compliance:	Compliant	
Flame rating:	Meets IEC 60332-1, IEC 60754-1, IEC 61034-2	
Cable diameter:	0.24 in. (6.1mm) nominal	
Operating temperature:	14°F-167°F (-10°C-75°C)	
Installation temperature:	-40°F-158°F (-40°C-70°C)	
Flammability rating:	CM LSZH dual rated	

KEY FEATURES AND BENEFITS

100% performance tested for wire map, NEXT, and return loss:	Confidence that each patch cord delivers specified component level performance	
Flexible stranded cable:	Copper cable made of 0.24 inch S/FTP stranded 26 AWG allows for high density applications and superior panel cable management	
Center de-embedded plug:	Performs in center of ANSI/TIA-568.2-D component range, ensuring interoperability and superior performance	
Integral pair manager:	Optimizes performance and consistency by reducing untwist at plug	
Patented tangle-free latch:	Prevents snags and provides easy release, saving time on frequent moves, adds, and changes	
Slender strain relief boot:	Provides easy access in high-density applications	

APPLICATIONS

TX6A 10Gig Shielded Patch Cords are a component of the TX6A10Gig Shielded Copper Cabling System. This end-to-end system provides a cost effective medium for ensuring that network bandwidth needs are easily met today and tomorrow. This shielded cabling system provides high performance, excellent EMI suppression, and aids in secure data transmission. The Panduit solution helps ensure organizations efficiently and reliably meet their data transmission needs. With certified performance to the ISO 11801 Class EA, IEEE 802.3an-2006 and ANSI/TIA-568.2-D Category 6A standards, this system will support the following applications:

- Stacking switched and switch-to-switch links
- Aggregation of Gigabit Ethernet channels
- Streaming video
- Scientific modeling
- Storage area networks
- Real-time intensive financial transactions
- Animation
- Medical imaging

TX6A 10Gig Shielded Patch Cords*

Foot lengths: STP6X*IG STP6X**MIG Meter lengths:

Tools and Accessories

Patch cord removal tool:

PCRT1

Flashlight kit: **KPCRT1-FL** Patch cord band: PCBAND^^Q

Standard RJ45 plug lock-in device:

PSL-DCPLE^^^+

Recessed RJ45 plug

PSL-DCPLRE^^^+ lock-in device:

*Feet lengths: 1-20 feet (every 1 foot)

25 - 50 feet (every 5 feet)

100 feet

**Meter lengths: 0.2 meters

0.5 - 5 meters (every 0.5 meters) 5 - 20 meters (every 1 meter) 25 - 50 meters (every 5 meters)

^Color: BU (Blue), BL (Black), GR (Green), RD (Red), YL (Yellow) or VL (Violet), or

IG (International Gray)

^^Color: BU (Blue), BL (Black), WH (White), GR (Green), RD (Red), YL (Yellow), VL (Violet), IG (International Gray), or El (Electric Ivory)

^^^ Colors other than Red: -BU (Blue), -BL (Black), -GR (green), -YL (Yellow), -IW (Off White), or IG (International Gray).

-Q indicates bulk packages with 25 pieces per pack to reduce singe-use plastic

++Add -X to indicates bulk packages with 10 pieces per pack or -C to indicate bulk packages with 100 pieces per pack to reduce singe-use plastic

♦ Lengths 1m to 15m or 6 inch to 49 feet are guaranteed to meet TIA and ISO component and channel requirements. Lengths greater than 15m or 49 feet are guaranteed to meet ISO component and both TIA and ISO channel requirements




TX6A™ 10Gig™ Shielded Patch Cords are pre-labeled with the RapidID™ Network Mapping System to enable faster tracing, placing, and network documentation. Learn more: www.panduit.com/rapid-id



All Part Numbers Compliant with the U.S. Trade Agreements Act (TAA) for purchases shipped to the United States.

TX6A[™] 10Gig[™] Shielded Patch Cords


ENGINEERING DRAWING





Recycle at end of life

T568B Wiring Scheme		
Plug Position	Cable Wire	
1	White/Orange	
2	Orange	
3	White/Green	
4	Blue	
5	White/Blue	
6	Green	
7	White/Brown	
8	Brown	



WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

