
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT	BUNDLE	E DIA.	Α	В	С	D	Е	F	MIN. LOOP	CROSS-	WEIGHT
PART NO.*	MIN.in	MAX.in	in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	TENSILE lbs.	SECTION	lbs./100pcs. (g)
SST1.5S	.06 (1.5)	1.25 (32)	.045	.180 (4.6)	.250 (6.4)	.165 (4.2)	.310 (7.9)	5.7 (146)	50 (222)	STANDARD	.18 (80)
SST2S	.06 (1.5)	1.75 (45)	.045	.180 (4.6)	.250 (6.4)	.165 (4.2)	.310 (7.9)	6.7 (172)	50 (222)	STANDARD	.22 (100)
SST3S	.06 (1.5)	3.00 (76)	.048	.180 (4.6)	.250 (6.4)	.165 (4.2)	.310 (7.9)	11.0 (279)	50 (222)	STANDARD	.44 (201)
SST4S	.06 (1.5)	4.00 (102)	.048	.180 (4.6)	.253 (6.4)	.200 (5.1)	.350 (8.9)	15.0 (381)	50 (222)	STANDARD	.59 (266)

NOTES:

*1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR. 2) RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC.

										DIMEN	SIONS IN PARENTHESES ARE	IN METRIC UNIT	·S.	
											CORP. TINLEY PARK, ILLINOIS			
										STA-STRAP CABLE TIES SS SERIES				
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .020(.51) (.XX) ± .02(.5) ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJE		
									[DRAWN BY JABO	MAT'L;	SCALE NONE		
4	11-29-01	JABO		REVISED AND REDRAWN	5550	4			1	date 11-29-01	NYLON 6.6	DRAWING NO. SS - 5550	DWG	
REV	DATE	BY	CHK	DESCRIPTION	ECN -	- R	CUST	SUP		CHK 'D		SHEET 2 OF 3	SIZE	