



Best-in-Class Outlet Density

---

Optimal Form Factors

---

Superior Reliability

---

Smartzone™ G5

# PDU Pocket Guide

NORTH AMERICA

**PANDUIT**®

infrastructure for a connected world



### Quality & Reliability

3-Year standard and 5-Year extended warranty.



### High Temperature

Built with premium components to withstand 140°F (60°C) at full load.



### High Density Power

Unique outlets design for high outlet density.



### Hot-Swappable & Upgradable

Hot-Swappable Controller with large OLED display.



### Hardened Security

Enhanced security with certificate-based advanced asymmetric encryption, validated and hardened with multiple security scanning tools.



### 1GB On Board Ethernet Connection

Reduces deployment time and labor as PDU auto negotiates to 1GB network switches.



### Real-Time Monitor

Real-time Monitoring of Power, Environmental & Cabinet Security.



### Plug & Play Accessories

Variety Environmental & Cabinet Access Control Accessories.



### Multi-Device WebGUI

Enhanced User-Experience with a self adjusting WebGUI that senses the device you are on.



### Multi-Color

A variety of colored PDU chassis, power cords, and cable ties.

### Monitored Input (MI Series)

Input power monitoring.

### Monitored Switched (MS Series)

Input power monitoring and outlet switching.

### Monitored Per Outlet (MPO Series)

Input and Outlet level power monitoring.

### Monitored & Switched Per Outlet (MSPO Series)

Input and Outlet level power monitoring and outlet switching.

**Note:** All intelligent PDU's include environmental monitoring with rack access control.


### Basic PDU's

Reliable power distribution (non-network).

### Accessories

Offering a variety of Environmental Sensors; Security Devices and Power Cords.

# G5 iPDU

























# Monitored Input (MI Series)

	Input Current per phase	Form Factor	Input Plug Type	Apparent Power (kVA)	Outlet Count	Outlet Configuration	Length (inches)	Width (inches)	Depth (inches) at Outlet position	Panduit Part No.
100-240VAC, 1-Phase	15	1U	5-15P	1.4	8	Ⓢ (8)5-20R	1.7	17.5	10.6	P08D09M
	20	1U	5-20P	1.9	8	Ⓢ (8)5-20R	1.7	17.5	10.6	P08D10M
	20	1U	L5-20P	1.9	8	Ⓢ (8)5-20R	1.7	17.5	10.6	P08D11M
	20	1U	L6-20P	3.3	12	Ⓢ (12)C13	1.7	17.5	10.6	P12D13M
	15	0U HALF	5-15P	1.4	16	Ⓢ (16)5-20R	32.2	2.0	2.1	P16D20M
	20	0U HALF	5-20P	1.9	16	Ⓢ (16)5-20R	32.2	2.0	2.1	P16D21M
	20	0U HALF	L5-20P	1.9	16	Ⓢ (16)5-20R	32.2	2.0	2.1	P16D22M
	30	0U MID	L5-30P	2.9	24	Ⓢ (24)5-20R	58.7	2.0	2.1	P24D23M
	20	0U MID	L6-20P	3.3	24	Ⓢ (20)C13, Ⓢ (4)C19	58.7	2.0	2.1	P24D24M
	30	2U	L5-30P	2.9	16	Ⓢ (16)5-20R	3.4	17.5	10.6	P16D12M
200-240VAC, 1-Phase	50	1U	CS8265C	8.3	6	Ⓢ (6)C19	1.7	17.5	10.6	P06D15M
	30	2U	L6-30P	5.0	16	Ⓢ (12)C13, Ⓢ (4)C19	3.4	17.5	10.6	P16D14M
	30	0U MID	L6-30P	5.0	24	Ⓢ (20)C13, Ⓢ (4)C19	58.7	2.0	2.1	P24D07M
	30	0U FULL	L6-30P	5.0	38	Ⓢ (32)C13, Ⓢ (6)C19	68.9	2.0	2.1	P38D25M
	50	0U FULL	CS8265C	8.3	36	Ⓢ (30)C13, Ⓢ (6)C19	68.9	2.0	2.1	P36D26M

# Monitored Input (MI Series)

	Input Current per phase	Form Factor	Input Plug Type	Apparent Power (kVA)	Outlet Count
100-120/200-240VAC, 3-Phase	30	1U	L21-30P	8.6	6
	30	0U MID	L21-30P	8.6	24
	30	0U FULL	L21-30P	8.6	30
	30	0U FULL	L21-30P	8.6	38
208VAC, 3-Phase	30	1U	L15-30P	8.6	6
	50	1U	CS8365C	14.4	6
	60	1U	IEC 60309 3P+E 9h (IP44)	17.3	6
	30	0U MID	L15-30P	8.6	24
	30	0U FULL	L15-30P	8.6	36
	50	0U FULL	CS8365C	10.0	36
	50	0U FULL	CS8365C	14.4	24
60	0U FULL	IEC 60309 3P+E 9h (IP44)	17.3	24	

Outlet Type	Length (inches)	Width (inches)	Depth (inches) at Outlet position	Panduit Part No.
 (6)C19	1.7	17.5	10.6	P06D17M
 (18)C13,  (6)C19	58.7	2.0	2.1	P24D01M
 (18)C13,  (6)C19,  (6)5-20R	68.9	2.0	2.1	P30D02M
 (30)C13,  (6)C19,  (2)5-20R	68.9	2.0	2.1	P38D28M
 (6)C19	1.7	17.5	10.6	P06D16M
 (6)C19	1.7	17.5	10.6	P06D18M
 (6)C19	1.7	17.5	10.6	P06D19M
 (18)C13,  (6)C19	58.7	2.0	2.1	P24D27M
 (30)C13,  (6)C19	68.9	2.0	2.1	P36D08M
 (30)C13,  (6)C19	68.9	2.0	2.1	P36D29M
 (12)C13,  (12)C19	68.9	2.0	2.1	P24D31M
 (12)C13,  (12)C19	68.9	2.0	2.1	P24D34M

# Monitored Input (MI Series)

	Input Current per phase	Form Factor	Input Plug Type	Apparent Power (kVA)	Outlet Count	Outlet Type	Length (inches)	Width (inches)	Depth (inches) at Outlet position	Panduit Part No.
415VAC, 3-Phase	30	1U	IEC 60309 3P+N+E 6h 30A (IP67)	17.3	6	☐ (6)C19	1.7	17.5	10.6	P06D01M
	30	1U	IEC 60309 3P+N+E 6h 30A (IP44)	17.3	6	☐ (6)C19	1.7	17.5	10.6	P06D03M
	30	1U	NEMA L22-30P	17.3	6	☐ (6)C19	1.7	17.5	10.6	P06D02M
	30	0U FULL	IEC 60309 3P+N+E 6h 30A (IP67)	17.3	24	☐ (12)C13, ☐ (12)C19	68.9	2.0	2.1	P24D02M
	30	0U FULL	IEC 60309 3P+N+E 6h 30A (IP44)	17.3	24	☐ (12)C13, ☐ (12)C19	68.9	2.0	2.1	P24D05M
	30	0U FULL	NEMA L22-30P	17.3	24	☐ (12)C13, ☐ (12)C19	68.9	2.0	2.1	P24D04M
	30	0U FULL	IEC 60309 3P+N+E 6h 30A (IP67)	17.3	36	☐ (24)C13, ☐ (12)C19	68.9	2.0	2.1	P36D01M
	30	0U FULL	IEC 60309 3P+N+E 6h 30A (IP44)	17.3	36	☐ (24)C13, ☐ (12)C19	68.9	2.0	2.1	P36D03M
	30	0U FULL	NEMA L22-30P	17.3	36	☐ (24)C13, ☐ (12)C19	68.9	2.0	2.1	P36D02M
	30	0U FULL - Wide	NEMA L22-30P	17.3	48	☐ (48)C13,	68.9	3.3	2.1	P48D03M
	30	0U FULL - Wide	IEC 60309 3P+N+E 6h 30A (IP67)	17.3	48	☐ (48)C13,	68.9	3.3	2.1	P48D04M
	30	0U FULL - Wide	IEC 60309 3P+N+E 6h 30A (IP44)	17.3	48	☐ (48)C13,	68.9	3.3	2.1	P48D08M
	30	0U FULL +	IEC 60309 3P+N+E 6h 30A (IP67)	17.3	42	☐ (36)C13, ☐ (6)C19	74.6	2.0	2.1	P42D05M
	30	0U FULL +	NEMA L22-30P	17.3	42	☐ (36)C13, ☐ (6)C19	74.6	2.0	2.1	P42D07M
	30	0U FULL +	IEC 60309 3P+N+E 6h 30A (IP44)	17.3	42	☐ (36)C13, ☐ (6)C19	74.6	2.0	2.1	P42D08M

# Monitored Switched (MS Series)

	Input Current per phase	Form Factor	Input Plug Type	Apparent Power (kVA)	Outlet Count	Outlet Type	Length (inches)	Width (inches)	Depth (inches) at Outlet position	Panduit Part No.
100-240VAC, 1-Phase	15	1U	5-15P	1.4	8	Ⓢ (8)5-20R	1.7	17.5	10.6	P08E14M
	20	1U	5-20P	1.9	8	Ⓢ (8)5-20R	1.7	17.5	10.6	P08E15M
	20	1U	L5-20P	1.9	8	Ⓢ (8)5-20R	1.7	17.5	10.6	P08E16M
	20	1U	L6-20P	3.3	8	Ⓢ (8)C13	1.7	17.5	10.6	P08E18M
	30	2U	L5-30P	2.9	16	Ⓢ (16)5-20R	3.4	17.5	10.6	P16E17M
	15	0U HALF	5-15P	1.4	12	Ⓢ (12)5-20R	36.1	2.0	2.1	P12E20M
	20	0U HALF	5-20P	1.9	12	Ⓢ (12)5-20R	36.1	2.0	2.1	P12E21M
	20	0U HALF	L5-20P	1.9	12	Ⓢ (12)5-20R	36.1	2.0	2.1	P12E22M
	20	0U HALF	L6-20P	3.3	16	Ⓢ (12)C13, Ⓢ (4)C19	36.1	2.0	2.1	P16E24M
	30	0U MID	L5-30P	2.9	18	Ⓢ (18)5-20R	58.7	2.0	2.1	P18E23M
200-240VAC, 1-Phase	30	2U	L6-30P	5.0	16	Ⓢ (12)C13, Ⓢ (4)C19	3.4	17.5	10.6	P16E19M
	30	0U FULL	L6-30P	5.0	24	Ⓢ (20)C13, Ⓢ (4)C19	68.9	2.0	2.1	P24E28M
	30	0U FULL	L6-30P	5.0	36	Ⓢ (30)C13, Ⓢ (6)C19	68.9	2.0	2.1	P36E33M
100-120/200-240VAC, 3-Phase	30	0U FULL	L21-30P	8.6	24	Ⓢ (18)C13, Ⓢ (6)C19	68.9	2.0	2.1	P24E30M
	30	0U FULL	L21-30P	8.6	36	Ⓢ (30)C13, Ⓢ (6)C19	68.9	2.0	2.1	P36E35M
208VAC, 3-Phase	30	0U FULL	L15-30P	8.6	24	Ⓢ (18)C13, Ⓢ (6)C19	68.9	2.0	2.1	P24E29M
	30	0U FULL	L15-30P	8.6	36	Ⓢ (30)C13, Ⓢ (6)C19	68.9	2.0	2.1	P36E34M
	50	0U FULL	CS8365C	14.4	24	Ⓢ (12)C13, Ⓢ (12)C19	68.9	2.0	2.1	P24E31M
	50	0U FULL	CS8365C	10.0	36	Ⓢ (30)C13, Ⓢ (6)C19	68.9	2.0	2.1	P36E12M
	60	0U FULL	IEC 60309 3P+E 9h (IP44)	17.3	24	Ⓢ (12)C13, Ⓢ (12)C19	68.9	2.0	2.1	P24E32M

## Monitored Switched (MS Series)










	Input Current per phase	Form Factor	Input Plug Type	Apparent Power (kVA)	Outlet Count	Outlet Type	Length (inches)	Width (inches)	Depth (inches) at Outlet position	Panduit Part No.
415 VAC, 3-Phase	30	0U FULL	IEC 60309 3P+N+E 6h 30A (IP67)	17.3	24	☹ (12)C13, ☹ (12)C19	68.9	2.0	2.1	P24E05M
	30	0U FULL	IEC 60309 3P+N+E 6h 30A (IP67)	17.3	24	☹ (18)C13, ☹ (6)C19	68.9	2.0	2.1	P24E07M
	30	0U FULL	IEC 60309 3P+N+E 6h 30A (IP67)	17.3	24	☹ (24)C13	68.9	2.0	2.1	P24E08M
	30	0U FULL	IEC 60309 3P+N+E 6h 30A (IP44)	17.3	24	☹ (12)C13, ☹ (12)C19	68.9	2.0	2.1	P24E09M
	30	0U FULL	IEC 60309 3P+N+E 6h 30A (IP44)	17.3	24	☹ (18)C13, ☹ (6)C19	68.9	2.0	2.1	P24E10M
	30	0U FULL	IEC 60309 3P+N+E 6h 30A (IP44)	17.3	24	☹ (24)C13	68.9	2.0	2.1	P24E11M
	30	0U FULL	NEMA L22-30P	17.3	24	☹ (12)C13, ☹ (12)C19	68.9	2.0	2.1	P24E06M
	30	0U FULL	NEMA L22-30P	17.3	24	☹ (18)C13, ☹ (6)C19	68.9	2.0	2.1	P24E12M
	30	0U FULL	NEMA L22-30P	17.3	24	☹ (24)C13	68.9	2.0	2.1	P24E13M
	30	0U FULL - Wide	IEC 60309 3P+N+E 6h 30A (IP67)	17.3	36	☹ (24)C13, ☹ (12)C19	68.9	3.3	2.1	P36E01M
	30	0U FULL - Wide	IEC 60309 3P+N+E 6h 30A (IP67)	17.3	36	☹ (30)C13, ☹ (6)C19	68.9	3.3	2.1	P36E03M
	30	0U FULL - Wide	IEC 60309 3P+N+E 6h 30A (IP44)	17.3	36	☹ (24)C13, ☹ (12)C19	68.9	3.3	2.1	P36E04M
	30	0U FULL - Wide	IEC 60309 3P+N+E 6h 30A (IP44)	17.3	36	☹ (30)C13, ☹ (6)C19	68.9	3.3	2.1	P36E05M
	30	0U FULL - Wide	NEMA L22-30P	17.3	36	☹ (24)C13, ☹ (12)C19	68.9	3.3	2.1	P36E02M
	30	0U FULL - Wide	NEMA L22-30P	17.3	36	☹ (30)C13, ☹ (6)C19	68.9	3.3	2.1	P36E06M

(table continues on next page)



## Monitored Switched (MS Series)

	Input Current per phase	Form Factor	Input Plug Type	Apparent Power (kVA)	Outlet Count
415VAC, 3-Phase	30	0U FULL - Wide +	NEMA L22-30P	17.3	48
	30	0U FULL - Wide +	IEC 60309 3P+N+E 6h 30A (IP67)	17.3	48
	30	0U FULL - Wide +	IEC 60309 3P+N+E 6h 30A (IP44)	17.3	48
	30	0U FULL - Wide +	IEC 60309 3P+N+E 6h 30A (IP67)	17.3	48
	30	0U FULL - Wide +	NEMA L22-30P	17.3	48
	30	0U FULL - Wide +	IEC 60309 3P+N+E 6h 30A (IP44)	17.3	48

Outlet Type	Length (inches)	Width (inches)	Depth (inches) at Outlet position	Panduit Part No.
 (48)C13	74.0	3.3	2.1	P48E04M
 (48)C13	74.0	3.3	2.1	P48E03M
 (48)C13	74.0	3.3	2.1	P48E11M
 (42)C13,  (6)C19	74.0	3.3	2.1	P48E05M
 (42)C13,  (6)C19	74.0	3.3	2.1	P48E06M
 (42)C13,  (6)C19	74.0	3.3	2.1	P48E12M

# Monitored Per Outlet (MPO Series)

	Input Current per phase	Form Factor	Input Plug Type	Apparent Power (kVA)	Outlet Count	Outlet Type	Length (inches)	Width (inches)	Depth (inches) at Outlet position	Panduit Part No.
200-240VAC, 1-Phase	30	0U FULL	L6-30P	5.0	24	☺ (20)C13, ☹ (4)C19	68.9	2.0	2.1	P24F01M
	30	0U FULL	L6-30P	5.0	36	☺ (30)C13, ☹ (6)C19	68.9	2.0	2.1	P36F15M
208VAC, 3-Phase	30	0U FULL	L15-30P	8.6	24	☺ (18)C13, ☹ (6)C19	68.9	2.0	2.1	P24F02M
	30	0U FULL	L21-30P	8.6	24	☺ (18)C13, ☹ (6)C19	68.9	2.0	2.1	P24F03M
	30	0U FULL	L15-30P	8.6	36	☺ (30)C13, ☹ (6)C19	68.9	2.0	2.1	P36F16M
	30	0U FULL	L21-30P	8.6	36	☺ (30)C13, ☹ (6)C19	68.9	2.0	2.1	P36F17M
	50	0U FULL	CS8365C	14.4	24	☺ (12)C13, ☹ (12)C19	68.9	2.0	2.1	P24F04M
	50	0U FULL	CS8365C	10.0	36	☺ (30)C13, ☹ (6)C19	68.9	2.0	2.1	P36F18M
	60	0U FULL	IEC 60309 3P+E 9h (IP44)	17.3	24	☺ (12)C13, ☹ (12)C19	68.9	2.0	2.1	P24F05M
415VAC, 3-Phase	30	0U FULL	IEC 60309 3P+N+E 6h 30A (IP67)	17.3	24	☺ (12)C13, ☹ (12)C19	68.9	2.0	2.1	P24F09M
	30	0U FULL	IEC 60309 3P+N+E 6h 30A (IP67)	17.3	24	☺ (18)C13, ☹ (6)C19	68.9	2.0	2.1	P24F11M
	30	0U FULL	IEC 60309 3P+N+E 6h 30A (IP67)	17.3	24	☺ (24)C13	68.9	2.0	2.1	P24F12M
	30	0U FULL	IEC 60309 3P+N+E 6h 30A (IP44)	17.3	24	☺ (12)C13, ☹ (12)C19	68.9	2.0	2.1	P24F13M
	30	0U FULL	IEC 60309 3P+N+E 6h 30A (IP44)	17.3	24	☺ (18)C13, ☹ (6)C19	68.9	2.0	2.1	P24F14M
	30	0U FULL	IEC 60309 3P+N+E 6h 30A (IP44)	17.3	24	☺ (24)C13	68.9	2.0	2.1	P24F15M
	30	0U FULL	NEMA L22-30P	17.3	24	☺ (12)C13, ☹ (12)C19	68.9	2.0	2.1	P24F10M
	30	0U FULL	NEMA L22-30P	17.3	24	☺ (18)C13, ☹ (6)C19	68.9	2.0	2.1	P24F16M
	30	0U FULL	NEMA L22-30P	17.3	24	☺ (24)C13	68.9	2.0	2.1	P24F17M

(table continues on next page)

## Monitored Per Outlet (MPO Series)

	Input Current per phase	Form Factor	Input Plug Type	Apparent Power (kVA)	Outlet Count					
						Outlet Type	Length (inches)	Width (inches)	Depth (inches) at Outlet position	Panduit Part No.
415VAC, 3-Phase	30	0U FULL - Wide	IEC 60309 3P+N+E 6h 30A (IP67)	17.3	48	☹ (24)C13, ☹ (12)C19	68.9	3.3	2.1	P36F01M
	30	0U FULL - Wide	IEC 60309 3P+N+E 6h 30A (IP67)	17.3	48	☹ (30)C13, ☹ (6)C19	68.9	3.3	2.1	P36F03M
	30	0U FULL - Wide	IEC 60309 3P+N+E 6h 30A (IP44)	17.3	48	☹ (24)C13, ☹ (12)C19	68.9	3.3	2.1	P36F04M
	30	0U FULL - Wide	IEC 60309 3P+N+E 6h 30A (IP44)	17.3	48	☹ (30)C13, ☹ (6)C19	68.9	3.3	2.1	P36F05M
	30	0U FULL - Wide	NEMA L22-30P	17.3	48	☹ (24)C13, ☹ (12)C19	68.9	3.3	2.1	P36F02M
	30	0U FULL - Wide	NEMA L22-30P	17.3	48	☹ (30)C13, ☹ (6)C19	68.9	3.3	2.1	P36F06M
	30	0U FULL - Wide +	NEMA L22-30P	17.3	48	☹ (48)C13	74.0	3.3	2.1	P48F04M
	30	0U FULL - Wide +	IEC 60309 3P+N+E 6h 30A (IP67)	17.3	48	☹ (48)C13	74.0	3.3	2.1	P48F03M
	30	0U FULL - Wide +	IEC 60309 3P+N+E 6h 30A (IP44)	17.3	48	☹ (48)C13	74.0	3.3	2.1	P48F11M
	30	0U FULL - Wide +	IEC 60309 3P+N+E 6h 30A (IP67)	17.3	48	☹ (42)C13, ☹ (6)C19	74.0	3.3	2.1	P48F05M
	30	0U FULL - Wide +	NEMA L22-30P	17.3	48	☹ (42)C13, ☹ (6)C19	74.0	3.3	2.1	P48F06M
	30	0U FULL - Wide +	IEC 60309 3P+N+E 6h 30A (IP44)	17.3	48	☹ (42)C13, ☹ (6)C19	74.0	3.3	2.1	P48F12M

# Monitored & Switched Per Outlet (MSPO Series)

	Input Current per phase	Form Factor	Input Plug Type	Apparent Power (kVA)	Outlet Count	Outlet Type	Length (inches)	Width (inches)	Depth (inches) at Outlet position	Panduit Part No.
100-240VAC, 1-Phase	30	0U FULL	L6-30P	5.0	24	☺ (20)C13, ☹ (4)C19	68.9	2.0	2.1	P24G01M
	30	0U FULL	L6-30P	5.0	36	☺ (30)C13, ☹ (6)C19	68.9	2.0	2.1	P36G18M
100-120/200-240VAC, 3-Phase	30	0U FULL	L21-30P	8.6	24	☺ (18)C13, ☹ (6)C19	68.9	2.0	2.1	P24G03M
	30	0U FULL	L21-30P	8.6	36	☺ (30)C13, ☹ (6)C19	68.9	2.0	2.1	P36G19M
208VAC, 3-Phase	30	0U FULL	L15-30P	8.6	24	☺ (18)C13, ☹ (6)C19	68.9	2.0	2.1	P24G02M
	30	0U FULL	L15-30P	8.6	36	☺ (30)C13, ☹ (6)C19	68.9	2.0	2.1	P36G22M
	50	0U FULL	CS8365C	14.4	24	☺ (12)C13, ☹ (12)C19	68.9	2.0	2.1	P24G04M
	50	0U FULL	CS8365C	10.0	36	☺ (30)C13, ☹ (6)C19	68.9	2.0	2.1	P36G20M
	60	0U FULL	IEC 60309 3P+E 9h (IP44)	17.3	24	☺ (12)C13, ☹ (12)C19	68.9	2.0	2.1	P24G05M
415VAC, 3-Phase	30	0U FULL	IEC 60309 3P+N+E 6h 30A (IP67)	17.3	24	☺ (12)C13, ☹ (12)C19	68.9	2.0	2.1	P24G09M
	30	0U FULL	IEC 60309 3P+N+E 6h 30A (IP67)	17.3	24	☺ (18)C13, ☹ (6)C19	68.9	2.0	2.1	P24G13M
	30	0U FULL	IEC 60309 3P+N+E 6h 30A (IP67)	17.3	24	☺ (24)C13	68.9	2.0	2.1	P24G14M
	30	0U FULL	IEC 60309 3P+N+E 6h 30A (IP44)	17.3	24	☺ (12)C13, ☹ (12)C19	68.9	2.0	2.1	P24G15M
	30	0U FULL	IEC 60309 3P+N+E 6h 30A (IP44)	17.3	24	☺ (18)C13, ☹ (6)C19	68.9	2.0	2.1	P24G16M
	30	0U FULL	IEC 60309 3P+N+E 6h 30A (IP44)	17.3	24	☺ (24)C13	68.9	2.0	2.1	P24G17M
	30	0U FULL	NEMA L22-30P	17.3	24	☺ (12)C13, ☹ (12)C19	68.9	2.0	2.1	P24G10M
	30	0U FULL	NEMA L22-30P	17.3	24	☺ (18)C13, ☹ (6)C19	68.9	2.0	2.1	P24G18M
	30	0U FULL	NEMA L22-30P	17.3	24	☺ (24)C13	68.9	2.0	2.1	P24G19M

(table continues on next page)

# Monitored & Switched Per Outlet (MSPO Series)

	Input Current per phase	Form Factor	Input Plug Type	Apparent Power (kVA)	Outlet Count
415VAC, 3-Phase	30	0U FULL - Wide	IEC 60309 3P+N+E 6h 30A (IP67)	17.3	36
	30	0U FULL - Wide	IEC 60309 3P+N+E 6h 30A (IP67)	17.3	36
	30	0U FULL - Wide	IEC 60309 3P+N+E 6h 30A (IP44)	17.3	36
	30	0U FULL - Wide	IEC 60309 3P+N+E 6h 30A (IP44)	17.3	36
	30	0U FULL - Wide	NEMA L22-30P	17.3	36
	30	0U FULL - Wide	NEMA L22-30P	17.3	36
	30	0U FULL - Wide +	IEC 60309 3P+N+E 6h 30A (IP67)	17.3	48
	30	0U FULL - Wide +	NEMA L22-30P	17.3	48
	30	0U FULL - Wide +	IEC 60309 3P+N+E 6h 30A (IP44)	17.3	48
	30	0U FULL - Wide +	IEC 60309 3P+N+E 6h 30A (IP67)	17.3	48
	30	0U FULL - Wide +	NEMA L22-30P	17.3	48
	30	0U FULL - Wide +	IEC 60309 3P+N+E 6h 30A (IP44)	17.3	48

Outlet Type	Length (inches)	Width (inches)	Depth (inches) at Outlet position	Panduit Part No.
☺ (24)C13, ☹ (12)C19	68.9	3.3	2.1	P36G01M
☺ (30)C13, ☹ (6)C19	68.9	3.3	2.1	P36G03M
☺ (24)C13, ☹ (12)C19	68.9	3.3	2.1	P36G04M
☺ (30)C13, ☹ (6)C19	68.9	3.3	2.1	P36G05M
☺ (24)C13, ☹ (12)C19	68.9	3.3	2.1	P36G02M
☺ (30)C13, ☹ (6)C19	68.9	3.3	2.1	P36G06M
☺ (48)C13	74.0	3.3	2.1	P48G03M
☺ (48)C13	74.0	3.3	2.1	P48G04M
☺ (48)C13	74.0	3.3	2.1	P48G12M
☺ (42)C13, ☹ (6)C19	74.0	3.3	2.1	P48G05M
☺ (42)C13, ☹ (6)C19	74.0	3.3	2.1	P48G06M
☺ (42)C13, ☹ (6)C19	74.0	3.3	2.1	P48G13M

# Basic PDU

	Input Current per phase	Form Factor	Input Plug Type	Apparent Power (kVA)	Outlet Count	Outlet Type	Length (inches)	Width (inches)	Depth (inches)	Panduit Part No.
									at Outlet position	
100-240VAC, 1-Phase	15	1U	NEMA 5-15P	1.4	12	☹ (12)5-20R	1.6	17.5	2.0	P12B01M
	20	1U	NEMA 5-20P	1.9	12	☹ (12)5-20R	1.6	17.5	2.0	P12B19M
	20	1U	NEMA L5-20P	1.9	12	☹ (12)5-20R	1.6	17.5	2.0	P12B30M
	20	1U	NEMA L6-20P	3.3	12	☹ (12)C13	1.6	17.5	2.0	P12B46M
	30	1U	NEMA L6-30P	5.0	12	☹ (12)C13	1.7	17.5	7.8	P12B47M
	50	1U	CS8265C	8.3	6	☹ (6)C19	1.7	17.5	7.8	P06B48M
	30	2U	NEMA L5-30P	2.9	16	☹ (16)5-20R	3.4	17.5	7.8	P16B41M
	15	0U HALF	NEMA 5-15P	1.4	16	☹ (16)5-20R	32.2	2.0	2.1	P16B04M
	20	0U HALF	NEMA 5-20P	1.9	16	☹ (16)5-20R	32.2	2.0	2.1	P16B07M
	20	0U HALF	NEMA L5-20P	1.9	16	☹ (16)5-20R	32.2	2.0	2.1	P16B08M
	20	0U HALF	NEMA L5-20P	1.9	22	☹ (20)C13, ☹ (2)C19	32.2	2.0	2.1	P22B05M
	20	0U HALF	NEMA L6-20P	3.3	22	☹ (20)C13, ☹ (2)C19	32.2	2.0	2.1	P22B10M
	30	0U HALF	NEMA L5-30P	2.9	22	☹ (22)5-20R	32.2	2.0	2.1	P22B09M
	30	0U HALF	NEMA L6-30P	5.0	20	☹ (20)C13	32.2	2.0	2.1	P20B16M
	30	0U MID	NEMA L6-30P	5.0	24	☹ (20)C13, ☹ (4)C19	58.7	2.0	2.1	P24B15M
	30	0U MID	NEMA L6-30P	5.0	42	☹ (36)C13, ☹ (6)C19	58.7	2.0	2.1	P42B17M
	50	0U MID	CS8265C	8.3	36	☹ (30)C13, ☹ (6)C19	58.7	2.0	2.1	P36B18M
	50	0U MID	50A Hardwire	8.3	36	☹ (30)C13, ☹ (6)C19	58.7	2.0	2.1	P36B20M
208VAC, 3-Phase	30	1U	NEMA L15-30P	8.6	6	☹ (6)C19	1.7	17.5	7.8	P06B49M
	30	1U	NEMA L21-30P	8.6	6	☹ (6)C19	1.7	17.5	7.8	P06B50M
	50	1U	CS8365C	14.4	6	☹ (6)C19	1.7	17.5	7.8	P06B02M
	30	1U	IEC 60309 3P+E 9h 60A (IP44)	17.3	6	☹ (6)C19	1.7	17.5	7.8	P06B03M
	50	0U HALF	NEMA L15-30P	8.6	18	☹ (18)C13	32.2	2.0	2.1	P18B21M
	60	0U HALF	NEMA L21-30P	8.6	18	☹ (18)C13	32.2	2.0	2.1	P18B24M
	30	0U MID	NEMA L15-30P	8.6	36	☹ (30)C13, ☹ (6)C19	58.7	2.0	2.1	P36B22M
	30	0U MID	NEMA L21-30P	8.6	30	☹ (24)C13, ☹ (3)C19, ☹ (3)5-20R	58.7	2.0	2.1	P30B25M
	30	0U MID	NEMA L21-30P	8.6	36	☹ (30)C13, ☹ (6)C19	58.7	2.0	2.1	P36B26M
	30	0U FULL	NEMA L15-30P	8.6	42	☹ (36)C13, ☹ (6)C19	68.9	2.0	2.1	P42B23M
	30	0U FULL	NEMA L21-30P	8.6	42	☹ (36)C13, ☹ (6)C19	68.9	2.0	2.1	P42B27M
	50	0U FULL	CS8365C	10.0	42	☹ (36)C13, ☹ (6)C19	68.9	2.0	2.1	P42B28M
60	0U FULL	IEC 60309 3P+E 9h 60A (IP44)	17.3	24	☹ (12)C13, ☹ (12)C19	68.9	2.0	2.1	P24B14M	

# Basic PDU


	Input Current per phase	Form Factor	Input Plug Type	Apparent Power (kVA)	Outlet Count	Outlet Type	Length (mm)	Width (mm)	Depth (mm) at Outlet position	Panduit Part No.
230VAC, 1-Phase	16	1U	IEC 60309 2P+E 6h 16A (IP44)	3.7	12	☺ (12)C13	41.5	443.5	49.9	P12B34M
	32	1U	IEC 60309 2P+E 6h 32A (IP44)	7.4	6	☺ (6)C19	43.5	443.5	197.4	P06B35M
	32	1U	IEC 60309 2P+E 6h 32A (IP44)	7.4	12	☺ (12)C13	43.5	443.5	197.4	P12B36M
	16	0U HALF	IEC 60309 2P+E 6h 16A (IP44)	3.7	22	☺ (20)C13, ☹ (2)C19	817.0	52.0	53.0	P22B39M
	32	0U HALF	IEC 60309 2P+E 6h 32A (IP44)	7.4	20	☺ (20)C13	817.0	52.0	53.0	P20B40M
	32	0U MID	IEC 60309 2P+E 6h 32A (IP44)	7.4	30	☺ (24)C13, ☹ (6)C19	1490.0	52.0	53.0	P30B06M
	32	0U MID	IEC 60309 2P+E 6h 32A (IP44)	7.4	42	☺ (36)C13, ☹ (6)C19	1490.0	52.0	53.0	P42B42M
	48	0U MID	IEC 60309 2P+E 6h 63A (IP44)	11.0	36	☺ (30)C13, ☹ (6)C19	1490.0	52.0	53.0	P36B43M
230/400VAC, 3-Phase	16	1U	IEC 60309 3P+N+E 6h 16A (IP44)	11.0	6	☺ (6)C19	41.5	443.5	49.9	P06B37M
	32	1U	IEC 60309 3P+N+E 6h 32A (IP44)	22.0	6	☺ (6)C19	43.5	443.5	197.4	P06B38M
	16	0U MID	IEC 60309 3P+N+E 6h 16A (IP44)	11.0	42	☺ (36)C13, ☹ (6)C19	1490.0	52.0	53.0	P42B44M
	16	0U MID	IEC 60309 3P+N+E 6h 16A (IP44)	11.0	30	☺ (24)13, ☹ (6)C19	1490.0	52.0	53.0	P30B13M
	32	0U FULL	IEC 60309 3P+N+E 6h 32A (IP44)	22.0	24	☺ (12)C13, ☹ (12)C19	1750.0	52.0	53.0	P24B12M
	32	0U FULL	IEC 60309 3P+N+E 6h 32A (IP44)	22.0	42	☺ (30)C13, ☹ (12)C19	1750.0	55.0	53.0	P42B11M

# Accessories

## Security & Environmental Accessories that connect directly to the G5 iPDU.


Note: A maximum of 8 sensors can be managed by the Panduit® SmartZone™ G5 PDU controller. See User Manual for Complete Details.

Description	Dimensions L x W x H (in.)	Length (ft.)	Panduit Part No.
Temperature Sensor	1.73 x 0.83 x 0.43	6.56	EA001
Temperature + Humidity Sensor	1.73 x 0.83 x 0.43	6.56	EB001
3 Temperature + Humidity Sensor	1.73 x 0.83 x 0.43	6.56	EC001
Water - Rope	2.36 x 2.36 x 0.87	6.56	ED001
Water - Spot	2.36 x 2.36 x 0.87	16.40	EE001
3 Sensor Hub	3.35 x 1.26 x 1.06	n/a	EF001
Water - Rope extension	n/a	6.56	EG001
Door Switch (magnetic 2 piece)	1.73 x 0.83 x 0.43 (1.14 x 0.67 x 0.28 for magnet)	3.28	ACA01
Dry Contact Input	1.73 x 0.83 x 0.43	9.84	ACC01
USB Light Strip	15 x 1 x 0.5	5.0	ACD01



## SmartZone™ Security Handle & Accessories that attach to the handle.

Description	Dimensions L x W x H (in.)	Length (ft.)	Panduit Part No.
SmartZone™ Security Handle with Humidity Sensor and Card Reader	n/a	n/a	ACF05
SmartZone™ Security Handle with Humidity Sensor and Card Reader + Keypad	n/a	n/a	ACF06
SmartZone™ Handle T + Door Sensor	n/a	7.64	ACF10
SmartZone™ Handle 3T + Door Sensor	n/a	9.84	ACF11
SmartZone™ Handle to iPDU Harness	n/a	9.12	ACF20







## Dual Locking Power Cords

(UL, CE, VDE, TUV Approved)


Color	Description	Ratings	Gauge / Cross Section Area	Jacket	Connector Angle	Length (ft.)	Panduit Part No. (10 pk)
Red	IEC C14 to IEC C13	10A / 250V	17 AWG / 1.0mm <sup>2</sup>	SJT / H05VV-F	Straight	2	LPCA01X
Red	IEC C14 to IEC C13	10A / 250V	17 AWG / 1.0mm <sup>2</sup>	SJT / H05VV-F	Straight	3	LPCA02X
Red	IEC C14 to IEC C13	10A / 250V	17 AWG / 1.0mm <sup>2</sup>	SJT / H05VV-F	Straight	4	LPCA03X
Red	IEC C14 to IEC C13	10A / 250V	17 AWG / 1.0mm <sup>2</sup>	SJT / H05VV-F	Straight	6	LPCA04X
Blue	IEC C14 to IEC C13	10A / 250V	17 AWG / 1.0mm <sup>2</sup>	SJT / H05VV-F	Straight	2	LPCA06X
Blue	IEC C14 to IEC C13	10A / 250V	17 AWG / 1.0mm <sup>2</sup>	SJT / H05VV-F	Straight	3	LPCA07X
Blue	IEC C14 to IEC C13	10A / 250V	17 AWG / 1.0mm <sup>2</sup>	SJT / H05VV-F	Straight	4	LPCA08X
Blue	IEC C14 to IEC C13	10A / 250V	17 AWG / 1.0mm <sup>2</sup>	SJT / H05VV-F	Straight	6	LPCA09X
Black	IEC C14 to IEC C13	10A / 250V	17 AWG / 1.0mm <sup>2</sup>	SJT / H05VV-F	Straight	2	LPCA11X
Black	IEC C14 to IEC C13	10A / 250V	17 AWG / 1.0mm <sup>2</sup>	SJT / H05VV-F	Straight	3	LPCA12X
Black	IEC C14 to IEC C13	10A / 250V	17 AWG / 1.0mm <sup>2</sup>	SJT / H05VV-F	Straight	4	LPCA13X
Black	IEC C14 to IEC C13	10A / 250V	17 AWG / 1.0mm <sup>2</sup>	SJT / H05VV-F	Straight	6	LPCA14X




**C14**




**C13**







**C14**




**C13**






**C14**



**C13**




# Accessories


## Dual Locking Power Cords

(UL, CE, VDE, TUV Approved)


Color	Description	Ratings	Gauge / Cross Section Area	Jacket	Connector Angle	Length (ft.)	Panduit Part No. (10 pk)
Red	IEC C20 to IEC C19	16A / 250V	15 AWG / 1.5mm <sup>2</sup>	SJT / H05VV-F	Straight	2	LPCB01X
Red	IEC C20 to IEC C19	16A / 250V	15 AWG / 1.5mm <sup>2</sup>	SJT / H05VV-F	Straight	3	LPCB02X
Red	IEC C20 to IEC C19	16A / 250V	15 AWG / 1.5mm <sup>2</sup>	SJT / H05VV-F	Straight	4	LPCB03X
Red	IEC C20 to IEC C19	16A / 250V	15 AWG / 1.5mm <sup>2</sup>	SJT / H05VV-F	Straight	6	LPCB04X
Blue	IEC C20 to IEC C19	16A / 250V	15 AWG / 1.5mm <sup>2</sup>	SJT / H05VV-F	Straight	2	LPCB06X
Blue	IEC C20 to IEC C19	16A / 250V	15 AWG / 1.5mm <sup>2</sup>	SJT / H05VV-F	Straight	3	LPCB07X
Blue	IEC C20 to IEC C19	16A / 250V	15AWG / 1.5mm <sup>2</sup>	SJT / H05VV-F	Straight	4	LPCB08X
Blue	IEC C20 to IEC C19	16A / 250V	15 AWG / 1.5mm <sup>2</sup>	SJT / H05VV-F	Straight	6	LPCB09X
Black	IEC C20 to IEC C19	16A / 250V	15 AWG / 1.5mm <sup>2</sup>	SJT / H05VV-F	Straight	2	LPCB11X
Black	IEC C20 to IEC C19	16A / 250V	15 AWG / 1.5mm <sup>2</sup>	SJT / H05VV-F	Straight	3	LPCB12X
Black	IEC C20 to IEC C19	16A / 250V	15 AWG / 1.5mm <sup>2</sup>	SJT / H05VV-F	Straight	4	LPCB13X
Black	IEC C20 to IEC C19	16A / 250V	15 AWG / 1.5mm <sup>2</sup>	SJT / H05VV-F	Straight	6	LPCB14X




IEC C20




IEC C19







IEC C20




IEC C19






IEC C20



IEC C19



Complete Warranty & Compliance information can be found at [www.panduit.com](http://www.panduit.com)  
Customer Service: [cs@panduit.com](mailto:cs@panduit.com) or 800.777.3300  
Technical Support: [techsupport@panduit.com](mailto:techsupport@panduit.com) or 866.405.6654

**PANDUIT**<sup>®</sup>

©2021 Panduit Corp. ALL RIGHTS RESERVED.  
Replaces PUCB20 **PUCB23--SA-ENG** 2/2021