


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PART NUMBER	MATERIAL	"A" HEIGHT +/- .062	IMPRINT AREA "B" +/- .062	VERTICAL REPEAT "C" +/- .062	LABELS PER ROW	STANDARD PKG. QTY.
S200X150VATY	GMV17 OR GMV18	1.50 [12.7]	0.50 [12.7]	1.75 [44.5]	2	5000
S200X225VATY	GMV17 OR GMV18	2.25 [57.2]	0.75 [19.1]	2.50 [63.5]		1000
S200X250VATY	GMV17 OR GMV18	2.50 [63.5]	1.00 [25.4]	2.75 [69.8]		
S200X400VATY	GMV17 OR GMV18	4.00 [101.6]	1.00 [25.4]	4.25 [108.0]		
S200X650VATY	GMV17 OR GMV18	6.50 [165.1]	1.50 [38.1] +/- .10	6.75 [171.5]		

IMPRINT AREA



NOTES:

1. MILLIMETERS ARE IN [].

TITLE		OPTIMUM SELF-LAM. S200X***VATY THERMAL TRANSFER PRINTABLE LABELS	
CUSTOMER DRAWING			
ITEM REVISION NAME		I00472BY/11	
DATASET FILE NAME		I00472BY_DC/11B C10468 CUST DWG	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.x ± .12 [3.05] .xxx ± .025 [.635]		SEE TABLE	
.xx ± .062 [1.57] ANGLES ±		DRAWING NUMBER:	
THIRD ANGLE PROJECTION		C10468	
DRAWN BY	DATE	CHK	SCALE
RVU	9/1/06	MSAD	NTS
SHT 1 OF 1		A	