

1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT. 2. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF ROHS (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE ROHS TECHNICAL ADAPTATION COMMITEE. 3. /ST PUMP KIT INCLUDES: BATTERY OPERATED PUMP CARRYING STRAP REMOTE PENDANT SWITCH - 18V MAKITA BATTERIES (QTY-2) (/ST ONLY) 120V BATTERY MAKITA CHARGER (QTY-1) (/ST ONLY - MANUALS 4. /TO PUMP ONLY INCLUDES: BATTERY OPERATED PUMP CARRYING STRAP REMOTE PENDANT SWITCH - MANUALS **GENERAL NOTES:** 1. PUMP OUTPUT IS 10,000 PSI. 2. PUMP WT. W/O BATTÉRY IS 12.1 POUNDS [5.5 Kg]. 3. DIMENSIONS (W/O BATTERY): LENGTH: 14.0" (356mm) WIDTH: 6.5" (165mm) HEIGHT: 11.5" (292mm) 4. PUMP ACCEPTS MAKITA BL-18XX SERIES LI-ION/LXT BATTERIES. (4 A-Hr OR GREATER RECOMMENDED) PUMP HOUSING HAS A LOW BATTERY LIGHT INDICATOR. 6. PUMP HOUSING HAS (2) STEEL RINGS FOR SHOULDER STRAP. PUMP IS CE AND ROHS COMPLIANT. QUALITY CERTIFICATES ARE AVAILABLE UPON REQUEST. PUMP IS SAFETY COMPLIANT AND MEETS OSHA SAFETY STANDARDS. DIMENSIONS ARE FOR REFERENCE ONLY. 10. THIS CUSTOMER DRAWING IS FOR US/NA. ACCESSORIES AVAILABLE: A. CHARGERS (120V, 230V AND 12VDC) - CT-CHRMK120V (MAKITA DC18RC) - 120V AC CT-CHRMK230VINT (MAKITA DC18RC-X230) -230V AC WITH EURO PLUG CT-CHRMK12VDC (MAKITA DC18SE) 12VDC B. BATTERIES (MAKITA BL-18XX SERIES) CT-LIBCMK3AH, BL-1830 (3 A-Hr) CT-LIBCMK4AH, BL-1840 (4 A-Hr) 4 A-Hr OR HIGHER RECOMMENDED D. CT-2902RFS REMOTE FOOT SWITCH E. CT-2902RPS REMOTE PENDANT SWITCH CT-900HPH HYDRAULIC HOSE ASSEMBLY (3M) ANY 10K PSI CRIMP HEADS AND CUT, CRIMP, PUNCH HEADS (/CCP) CT-2902BPHP/ST & CT-2902BPHP/T0 CD, CT-2902BPHP SERIES, BO PUMP, 10K PSI CUSTOMER DRAWING TEM REVISION NAM R29180BA/02 ATASET FILE NAME PANDUIT R29180BA/02 THIRD ANGLE PROJECTION TP29180B01 AS NOTED В BJPU TCAV SHEET 1 OF 1 10-10-18 NONE