

Identification Solutions for Harsh Environments

Minimize downtime, installation time, and waste while reducing Mean Time To Repair (MTTR).

Properly identifying products, premises, and infrastructure can significantly reduce the time to troubleshoot and repair. Without identifying components, wires/cables, etc., troubleshooting becomes a lengthy process of tracing and identifying the specific source of a problem. Conversely, by having components and wires/cables clearly identified, technicians can quickly go to the source of the problem. In certain cases, a properly identified infrastructure can save hours of troubleshooting time - which can translate into millions of dollars for critical applications. This guide provides an overview of Panduit identification solutions and how these products enhance performance and productivity in harsh environments.

Introduction

Using this Guide2-3	
Applications	
Key Selection Criteria	
Legibility7	
Adhesive Holding Power	
Temperature Resistance7	
Chemical Resistance	
Outdoor Durability	
Fire Safety Properties10	
Product Selection Guides	
Heat Shrink Labels]
Self-Laminating Labels	
Marker Plates	
Raised Panel Labels12	
Safety Identification	ļ
Permanent Identification	
Mobile and Desktop Printers	
Identification Software	
Industry Compliance	
Compliance with Industry Standards	



Industrial

Oil Rigs

Refineries

Chemical Plants

Natural Gas

Processing Plants

LNG Plants

Water Treatment

Facilities

Wind Farms

Solar

Nuclear

Mining

Ships

Submarines

Cell Towers

Telecommunications

Transportation

OEM

INTRODUCTION

Using this Guide

Applications

This section includes product recommendations for typical applications; always verify product suitability based on specific requirements and key selection criteria.



Key Selection Criteria

Utilize material and attribute charts to help select the Panduit products required to deliver superior performance in specific applications Select the appropriate printers and tools to reduce time required and to take advantage of our lowest installed cost solutions Consider Panduit permanent identification solutions to help provide legibility in harsh environments; the complete solution includes marker plates, tags, and ties and is available for use with on-site custom marking tools or through our factory custom marking service

Selection Guides

Organized by part number, use each chart to assist with your product selection



Reliable material/adhesive systems:

Appropriate for specific applications and environments at lowest installed cost

Less waste:

Panduit printers are designed to lower label material waste by as much as 65%

Ease of use to minimize printing time:

With Panduit identification solutions, the time required for labeling can be reduced by up to 75%

Minimized installation time:

Delivers pre-cut labels, partial cut labels and ease of wire insertion to speed installation time





OUTPUT:001

Heat Shrink Labels

Panduit heat shrink labels, available in multiple colors, grades, and sizes, for single or double-sided printing, offer a durable wire and cable identification solution for harsh environments with patented, time-saving features.

Raised Panel Labels

Panduit raised panel labels are designed for 20 years of outdoor exposure, tested for use in solar applications, and compliant with print-performance requirements of UL969 and MIL-STD-202G. The labels are compliant with IP69K for washdown applications and provide a rugged and professional appearance similar to engraved plates without the lengthy lead times or expensive engraving equipment.

This bland produce is the second of the seco







Safety Identification

Panduit safety identification products are available in a wide selection of printing methods and materials. They are also available in a broad selection of colors, sizes, and legends to effectively communicate safety messages.

Permanent Identification

Panduit offers one of the widest ranges of permanent identification solutions in the industry. This solution includes stainless steel cable ties, marker plates, tags, and onsite marking tools for quick and easy identification in the field.

EDENT 12-E

Mobile and Desktop Printers

The MP300 and MP200 mobile printers for remote and mobile labeling in harsh environments are ideal for printing labels on a job site. The versatile TDP43ME, TDP43HE, and TDP46HE thermal transfer desktop printers allow printing up to eight inches per second with professional 300 dpi or 600 dpi resolution of labels and tapes up to four inches wide. The compact design provides mobility and is easily deployable, with minimum setup or calibration time and minimum label waste.

Identification Software

Easy-Mark Plus™ Labeling Software helps create industry-compliant labels for harsh environments and saves up to 75% of the time required to generate labels for the energy infrastructure. Labeling Software saves up to 75% of the time required to generate labels for the industrial applications by utilizing identifiers previously created in CAD files to eliminate manual entry of data into labeling software.





The information contained herein is intended as a guide for use by persons having technical skill. Suitability of the Panduit product for intended use should be determined. User assumes all risk and liability whatsoever in connection with such use.

Applications

Panduit offers a wide variety of identification systems to meet your specific application requirements. Common applications include:

Wire and Cable Labeling

Description: Products encounter some of the harshest environments such as high temperature, frigid cold, salt water, sand, radiation, and chemical corrosion. Selection of the right material of construction is a key design criterion.

Oil & Gas, Power Generation, Industrial

Selection Criteria: Low-smoke emissions; resistance to chemical corrosion, high temperatures, ultra-violet light, flame, and high radiation

Product Recommendations:

- Marker Plates
- Tedlar Self-Laminating Labels
- Heat Shrink Labels
- Marker Plates

Rail Car Undercarriage, Industrial

Selection Criteria: Resistance to extreme solvents, oils, and chemicals

Product Recommendations:

• Stainless Steel Marker Plates (embossed)

Shipbuilding, Rail Car Controls

Selection Criteria: Excellent fire safety properties, minimal smoke emissions

Product Recommendations:

- Halogen-Free Heat Shrink Labels
- Halogen-Free Marker Plates
- 316 Stainless Steel Marker Plates (embossed)

Harsh Environments

Selection Criteria: Flame retardant, extreme temperatures; rated for harsh environments

Product Recommendations:

- Heat Shrink Labels
- High-Temperature, Flame-Retardant Marker Plates











Cable Tray Identification

Description: The design requirements for this application are very similar to cable and wire identification applications. In addition, the products are often in remote locations.

Oil Rigs, Shipbuilding, Industrial

Selection Criteria: Ultra-aggressive adhesive, resistance to extreme temperatures and tears

Product Recommendations:

- Super-Tack Continuous Tapes
- Raised Panel Labels



Pipe Identification

Description: This application is critical for ensuring personnel and equipment safety. During emergencies or plant turn-arounds, it becomes necessary to isolate sections of pipelines to prevent hazardous or explosive materials from becoming exposed.

Refineries, Chemical Plants, **Waste Water Treatment**

Selection Criteria: Flexible material; wide variety of color-coding options; resistance to chemical corrosion, ultra-violet light

Product Recommendations:

- Continuous Tapes (Vinyl)
- Stainless Steel Marker Plates and Tags
- Rigid Strap on Pipe Markers

Control Panel Identification

Description: Control systems are critical to almost all industrial segments, and control panels are an essential component of these systems. Increasingly, control panels are network-enabled and play a lead role in maximizing network uptime. In order to reduce MTTR, the design of the panel should enable quick fault finding.

Indoor - Terminal Blocks, Ratings Plates, Relays, PLCs

Selection Criteria: Extreme temperatures, tear resistance, ultra-aggressive adhesive

Product Recommendations:

- Super-Tack Continuous Tapes
- Super-Tack Component Labels
- Raised Panel Labels
- Heat Shrink Labels







Control Panel Identification (continued)

Outdoor – Natural Gas Hydraulic Fracturing, Pumping Stations

Selection Criteria: Extreme UV resistance; strong holding power for rough, textured, and powder-coated surfaces

Product Recommendations:

- Raised Panel Labels
- Stainless Steel Marker Plates and Tags



Solar Photovoltaic System Labeling

Description: This labeling system is designed to meet required safety standards for PV installation labeling. All labels are designed to have extreme UV resistance for outdoor application and strong holding power for rough, textured, and powder-coated surfaces.

Enclosures, Disconnects, Junction Boxes:

Selection Criteria: Extreme UV resistance; strong holding power for rough, textured, and powder-coated surfaces

Product Recommendations:

- Polyester Labels and Over-laminates
- Raised Panel Labels



Safety Identification

Description: Panduit safety identification solutions are reliable for the protection of personnel from potential hazards. This includes creating a visual workplace to ensure that hazards are properly recognized and identified. It is also important to identify energy in a workplace (electrical, chemical, pneumatic, mechanical, hydraulic, kinetic, and others) with Lockout/Tagout devices, as well as facility signage and equipment labeling.

Offshore Platforms, Refineries, Petrochemical, Wind & Solar Farms:

Selection Criteria: Labels and signs suitable for industrial environments with OSHA and ANSI compliant layouts and colors to communicate safety messages.

Product Recommendations:

- Adhesive Polyester Signs and Labels
- Rigid Polyethylene Signs
- 316 Stainless Steel Marker Plates


KEY SELECTION CRITERIA

Legibility

Identification is permanent immediately after printing and remains legible even when exposed to weather, chemicals, and abrasion. Contrasting text and background colors enhance the readability of legends in all lighting conditions.


Adhesive Holding Power

Strong, permanent adhesives ensure that vital identification stays affixed to industrial surfaces. Special adhesive formulations provide strong grip and long-lasting performance in harsh applications.



Temperature Resistance

Identification products are engineered to perform in a wide range of temperature extremes. Materials and adhesives meet demanding conditions from freezing Arctic temperatures to intense desert heat.






Chemical Resistance

The harshest environments often expose critical identification labels and markers to chemical, fluids, and oils. Panduit materials, such as fluid-resistant heat shrink, are tested to the highest industry standards against some of the most extreme chemicals. Through this exhaustive research, Panduit products are the preferred solutions to meet AMS-DTL-23053/6 Class 1 and NF F00-608 Class A & H, SAE-AS5942, MIL-STD-883F Method 2015.13, Solutions A and D, and MIL-STD-202G Method 215K, Solutions A, and D. These standards are particularly important for certain industries such as rail transit, aerospace, and industrial construction.

															/ /	/ /	
					The state of the s	, J.X.	The see that the s		KR311			September 19 Contract		A.KII M	A CHECK	The state of the s	/ Jul
			THE TOTAL STATE OF THE STATE OF		ZMAT!	Se Com		285 S	/ \$\ /	/	/ /	A CONTRACT C	Tage /	TO SEN MAN TO THE PROPERTY OF	NE SPES		oligies (
		/	D. A.	Tour	S, Will C.	, Hai	, Fluid	als Chil	Sold in the second seco	Sur Sur Sur Sur	CMION	ziel jadi	Leit 13D	100°	Signs	at a market	
		Olgies S	o vice		Se. Y.S.	\$6. \\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\	be. Sales	ad Jin	Jing	, Pilo	100 PG	No. COUR	50, July 118	Hotry	Ser Pi	indialec	
GROUP	Maj	Toy No	18 18 18 18 18 18 18 18 18 18 18 18 18 1	isu. Ye	regui.	Su. Sign	, o o	Zar. Sar	, ari	'Sur.	\$ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \	ester /	riinu ^U çiç	90	Jab Custom		
Acids	0		0	0	0	0	0	0	0								
Alcohols		-				0						0					
Bases		-	0	0	0	0	0	0	0								
Cleaner/Degreaser										0	0	0					
Detergents																	
Fuels	0				0					0		0		0			
Hydraulic Fluids					-	-				0	0	0		0			
Oils																	
Organic Solvents		-	-		0	0				-	0	-		-	$\overline{\bigcirc}$		
Salt Solutions		0	0	0	-	0	0	0	0	0	0	0		0	0		
Water		0	0	0	0	0	0	0	0	0	0	0	0	0	0		
= Lowest recommend	ation 👄	= Accep	table wit	h some o	hemicals	= Hi	ighest red	commend	dation								

Outdoor Durability

A reliable labeling solution for outdoor use is vital to customers in industries such as solar energy and utilities. Standard label materials are not designed to withstand the extreme exposure to UV light, moisture, and temperature fluctuations of an outdoor application. Panduit has many years of experience in designing, testing, and manufacturing labels and markers with special properties specifically for outdoor use. For example, Panduit raised panel labels are designed to last through 20 years of outdoor exposure and are verified and tested for weather resistance and for use in demanding solar applications. Panduit also provides over-laminate materials to extend the life of printed labels outdoors.



Fire Safety Properties

In some applications, fire safety is a critical concern. For these environments, identification labels and markers with low-smoke emissions and no halogens are required. Panduit Halogen-Free, Heat Shrink Labels meet the strict requirements of BS6853; 1999 Vehicle Category 1a for burning behavior and toxic gas emissions. Additionally, Panduit flame-retardant, halogen-free marker plates meet UL Standard 224 with a VW-1 rating for flammability and AMS-DTL-23053/5C (Class 1 and Class 3). These properties are particularly important to industries such as rail transit, shipbuilding, and industrial construction.

PRODUCT SELECTION GUIDES

Heat Shrink Labels





	Wie	dth	Hei	ght		Cable D.	Max.	Labels Per	
Part Number	ln.	mm	ln.	mm	ln.	mm	ln.	mm	Roll
H100X025H1T	1.00	25.4	0.05	6.4	0.04	1.0	0.10	2.2	1000
H200X025H1T	2.00	50.8	0.25	6.4	0.04	1.0	0.13	3.3	500
H100X034H1T	1.00	25.4	0.24	0.6	0.06	4.5	0.10	4.0	1000
H200X034H1T	2.00	50.8	0.34	8.6	0.06	1.5	0.19	4.8	500
H100X044H1T	1.00	25.4	0.44	11.2	0.00	2.0	0.05	6.4	1000
H200X044H1T	2.00	50.8	0.44	11.2	0.08	2.0	0.25	6.4	500
H100X064H1T	1.00	25.4	0.04	10.0	0.10	0.0	0.00	0.7	1000
H200X064H1T	2.00	50.8	0.64	16.3	0.13	3.3	0.38	9.7	500
H100X084H1T	1.00	25.4	0.04	01.0	0.17	4.0	0.50	10.7	1000
H200X084H1T	2.00	50.8	0.84	21.3	0.17	4.3	0.50	12.7	500
H100X165H1T	1.00	25.4	1.65	41.0	0.22	0.4	1.00	25.4	500
H200X165H1T	2.00	50.8	1.65	41.9	0.33	8.4	1.00	25.4	250

Additional sizes and colors available on www.panduit.com.

Two-Sided Military Grade Heat Shrink Labels



	Wie	dth	Height		Min. 0	Cable D.	Max. O.	Labels Per	
Part Number	ln.	mm	ln.	mm	In.	mm	ln.	mm	Roll
H100X025H1T-2	1.00	25.4	0.25	6.4	0.04	1.0	0.13	3.3	1000
H200X025H1T-2	2.00	50.8	0.23	0.4	0.04	1.0	0.13	3.3	500
H100X034H1T-2	1.00	25.4	0.34	8.6	0.06	1.5	0.19	4.8	1000
H200X034H1T-2	2.00	50.8	0.34	0.0	0.06	1.5	0.19	4.0	500
H100X044H1T-2	1.00	25.4	0.44	11.2	0.08	2.0	0.25	6.4	1000
H200X044H1T-2	2.00	50.8	0.44	11.2	0.08	2.0	0.25	0.4	500
H100X064H1T-2	1.00	25.4	0.64	16.3	0.13	3.3	0.38	9.7	1000
H200X064H1T-2	2.00	50.8	0.64	10.3	0.13	3.3	0.36	9.7	500
H100X084H1T-2	1.00	25.4	0.84	21.3	0.17	4.3	0.50	12.7	1000
H200X084H1T-2	2.00	50.8	0.64	21.3	0.17	4.3	0.50	12.7	500
H100X122H1T-2	1.00	25.4	1.00	21.0	0.05	6.0	0.75	10.0	500
H200X122H1T-2	2.00	50.8	1.22	31.0	0.25	6.3	0.75	19.0	250
H100X165H1T-2	1.00	25.4	1.65	41.0	0.22	0.4	1.00	05.4	500
H200X165H1T-2	2.00	50.8	1.65	41.9	0.33	8.4	1.00	25.4	250

Additional sizes and colors available on www.panduit.com.

Halogen-Free Two-Sided Heat Shrink Labels

	Width		Hei	Height		Cable D.	Max. O.	Labels Per	
Part Number	ln.	mm	ln.	mm	In.	mm	ln.	mm	Roll
H200X025HFT-2			0.25	6.4	0.06	1.5	0.13	3.3	
H200X034HFT-2			0.34	8.6	0.09	2.3	0.19	4.8	
H200X044HFT-2	2.00	50.0	0.44	11.1	0.13	3.3	0.25	6.4	500
H200X064HFT-2	2.00	50.8	0.64	16.2	0.19	4.8	0.38	9.7	
H200X084HFT-2			0.84	21.3	0.25	6.4	0.50	12.7	
H200X165HFT-2			1.65	41.9	0.50	12.7	1.00	25.4	250

 $\label{lem:additional} \mbox{Additional sizes and colors available on www.panduit.com}.$

Self-Laminating Labels

- Self-extinguishing material
- Sized specifically for wire and cable applications
- Temperature range: -65 °F to 275 °F (-54 °C to 135 °C)
- UL969 recognized File # MH14979; cUL recognized C22.2 No. 0.15.01, File # MH14979



Tedlar[™] **Self-Laminating Labels**

	Print-On Area	Wie	dth	Len	gth	Print Area H		Min O.	Cable D.	Max (Cable D.		Labels Per	Std. Pkg.
Part Number	Color	ln.	mm	ln.	mm	ln.	mm	ln.	mm	ln.	mm	Wire Range	Row	Qty.
S050X150TAT-A		0.50	12.7	1.50	38.1	0.50	12.7	0.16	4.0	0.32	8.1	Cat. 5e UTP/Cat. 6 UTP/ Cat. 6A UTP/ Cat. 5e FTP/10- 6 AWG	8	5000
S075X125TAT-A		0.75	19.1	1.25	31.8	0.38	9.7	0.12	3.1	0.28	7.0	Cat. 3 UTP/12 - 10 AWG	5	3000
S100X075TAT-A	\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\			0.75	19.1	0.25	6.4	0.08	2.0	0.16	4.0	Cat. 6 28 AWG/18 – 14 AWG		0500
S100X150TAT-A	White	1.00	25.4	1.50	38.1	0.50	12.7	0.16	4.0	0.32	8.1	Cat. 5e UTP/Cat. 6 UTP/Cat. 6A UTP/Cat. 5e FTP/10 - 6 AWG	4	2500
S100X225TAT-A				2.25	57.2	0.75	19.1	0.24	6.1	0.48	12.1	Cat. 6 FTP/Cat. 6A UTP/ Cat. 6A FTP/8 – 4 AWG		1500
S100X400TAT-A				4.00	101.6	1.00	25.4	0.32	8.1	0.95	24.1	I.1 2 – 1 AWG		2500
S200X400TAT-A		2.0	50.8	4.00	101.6	1.00	25.4	0.32	0.1	0.95	24.1	2 – 1 AWG	2	500


Tedlar is a registered trademark of E.I. du Pont de Nemours and Company.

Order number of labels required in multiples of Standard Package Quantity.

Marker Plates

Standard Marker Plates

		Width		Ler	igth	Ar Wie	Std. Pkg. Qty.		
Part Number	Color	ln.	mm	ln.	mm	ln.	mm	(Roll)	
M200X050Y7T		0.00	50.0	0.50	12.7	1.07	27.3		
M200X100Y7T	\A/I=:+-	2.00	50.8	1.00	25.4	0.80	20.3		
M300X050Y7T	White	0.00		0.50	12.7	2.07	52.6	1	
M300X100Y7T		3.00	76.2	1.00	25.4	1.80	45.7		



Additional colors at www.panduit.com.

^{*}Labels are roll mounted on 3.00" cores; when using the TDP43ME printer and 3.00" cores, the roll stand (TDP43ME-RS) is required.



Halogen-Free Marker Plates

							Std.			
	Wi	dth	Hei	ght	Width		Height		Pkg. Qty.	
Part Number	ln.	mm	ln.	mm	ln.	mm	ln.	mm	(Roll)	
M200X042UPT			0.42	10.7	0.42	10.7				
M200X042UPT-B	2.00	50.8		10.7	0.42	10.7	1.30	33.0		
M200X080UPT	2.00	50.8		20.3	0.80	20.3	1.30	33.0	!	
M200X080UPT-B			0.80	20.3	0.60	20.3				

High-Temp Marker Plates

							Std.		
	Wi	dth	Hei	ght	Width		Height		Pkg. Qty.
Part Number	ln.	mm	In.	mm	ln.	mm	ln.	mm	(Roll)
M200X042FQT			0.42	10.7	0.42	10.7		31.0	
M200X042FQT-B	2.00	50.8	0.42	10.7	0.42	10.7	1.22		
M200X080FQT	2.00		0.80	20.3	0.80	20.3	1.22		!
M200X080FQT-B			0.80	20.3	0.80	20.3			

Raised Panel Labels

Panduit raised panel labels, which are designed for 20 years of outdoor exposure, tested for use in solar applications, and compliant with print-performance requirements of UL969 and MIL-STD-202G, provide a rugged and professional appearance similar to engraved plates, but without the lengthy lead times or expensive engraving equipment.



	Wi	dth	He	ight		n Area ght	Std. Pkg.
Part Number	In.	mm	ln.	mm	In.	mm	Qty.
Raised Panel Push	Button La	bels					
C120X150APT-22	1.20	30.5	1.50	38.1	0.45	11.4	
C120X190APT-22	1.20	30.5	1.90	48.3	0.85	21.6	500
C180X180APT-30	1.80	45.7	1.80	45.7	0.36	9.1	300
C240X240APT-30	2.40	60.9	2.40	60.9	0.90	22.9	
Raised Panel Comp	onent Lab	els					
C100X050APT	1.00	25.4	0.50	12.7	0.50	12.7	
C125X030APT	1.25	31.8	0.30	7.6	0.30	7.6	
C200X100APT	2.00	50.8	1.00	25.4	1.00	25.4	
C252X030APT	2.52	64.0	0.30	7.6	0.30	7.6	
C300X100APT	3.00	76.2	1.00	25.4	1.00	25.4	500
C300X250APT	3.00	76.2	2.50	63.5	2.50	63.5	
C350X300APT	3.50	88.9	3.00	76.2	3.00	76.2	
C379X030APT	3.79	96.3	0.30	7.6	0.30	7.6	
C400X100APT	4.00	101.6	1.00	25.4	1.00	25.4	

Additional sizes and colors available on www.panduit.com

Safety Identification

				Wi	dth	Height		Std. Pkg.
Part Number	Header	Legend	Color	ln.	mm	ln.	mm	Qty.
Pre-Printed Adl	nesive Poly	ester Labels						
PPS0204W2100A		Potential Arc	1	4.50	114.3	2.25	57.2	
PPS0507W2100	WARNING	Flash Hazard	Black/ Orange	7.00	177.8	5.00	127.0	
PPS0305W2200		RISK OF FIRE OR ELECTRIC SHOCK	Black and Orange/ White					5
PPS0305C174A	CAUTION	THIS UNIT IS FED BY MORE THAN ONE SOURCE OF ENERGY	Black/ Yellow	5.00	127.0	3.50	88.9	
PPS0710C141		AREA IN FRONT OF THIS ELECTRIC PANEL	Tellow	10.00	254.0	7.00	177.8	1
PPS0305D79		HIGH VOLTAGE KEEP AWAY		5.00	127.0	3.50	88.9	5
PPS0710D66		AREA IN FRONT OF THIS ELECTRIC PANEL						
PPS0710D72	DANGER	HIGH VOLTAGE	Red and Black/ White	10.00	254.0	7.00	177.8	1
PPS0710D75		HIGH VOLTAGE UNAUTHORIZED PERSONNEL KEEP OUT						
Pre-Printed Rigi	d Polyethy	lene						
PRS1014D73	DANGER	HIGH VOLTAGE KEEP OUT	Red and Black/ White	14.00	355.6	10.00	254.0	1
Print On-Demar	nd Labels	1						
C200X400A51	WARNING		Black and Orange/ White			2.00	50.8	
		l .		1				

Red and

White

Black and

Orange/ White

Red and

White

Red and

Black/

White

Orange

and White

Red and

6.00

4.00

10.00 254.0

101.6

4.00

7.00

14.00 355.6 10.00 254.0

20.00 508.0 14.00 355.6

24.00 | 609.6 | 18.00 | 457.2

4.00

101.6

152.4

101.6

177.8

1

DANGER

WARNING

DANGER

N/A

DANGER

Blank (No Legend)

High Voltage

High Voltage

Keep Out

High Voltage

Keep Away

High Voltage

Unauthorized Personnel Keep Out

High Voltage

Blank (No Legend)

C200X400YZ1

C400X400A51

C400X400YZ1

C400X600A41

C400X600A51

C400X600AX1

C400X600AZ1

C400X600Y81

C400X600YX1

C400X600YZ1











Permanent Identification

Permanent Identification

			Ler	ngth	Wi	dth	Max. 3/16" (4.77mm)	Recommended Tie Cross Section	
Part Number	Material	Color	In. mm		ln.	mm	Characters per Line	Standard	Heavy

Metal Marker Plates – Dual Cable Tie Installation Stainless Steel Marker Plates

MMP350-C	304SS						23		×		
MMP350-C316	316SS				0.75	19.0	23	3	^		
MMP350H-C	304SS		2.50	00.0	0.75	19.0		3		Х	
MMP350H-C316	316SS		3.50 89.0			00			^		
MMP350W38-CQ	304SS	Natural			0.38	00 10 0	20	4			
MMP350W38-CQ316	316SS	Maturai	Natural			0.36	10.0		'		
MMP172-C	304SS				0.75	19.0		3	×		
MMP172-C316	316SS		1 70	44.0	0.75	19.0	8	3	^		
MMP172W38-C	304SS		1.72	1.72 44.0	0.38	8 10.0	0	1			
MMP172W38-C316	316SS										



Metal Tags - Single Cable Tie Installation Stainless Steel Tags

MT350-C	304SS		3.50	000	89.0		26				
MT350-C316	316SS		3.50	69.0	0.75	19.0	20	3			
MT172-C	304SS	Natural		0.75	19.0	10	3				
MT172-C316	316SS	Natural		44.0			10		X		
MT1D-Q	304SS		1.00* 25.0**	00* 25.0**	00* 25.0**	N/A	N/A	5	1		
MT150D-Q	304SS		1.50*	38.0**	IN/A	IN/A	5, 6, 5	3			



Representative offering only, consult www.panduit.com for complete listing of product.

Metal Embossing Tools

Part Number	Description	Std. Pkg. Qty.
-------------	-------------	----------------------

Portable Embossing Systems

PES400	Portable embossing system 3/16" (4.77mm) character, 11.5" (292mm) x 21.0" (534mm) x 19.0" (483mm), 95 lbs. (43 kg), 115 volt, 60 Hz with Easy-Mark™ Software	1	
--------	--	---	--

Metal Indenting Machine

MIM187	Indenting machine with 3/16" (4.77mm) character wheel, 11.25" (286mm) x 16.25" (413mm) x 11.75" (298mm), 41 lbs. (18.6 kg). Indenting machine with 1/8" (3.18mm) character wheel,	
MIM125	11.25" (286mm) x 16.25" (413mm) x 11.75" (298mm), 41 lbs. (18.6 kg).	1
MIM094	Indenting machine with 3/32" (2.38mm) character wheel, 11.25" (286mm) x 16.25" (413mm) x 11.75" (298mm), 41 lbs. (18.6 kg).	



Metal Embossing Hand Tool Kit

MEHT187	Includes tool, additional marking wheel, carrying case, one roll each META (aluminum) and METS (stainless steel) tape. Characters included:	4
IVIETT 1 101	META (aluminum) and METS (stainless steel) tape. Characters included.	
	ABCDEFGHIJKLMNOPQRSTUVWXYZ123456789/().	

Note: See our online custom order form: https://www.panduit.com/en/support/download-center/Custom-Order-Forms.html

^{*}Diameter (In.) **Diameter (mm).

Mobile and Desktop Printers

Thermal Transfer Hand-Held Printers

Part Number	Description	Std. Pkg. Qty.
MP300	Offers a wide variety of die-cut and continuous label sizes up to 1.5" wide, an automatic cutter for full and half cuts, 360 DPI resolution and fast printing speed. Includes label cassette, hard carrying case, rechargeable battery pack, magnetic attachments, USB cable, and power adapter. Available only in North America.	
MP200	Offers continuous labels up to 1.0" wide, print speeds up to 1.2" per second, a powered cutter for both full and half cuts, a large LCD back-lit screen, custom label modes, bar-codes and symbols. Includes continuous label cassette and a quick reference card. For use globally.	1
MP200-KIT	The MP200-KIT printer is a rugged, high performance, economical industrial printer. It features fast print speeds up to 1.2"/sec, a powered cutter, a large LCD backlit screen, custom label modes, barcodes and symbols. The MP200 prints continuous tapes up to 1.0" wide for network, electrical, and other industrial applications. It comes with the printer, a continuous label cassette, hard carrying case, rechargeable battery pack, magnetic feet, USB cable, and power adapter. For use in North America.	



Thermal Transfer Desktop Printers

Part Number	Description	Std. Pkg. Qty.
TDP43ME	300 dpi printer (up to 4.00" per second); includes moderate-use printer, Easy-Mark™ Labeling Software, RMEH4BL black hybrid ribbon, user manual, quick start card, driver disk, USB cable, AC power adapter with U.S. power cord; for use in North America	
TDP43ME-KIT	TDP43ME printer, Easy-Mark™ Labeling Software, RMEH4BL black hybrid ribbon, user manual, quick start card, TDP43ME-CASE carrying case, one roll S100X-150VATY labels, roll stand, driver disk, USB cable, AC power adapter with U.S. power cord; for use in North America	
TDP43HE	300 dpi printer (up to 8.00" per second); includes high-volume printer, Easy-Mark" Labeling Software, RMEH4BL black hybrid ribbon, user manual, quick start card, driver disk, USB cable, AC power adapter with U.S. power cord; for use in North America	
TDP46HE	600 dpi printer (up to 4.00" per second); includes high-volume printer, Easy-Mark™ Labeling Software, RMEH4BL black hybrid ribbon, user manual, quick start card, driver disk, USB cable, AC power adapter with U.S. power cord; for use in North America	



Identification Software

Desktop Printers	Description	Std. Pkg. Qty.
EMPLUS-CD	Easy-Mark Plus™ Labeling Software, CD-ROM	
EMPLUS-DL	Easy-Mark Plus™ Labeling Software, online download.	
EMPLUS-2GO	Easy-Mark Plus™ Portable Application, USB flash drive.	1
EMPLUS-SERVER	Easy-Mark Plus™ Labeling Software, networkable server based version.	



INDUSTRY COMPLIANCE

Spec/Approval	Requirement	Products
UL -224 with VW-1 flame rating	Flame-resistant material. The tubing must not continue to burn longer than 1 minute.	Military Grade Heat Shrink Label
UL 969	Material must not lose legibility, defacement and adhesion properties when exposed to 48 hrs. water immersion, 10 days oven exposure at maximum temperature and 7 hrs. at minimum temperature, and 750 hrs. UV radiation exposure.	Raised Panel Label, Self-Laminating Tedlar Super-Tack Polyester Label/Tape, Continuous Vinyl Tape
C22.2 No. 0.15-01	Material must not lose legibility, defacement, and adhesion properties when exposed to same conditions as UL969. In addition, the material is also exposed to heat and cold humidity cycling, solvent immersion, abrasion and solvent abrasion.	Raised Panel Label, Self-Laminating Tedlar Super-Tack Polyester Label/Tape, Continuous Vinyl Tape
AMS-DTL-23053/5 (Class 1 and 3)	Flame-resistant material. Continuous operating temperature range is -55 °C (-67 °F) to 135 °C (275 °F).	Military Grade Heat Shrink Label
AMS-DTL-23053/6 (Class 1)	Flame-resistant material. Continuous operating temperature range is -55 °C (-67 °F) to 135 °C (275 °F).	Fluid-Resistant Heat Shrink Label
SAE-AS81531 (Rub Test)		High-Temperature Marker Plate
SAE-AS5942 (Rub Test)	Print shall remain legible after 20 rubs with hard hand pressure.	Military Grade Heat Shrink Label, Halogen-Free Heat Shrink Label, Fluid-Resistant Heat Shrink Label
MIL-STD-883F (Test Standard) - Chemical Information below	The markings on the component parts shall remain legible when subjected to the following solvents; these solvents will not cause deleterious, mechanical or electrical damage, or deterioration of the material.	See below product for each chemical test
Chemical Used - METHOD 2015.13 SOLUTION A	At 20C-30C a mixture consisting of the following: (1) one part by volume of isopropyl alcohol; and (2) three parts by volume of mineral spirits.	Military Grade Heat Shrink Label, Halogen-Free Heat Shrink Label, Fluid-Resistant Heat Shrink Label
Chemical Used - METHOD 2015.13 SOLUTION B	A semi-aqueous or non-aqueous based organic solvent like a terpene or heterocyclic compound.	Military Grade Heat Shrink Label, Halogen-Free Heat Shrink Label
Chemical Used - METHOD 2015.13 SOLUTION D	At 63C-70C, a mixture consisting of the following: (1) 42 parts by volume of deionized water; (2) 1 part by volume of propylene glycol monomethyl ether; and (3) 1 part by volume of monoethanolamine.	Military Grade HeatShrink Label, Halogen-Free Heat Shrink Label, Fluid-Resistant Heat Shrink Label
MIL-STD202G (Test Standard) - Chemical Information below	The markings on the component parts shall remain legible when subjected to the following solvent; these solvents will not cause deleterious, mechanical or electrical damage, or deterioration of the material.	See below product for each chemical test
Chemical Used - METHOD 215K SOLUTIONS A	A mixture consisting of the following: (1) one part by volume of isopropyl alcohol; and (2) three parts by volume of mineral spirits.	Marker Plate Halogen-Free Heat Shrink Label, Raised Panel Label, Fluid-Resistant Heat Shrink Label
Chemical Used - METHOD 215K SOLUTIONS C	A terpene defluxer consisting of a minimum of 90% d-limonene and 10 % surfactant.	Marker Plate Halogen-Free Heat Shrink Label, Raised Panel Label
Chemical Used - METHOD 215K SOLUTIONS D	A mixture consisting of the following: (1) 42 parts by volume water; (2) 1 part by volume of propylene glycol monomethyl ether; and (3) 1 part by volume of monoethanolamine.	Marker Plate Halogen-Free Heat Shrink Label, Raised Panel Label, Fluid-Resistant Heat Shrink Label
	1000 VVVV 0 1 1 1 1 1 1 1 1 1 1 1 1 1 1	
BS6853	1999 Vehicle Category 1A for burning behavior and toxic gas emissions. Smoke Density Class II	Halogen-Free Heat Shrink Label
NF F00-608 Class A and H	Print shall remain legible after 10 rubs after being immersed for 168 hrs. in HCL acid, diesel, NaOH base and 70 hrs. in mineral spirit. Tensile strength shall be equal to or greater than 14MPa and elongation shall be 400% or higher.	Fluid-Resistant Heat Shrink Label
LOCA/MSLB (IEEE 323-2003)	The qualification requirements in this standard, when met, demonstrate and document the ability of equipment to perform safety function(s) under applicable service conditions, including design basis events, reducing the risk of common-cause equipment failure.	High-Temperature Marker Plate, Military Grade Heat Shrink Label (AMS-DTL-23053/5[Class 1 and 3] only)

Please refer to the Technical Data Sheet for each product for complete information.



infrastructure for a connected world

- Industrial
- Oil Rias
- Refineries
- Chemical Plants
- Natural Gas Processing Plants
- LNG Plants
- Water Treatment Facilities
- Wind Farms
- Solar
- Nuclear
- Mining
- Ships
- Submarines
- Cell Towers
- Telecommunications
- Transportation
- OEM

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

Panduit Canada Markham, Ontario cs-cdn@panduit.com Phone: 800.777.3300

Panduit Europe Ltd. London, UK cs-emea@panduit.com Phone: 44.208.601.7200

Panduit Singapore Pte. Ltd. Republic of Singapore cs-ap@panduit.com Phone: 65.6305.7575

Panduit Japan Tokyo, Japan cs-japan@panduit.com Phone: 81.3.3767.7011

Panduit Latin America Guadalajara, Mexico cs-la@panduit.com

Phone: 52.33.3777.6000 Panduit Australia Pty. Ltd. Victoria, Australia cs-aus@panduit.com Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com or by phone: 800-777-3300

©2022 Panduit Corp. ALL RIGHTS RESERVED. Printed in the U.S.A. IDCB96-SA-ENG 05/2022

COMPLIANCE WITH INDUSTRY STANDARDS

Panduit identification solutions are engineered to meet the highest standards. Our products meet or exceed the most stringent industry standards including RoHS, UL, CSA, MIL, ASTM, NF, and many others. They also assist in compliance with OSHA, NEC, NFPA, TIA, and other requirements.



















Panduit offers one of the widest ranges of permanent identification solutions in the industry to enable reliable, comprehensive, identification throughout the physical infrastructure. Ideal in harsh and industrial environments, the Panduit permanent identification system delivers long-term durability and legibility for optimum identification of pipes, conduit, cables and equipment. Safe, quick, and easy to install, the system includes stainless steel, and aluminum marker plates, tags, marking tools and ties engineered for maximum reliability, improved productivity and workplace safety to mitigate risk.

PANDUIT DIFFERENCE

Panduit is committed to delivering a consistently high level of quality and service the world over. With a presence in more than 100 countries, local Panduit sales representatives and technical specialists offer guidance and support that bring value to your business. Our global supply chain, which includes manufacturing, customer service, logistics, and distribution partners, provides prompt response to your inquiries and streamlines delivery to any worldwide destination.

COMPLETE SOLUTIONS FROM PANDUIT

Panduit harsh environment solutions include the Pan-Steel™ System, power and grounding connectors, identification and safety, abrasion protection, heat shrink, wiring duct, industrial ethernet, and cable tie solutions. These solutions feature Panduit world-class quality, rigorously tested to deliver the highest performance, and lowest total cost of ownership.





Identification and Safety



Wiring Duct



Abrasion Protection



VeriSafe[™] Absence of **Voltage Testers**



Power and Grounding Connectors



Heat Shrink



Cable Ties