



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT P/N	WEIGHT
SEE SHEET 2	SEE SHEET 2




LEFT VIEW



REAR VIEW



RIGHT VIEW



FRONT VIEW

BOTTOM VIEW

PLUG / RECEPTACLE BLOCK

PLUG
IEC 60309 2P+E 6H
IP44 (SPASHPROOF)
32A, 250VAC MAX RATED INPUT

RECEPTACLE
IEC 60320 C13
10A, 250V MAX RATED OUTPUT

RECEPTACLE
IEC 60320 C19
16A, 250V MAX RATED OUTPUT

SPECIFICATION:


- STANDARD
UNIT TYPE: MONITORED PER OUTLET
ORIENTATION: VERTICAL, 0U FULL
OUTLET QTY & TYPE: (20)C13, (4)C19
INPUT VOLTAGE: 100-240VAC
INPUT FREQUENCY: 50/60HZ
INPUT CURRENT: 32A
BREAKER QTY & TYPE: (2)16AMP, SINGLE-POLE
INPUT PHASE: SINGLE-PHASE
RATED POWER: 7.4 kVA
INPUT PLUG: IEC 60309 2P+E 6H 32A
INPUT POWER CORD: SEE SHEET 2 PART NUMBER TABLE
REGULATORY STANDARD: RoHS COMPLIANT
- ADDITIONAL:
NONE
- ACCESSORIES:
DOCUMENTATION KIT
PRODUCT SAFETY WARNING SHEET

NOTES:

- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSIONS ARE IN [INCHES]
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
- FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
- DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

IDENTIFICATION:

FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: E24F06M-XXYZ



WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		SIGN	
		DATE	
		PRINT	
TITLE INTELLIGENT SERIES PDU E24F06M CONTROL DRAWING			
ITEM REVISION NAME:		PANDUIT	
DATASHEET FILE NAME:			
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR: N/A	
Tolerance (mm) 0 < L ≤ 50 ± 0.5 50 < L ≤ 250 ± 1.0 250 < L ≤ 500 ± 1.5 500 < L ≤ 1000 ± 2.5 1000 < L ≤ 2000 ± 4.0		DRAWING NUMBER: E24F06M_DC	
THIRD ANGLE PROJECTION	DRAWN BY: LL		SCALE: NONE
	DATE: 08/29/2023	CHK: MIM	SCALE: NONE
			SHT 1 OF 2
			SCALE: B

00A	08/29/2023	LL	MIM	MJD	INITIAL RELEASE	E24F06M
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
E24F06M	MPO PDU, 32A, (20)C13 (4)C19, IEC 60309 2P+E 6h IP44-3M, TOP-FED, BLACK	BLACK(RAL 9005)	3M(+254MM/-127MM)[10'(+10"/-5"']	7.1kg

00A	08/29/2023	LL	MIM	MJD	INITIAL RELEASE	E24F06M
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		SIGN
		DATE
		PRINT
TITLE INTELLIGENT SERIES PDU E24F06M CONTROL DRAWING		
ITEM REVISION NAME:		PANDUIT
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR: N/A
Tolerance (mm) 0 < L ≤ 50 ± 0.5 50 < L ≤ 250 ± 1.0 250 < L ≤ 500 ± 1.5 500 < L ≤ 1000 ± 2.5 1000 < L ≤ 2000 ± 4.0		DRAWING NUMBER: E24F06M_DC
THIRD ANGLE PROJECTION		
DRAWN BY: LL	DATE: 08/29/2023	CHK: MIM
SCALE: NONE	SHT 2 OF 2	
		SCALE: B