



Pan-Steel® Super-Heavy Cable Tie System

Pan-Steel® Super-Heavy Cable Tie System provides a superior bundling solution in applications requiring cables to be safely restrained in the event of a short circuit. Designed to work together, Pan-Steel® Super-Heavy Cable Ties, cushion sleeve and tool provide an 80% time savings when compared to conventional cable cleat installations. The patented locking head design, allows these ties to meet the critical strength requirements to restrain cables in the event of a short circuit, with substantial reduction in material costs compared to the conventional methods. The installation tools feature an adjustable tension control mechanism to provide repeatable installations with consistent bundle tension for improved productivity and reliability. The cushion sleeve provides additional bundle protection against abrasion during and after installation. The Pan-Steel® Super-Heavy Cable Tie System is part of the complete bundling solution from Panduit, delivering maximum reliability throughout the physical infrastructure.

Key Features Benefits

Self-locking cable tie design	Helps to reduce the number of installation steps required to deliver an 80% installation time savings – lowering installed costs				
	Provides infinite bundling capacity to accommodate multiple bundle sizes to reduce inventory and increase jobsite flexibility				
Stainless steel head construction	High strength construction improves durability				
	Reduces material required for the job (compared to competition) to deliver a substantial cost reduction in material				
Fully assembled discrete lengths	Eliminates tie assembly, reducing installation time				
Stainless steel construction	Superior corrosion resistance to deliver a long service life				
Cushion sleeve	Covers the edge of the tie to provide additional bundle and cable jacket protection				
Tension control tool	Provides consistent/repeatable installations for increased reliability and productivity				

Technical Information — Super-Heavy Locking Ties

Material	AISI 304 or AISI 316 grade stainless steel	RoHS	Compliant
Maximum temperature rating	538°C (1000°F)	Flammability	Non-flammable
Minimum temperature rating	-80°C (-112°F)	Ultraviolet light resistance	Excellent

Pan-Steel® Super-Heavy Cable Tie System

Super-Heavy Metal Locking Ties

Part Number		Max. Bundle Diameter		Length***		Min. Loop Tensile Strength**		Min. Bundle Diameter		Width		Thickness		Std. Ctn.
	ln.	mm	ln.	mm	Lbs.	N	ln.	mm	ln.	mm	ln.	mm	Pkg. Qty.+	Qty.
AISI 304 Stainles	s Steel -	- For G	eneral l	urpos	е									
MLT4SH-LP	4.0	102	17.1	434		4005	1.00	25.4	.63	15.9	.015	.38	50	250
MLT6SH-LP	6.0	152	23.4	594									50	250
MLT8SH-LP	8.0	203	29.7	754	900								50	250
MLT10SH-LP	10.0	254	35.9	912									50	250
MLT12SH-Q	12.0	305	42.2	1072									25	125
AISI 316 Stainles	s Steel -	- For S	uperior	Corros	ion Res	istance								
MLT4SH-LP316	4.0	102	17.1	434			1.00	25.4	.63	15.9	.015	.38	50	250
MLT6SH-LP316	6.0	152	23.4	594	900	4005							50	250
MLT8SH-LP316	8.0	203	29.7	754									50	250
AISI 304 Stainles	s Steel -	Double	e Wrapp	oed^ - F	or Addi	itional St	rength	1						
MLT4DSH-Q	4.0	102	29.5	749		5340	1.00	25.4	.63	15.9	.015	.38	25	125
MLT6DSH-Q	6.0	152	41.5	1054	1200								25	125
MLT8DSH-Q	8.0	203	53.5	1359									25	125
AISI 316 Stainles	s Steel -	Double	e Wrapp	oed^ - F	or Addi	itional St	rength							
MLT4DSH-Q316	4.0	102	29.5	749									25	125
MLT6DSH-Q316	6.0	152	41.5	1054	1200	5340	1.00	25.4	.63	15.9	.015	.38	25	125
MLT8DSH-Q316	8.0	203	53.5	1359									25	125

^{**}Per SAE Standard AS23190/3 (formerly MIS).

PCS Cushion Sleeving

 Black neoprene sleeving used with Pan-Steel® Stainless Steel Ties, custom length banding, and MS strap Isolation between dissimilar metals allows the ties and straps to be used with aluminum cable tray





	Used with		dth	Len	Std. Pkg.	
Part Number	Pan-Steel® Ties/Strapping	ln.	mm	Ft.	m	Qty+
PCSSH-B-CR*	MLT/EH/SH and MS Straps	.91	23.1	100	30.5	1

^{*}Meets MIL-R-6855.

Installation Tools

Part Number	Part Description	Std. Pkg. Qty.
PBTMT	Battery powered installation tool, for use with Pan-Steel® heavy, extra-heavy, and super-heavy, cross section MLT style ties, and MLTD double wrapped style ties, 2 –12 volt lithium-ion batteries and 115 volt, 60 Hz charger included.	1
RT2HT	Use with extra-heavy .50" (12.7mm) and super-heavy .63" (15.9mm) cross section Pan-Steel® type MLT ties. Width of tool nose 2.60" (66.0mm).	1
RT2HTN	Narrow nose installation tool for use with extra-heavy .50" (12.7mm) and super-heavy .63" (15.9mm) cross section Pan-Steel® type MLT ties. Width of tool nose 1.06" (27.0mm).	1
KRT2HTB	Replacement cutter handle for RT2HT.	1

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA Markham, Ontario cs-cdn@panduit.com Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK cs-emea@panduit.com Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore cs-ap@panduit.com Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan cs-japan@panduit.com Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Jalisco, Mexico cs-la@panduit.com Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia cs-aus@panduit.com Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty





^{***}Other lengths available, contact Panduit Customer Service.

[^]Tested for short circuit applications up to 71.5 kA.

⁺Order in multiples of Standard Package Quantities.

⁺Order in multiples of Standard Package Quantities.