

Mini-Com® TX5e™ Keyed UTP Jack Modules

specifications

Category 5e/Class D, 8-position keyed UTP jack modules shall terminate unshielded twisted 4-pair, 22 – 26 AWG, 100 ohm cable and shall not require the use of a punchdown tool. The jack module shall be mechanically keyed with color-specific positive and negative keying features to prevent unintentional mating with unlike keyed or non-keyed modular plugs. The forward motion termination method shall optimize performance by maintaining cable pair geometry and eliminating conductor untwist. The red termination cap shall be color coded for T568A and T568B wiring schemes.



TX5e™ Keyed UTP Copper Cabling System

Mini-Com® TX5e™ Keyed UTP Jack Modules

Keyed A (black):	CJK5E88TGBL
Keyed B (red):	CJK5E88TGRD
Keyed C (green):	CJK5E88TGGR
Keyed D (yellow):	CJK5E88TGYL
Keyed E (orange):	CJK5E88TGOR
Keyed F (blue):	CJK5E88TGBU

TX5e™ Keyed UTP Patch Cords

Keyed A (black):	UTPKCH*BL
Keyed B (red):	UTPKCH*RD
Keyed C (green):	UTPKCH*GR
Keyed D (yellow):	UTPKCH*YL
Keyed E (orange):	UTPKCH*OR
Keyed F (blue):	UTPKCH*BU

TX5500™ UTP Copper Cable

Plenum:	PUP5504**-UY
Riser:	PUP5504**-UY

Mini-Com® Angled Flush Mount Modular Patch Panels

24-port, 1RU:	CPPA24FMWBLY
48-port, 2RU:	CPPA48FMWBLY

Mini-Com® Flat Flush Mount Modular Patch Panels

24-port, 1RU:	CPP24FMWBLY
48-port, 2RU:	CPP48FMWBLY
72-port, 2RU:	CPP72FMWBLY

For additional modular patch panels reference www.panduit.com

Tools and Accessories

Termination tools:	TGJT or EGJT
Wire snipping tool:	CWST
Wire stripping tool:	CJAST
Clear dust cap:	MDC-C

*Substitute for length in feet: 3, 5, 7, 10 or 14 feet. Contact customer service for universal reference patch cords.

**To designate color, add suffix BU (Blue), WH (White), YL (Yellow) or IG (International Gray). For additional cable colors, contact customer service.

technical information

Category 5e/Class D channel and component performance:	Certified channel performance in a 4-connector configuration up to 100 meters and exceeds the requirements of ANSI/ TIA-568-C.2 Category 5e and ISO 11801 2nd Edition Class D standards Certified component performance to the ANSI/TIA-568-C.2 Category 5e and ISO 11801 Class D standards
FCC compliance:	Meets ANSI/TIA-1096-A; contacts plated with 50 microinches of gold for superior performance
IEC compliance:	Meets IEC 60603-7
PoE compliance:	Meets IEEE 802.3af and IEEE 802.3at for PoE applications
UL rated:	No. 1863

key features and benefits

Color-specific keys with positive and negative keying features	Mechanically and visually distinguish connections to prevent unintentional insertion into unlike keyed or non-keyed ports, all network design flexibility and versatility, and accommodate more discrete networks
100% performance tested	Confidence that each jack module will deliver the critical electrical performance requirements
Utilizes enhanced Giga-TX™ Technology	Wire cap optimizes performance by eliminating conductor untwist and reduces installation time and expense; simplifies termination and maintains conductor twists for reliable and consistent terminations
True strain relief	Controls cable bend radius for long term installed performance
Modular	Jack modules snap in and out of Mini-Com® Faceplates, Modular Patch Panels, and Surface Mount Boxes for easy moves, adds, and changes
Individually serialized	Marked with quality control number for future traceability
Integrated block out feature	Prevents standard RJ11 modular plugs from mating with keyed jack modules

applications

The TX5e™ Keyed UTP Jack Modules are a component of the Panduit® TX5e™ UTP Copper Cabling System. Keyed connectivity enables a level of visual and mechanical differentiation, and physical layer security that conventional cabling systems cannot provide. Key applications include:

- Ethernet 10BASE-T, 100BASE-T (Fast Ethernet), 1000BASE-T (Gigabit Ethernet)
- 155 Mb/s ATM, 622 Mb/s ATM
- Token Ring 4/16
- Voice/data systems
- Voice over Internet Protocol (VoIP)


Mini-Com® TX5e™ Keyed UTP Jack Modules

Reliability Tests

Mechanical Test	Test Method	Measurement	Typical Test Results
<i>Normal Force</i>	—	Load (grams)	>100
<i>Vibration</i>	IEC 512-6d	Circuit Resistance (mOhms)	<40
<i>Shock</i>	IEC 512-6c	Contact Disturbance (microseconds)	<5
<i>Durability</i>	IEC 512-9a	Circuit Resistance (mOhms)	<40
<i>Mating/Un-Mating</i>	IEC 512-13b	Mating Force (N)	<20
		Un-Mating Force (N)	<20
<i>Termination Cycles</i>	IEC 352	Number of Cycles	<20

Electrical Test	Test Method	Measurement	Typical Test Results
<i>Low Level Circuit Resistance</i>	IEC 512-2a	Resistance (mOhms)	<20
<i>Dielectric Withstand Voltage</i>	IEC 512-4a	1000 V, 1 minute	Passed
<i>Insulation Resistance</i>	IEC 512-3a	Resistance (mOhms)	>500

Environmental Test	Test Method	Measurement	Typical Test Results
<i>Temperature Life</i>	IEC 512-9b	Circuit Resistance (mOhms)	<40
<i>Humidity</i>	IEC 512-11c	Circuit Resistance (mOhms)	<40
<i>Thermal Shock</i>	IEC 512-11d	Circuit Resistance (mOhms)	<40
<i>Climatic Sequence</i>	IEC 512-11a	Circuit Resistance (mOhms)	<40
<i>Flowing Mixed Gas Corrosion</i>	IEC 512-11g	Circuit Resistance (mOhms)	<40



Shielded Jack Color/Key Code and Part Number

A – Black	B – Red	C – Green	D – Yellow	E – Orange	F – Blue
CJK5E88TGBL	CJK5E88TGRD	CJK5E88TGGR	CJK5E88TGYL	CJK5E88TGOR	CJK5E88TGBU

Dimensions are in inches. [Dimensions in brackets are metric].

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA
Markham, Ontario
cs-cdn@panduit.com
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
cs-la@panduit.com
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300 and reference COSP249

PANDUIT®

©2012 Panduit Corp.
ALL RIGHTS RESERVED.
COSP249--WW-ENG
Replaces WW-COSP153
10/2012