

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
P24D##M-XXYZ	SEE SHEET 2

**SPECIFICATION:**

- |   |   |
|---|---|
| <p>1. STANDARD<br/> UNIT TYPE:<br/> ORIENTATION:<br/> OUTLET QTY &amp; TYPE:<br/> INPUT VOLTAGE:<br/> INPUT CURRENT:<br/> BREAKER QTY &amp; TYPE:<br/> INPUT PHASE:<br/> RATED POWER:<br/> INPUT PLUG:<br/> INPUT POWER CORD:</p> | <p>MONITORED INPUT<br/> VERTICAL, OU FULL<br/> SEE SHEET 2 FOR CONFIGURATIONS<br/> 200-240/346-415VAC<br/> 30A (24A DERATED)<br/> (6) 20A, SINGLE POLE<br/> THREE-PHASE WYE<br/> 17.3 kVA<br/> SEE SHEET 2 FOR CONFIGURATIONS<br/> SEE SHEET 2 FOR PART NUMBER<br/> TABLE</p> |
|---|---|

REGULATORY STANDARD: RoHS COMPLIANT

2. ADDITIONAL:  
CIRCUIT BREAKERS RATED AT 10KAIC


3. ACCESSORIES:  
(1) QUICK-START GUIDE

**NOTES:**


- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSIONS ARE IN [INCHES]
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
- VISIT OUR ON-LINE CATALOG AT [WWW.PANDUIT.COM](http://WWW.PANDUIT.COM) FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PRODUCT
- FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
- DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

**IDENTIFICATION**

FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: P24D##M - XXYZ




**LEFT VIEW**




**REAR VIEW**


TOOLESS MOUNTING  
BUTTON LOCATIONS (12)PL



**RIGHT VIEW**



**FRONT VIEW**



**BOTTOM VIEW**

XX: FINISHED GOOD COLOR BL=BLACK YL=YELLOW RD=RED BU=BLUE WH=WHITE GN=GREEN	Y: INPUT FEED TYPE 1=TOP-END FED 2=BOTTOM-END FED	Z: INPUT CORD LENGTH A=1 METER B=2 METER C=3 METER
--	---	---

FOUR CHARACTER SUFFIX FOR ALTERNATE  
PRODUCT CONFIGURATIONS

**PLUG/ RECEPTACLE BLOCK**

	IEC 60309, 4P 5W, 6H IP67 (WATERTIGHT) 30A, 346-415V MAX RATED INPUT 24A DERATED		IEC 60320/C19 16A, 250V MAX RATED OUTPUT
	IEC 60309, 4P 5W, 6H IP44 (SPASHPROOF) 30A, 346-415V MAX RATED INPUT 24A DERATED		IEC 60320/C13 10A, 250V MAX RATED OUTPUT
	NEMA L22-30P, 4P 5W 30A, 277-480V MAX RATED INPUT 24A DERATED		

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGNTHE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.

SIGN	
DATE	
PRINT	

TITLE		INTELLIGENT SERIES PDU	
		P24D##M-XXYZ	
		CUSTOMER DRAWING	
ITEM REVISION NAME			
DATASET FILE NAME			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: mm [IN]		MATERIAL:	
Tolerance (mm)		DRAWING NUMBER:	
0<L<50 ±0.5		P24D_DC	
50<L<250 ±1.0			
250<L<500 ±1.5			
500<L<1000 ±2.5			
1000<L<5000 ±4.0			
THRID ANGLE PROJECTION		BY: WAC DATE: 03/14/19 CHK: - SCALE: NTS	
REV: 01A DATE: 3/21/2019 BY: WAC CHK: DACU APR: JAWI DESCRIPTION: RELEASED TO PRODUCTION ECN: P24D		SHEET 1 OF 2	


REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
01A	3/21/2019	WAC	DACU	JAWI	RELEASED TO PRODUCTION	P24D

D10100DB/17

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	INPUT PLUG CONFIGURATION	RECEPTACLE CONFIGURATION	COLOR	INPUT CORD LENGTH	WEIGHT
<b>P24D04M</b>	VERTICAL, (12)C13, (12)C19, MONITORED INPUT, 200-240/346-415V/30A/3 PHASE WYE, TOP-END FED, 3 METER INPUT CORD, BLACK	L22-30P 30A 4P, 5W	(12) C13, (12) C19	BLACK (RAL 9005)	3M(+254MM/-127MM) 10' [+10"/-5"]	13.7kg
P24D02M	VERTICAL, (12)C13, (12)C19, MONITORED INPUT, 200-240/346-415V/30A/3 PHASE WYE, TOP-END FED, 3 METER INPUT CORD, BLACK	IEC60309 30A 4P, 5W, IP67 (WATERTIGHT)	(12) C13, (12) C19	BLACK (RAL 9005)	3M(+254MM/-127MM) 10' [+10"/-5"]	13.7kg
P24D05M	VERTICAL, (12)C13, (12)C19, MONITORED INPUT, 200-240/346-415V/30A/3 PHASE WYE, TOP-END FED, 3 METER INPUT CORD, BLACK	IEC60309 30A 4P, 5W, IP44 (SPLASHPROOF)	(12) C13, (12) C19	BLACK (RAL 9005)	3M(+254MM/-127MM) 10' [+10"/-5"]	13.7kg

(12)C13, (12)C19



WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.

SIGNATURE BOX		SIGNATURE	
DATE		DATE	
PRINT		PRINT	
TITLE			
INTELLIGENT SERIES PDU <b>P24D##M-XXYZ</b> CUSTOMER DRAWING			
ITEM REVISION NAME		MATERIAL:	
DATASET FILE NAME		<b>PANDUIT</b>	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: mm [IN]		DRAWING NUMBER:	
Tolerance (mm) 0<L<50 ±0.5 50<L<250 ±1.0 250<L<500 ±1.5 500<L<1000 ±2.5 1000<L<2000 ±4.0		<b>P24D_DC</b>	
BY	DATE	CHK	SCALE
WAC	03/14/2019	-	NTS
SHEET 2 OF 2			SIZE
			B

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
01A	3/21/2019	WAC	DACU	JAWI	RELEASED TO PRODUCTION	P24D

D:10100DBE/17