


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART No.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	WEIGHT 100 pcs lbs. (g)
	MIN. in (mm)	MAX. in (mm)								
PLT100-UV15	.03 (.8)	.9 (23)	.038 (.97)	.188 (3.0)	.173 (4.4)	.154 (3.9)	.209 (5.3)	4.2 (105.9)	18 (80)	.066 (30.0)
PLT150-UV15	.03 (.8)	1.5 (38)	.040 (1.0)	.168 (4.3)	.220 (5.6)	.179 (4.5)	.306 (7.8)	6.2 (157.0)	40 (178)	.145 (66)
PLT200-UV15	.06 (1.5)	2.0 (51)	.046 (1.2)	.225 (5.7)	.290 (7.4)	.220 (5.6)	.342 (8.7)	8.3 (210.8)	50 (222)	.30 (137)
PLT250-UV15	.16 (4.1)	2.6 (66)	.050 (1.3)	.225 (5.7)	.318 (8.1)	.220 (5.6)	.360 (9.1)	10.4 (264.2)	75 (334)	.41 (185)
PLT300-UV15	.161 (4.1)	3.2 (81)	.050 (1.3)	.225 (5.7)	.318 (8.1)	.220 (5.6)	.360 (9.1)	12.4 (315.0)	75 (334)	.49 (220)
PLT350-UV15	.19 (4.8)	4.13 (105)	.064 (1.6)	.330 (8.4)	.393 (10)	.290 (7.4)	.546 (13.9)	15.3 (338.6)	120 (534)	1.18 (536)
PLT450-UV15	.19 (4.8)	5.2 (132)	.068 (1.7)	.380 (9.7)	.425 (11)	.320 (8.1)	.597 (15.2)	18.6 (471.0)	175 (778)	1.70 (772)

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
02	3/27/19	BWG	MPH	JADE	REMOVED MATERIAL COLUMN .	042397/02
01	3/21/19	BWG	MPH	JADE	UPDATED ECN DOCUMENT	042397/01
00	11/07/18	BWG	MPH	JADE	RELEASED	042397/00

Super-Grip Ivory UV Resistant Ties

CUSTOMER DRAWING

ITEM REVISION NAME: 00226NB/02

DATASET FILE NAME: 00226NB/02

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)

.X ± .02 (.XX) .XXX ± .020 (.XXX)

.XX ± .02 (.XX) ANGLE ±

THIRD ANGLE PROJECTION

MATERIAL: IVORY UV RESISTANT NYLON 6.6

DRAWING NUMBER: 00226NB_DC

DRAWN BY: BWG DATE: 11/07/18 CHK: MPH SCALE: NONE

SHT 1 OF 1 SIZE: A

D101000A/20