
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT LENGTH WEIGHT MOUNTING HOLE DIM'S

PANDUIT PART NO.	LENGTH	WE I GHT	MOUNTING HOLE DIM'S				
T45B**8	96.00 ±.18 (2348 ±4.5)	1.60 LB/96 IN. (723.8 G/2438 MM)	1.47	3.91	8.00 (203.2)		
T45B**10	120.00 ±.18 (3048 ±4.5)	2.00 LB/120 IN. (904.8 G/3048 MM)	1.47	3.91	8.00 (203.2)		



В

NOTES:

- ** 1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLORS AND OR PACKAGE QUANTITY.
 - 2. THE T45B IS USED WITH THE T45C RACEWAY COVER.
 - 3. DIMENSIONS IN PARENTHESIS ARE IN METRIC.
 - 4. PART IS DESIGNED TO SUPPORT MAXIMUM WEIGHT ON A CLEAN, DRY, SMOOTH SURFACE. THE SURFACE MUST BE PROPERLY PREPARED IN ACCORDANCE WITH PANDUIT RECOMMENDATIONS.
 - 5. TO APPLY PART:
 - a. REMOVE PROTECTIVE LINER.
 - 6. PLACE PART IN DESIRED LOCATION.
 - c. APPLY PRESSURE TO FLAT SURFACE OF PART.

.075 [18.5]
[1.9] OPTIONAL TAPE
[60.3]

NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.

							I I I LE					
							T-45 BASE					
							(T45B)					
							CUSTOMER DRAWING					
							D36975EC/04			The supplier		
							DATASET F				PANDUI	
							D36975EC_DC_T45B_04A			_		
							DIMEN	NLESS OTHERW SIONAL TOLER	ISE SPE ANCES A	CIFIED, RE: IN [mm]	MATERIAL:	
							.x ± .02 [.51] .xxx ± .005 [.127]		PVC			
							.xx ±	.01 [.25]	ANGLES ±	_		
04A	5-5-22	BJN	BSN	TAM	RELEASED TO PRODUCTION	36975-65				IRD ANGLE OJECTION	36975 - 65	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	BJN	5-5-22	BSN	N/A	SHT 1 0F 1	SIZE