
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES, UNLESS OTHERWISE SPECIFIED:

- Interchangeable Crimp Die Inserts used with CT-2500CH Crimp Head frame and CT-2300 Micro Crimp Tool to crimp Panduit #26 - 8 AWG (0,14 – 10,0mm²) insulated and non-insulated single wire ferrules and #22 - 12 AWG (0,05 - 4,0mm²) insulated twin ferrules with a square profile
- Laser etched as shown
- Bottom and sides of pockets and top of indenters polished




WEIGHT: 4.3 oz. [0.12] kg

DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.


DIMENSIONS IN BRACKETS [MM] ARE METRIC.

CD-090	GO / NO (LISH GO GAGE BERS	METRIC GO / NO GO GAGE MEMBERS		
CRIMP POCKET	"G" Dia. (GO)	"NG" Dia. (NO GO)	"G" Dia. (GO)	"NG" Dia. (NO GO)	
1	0.018"	" 0.026" 0,4		0,65mm	
2	0.035"	0.043"	0,90mm	1,10mm	
3	0.051"	0.059"	1,30mm	1,50mm	
4	0.071"	0.079"	1,80mm	2,00mm	
5	0.093"	0.104"	2,35mm	2,55mm	
6	0.110"	0.118"	2,80mm	3,00mm	


Location: Teamcenter	CD-090 DI							
RAWING	CUSTOMER DR							
PANDUIT	TF28309B01_02	10220/ 01	ADDED POLISH AND LASER NOTES AND INDICATED POCKET AND INDENTER.	JADE	ВЈРИ	BWG	5-22-19	02
		20454	(A) WAS 26-10(0,14-6,0); (B) ADD	JADE	ВЈРИ	BLR	3-15-18	01
MATERIAL:	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		AWG/SIZE LASER ETCH; O ADD					
	(.x) ± (.xxx) ± (.xx) ±		AWG COLUMN					
DRAWING NUMBER: TF28309B01	THIRD ANGLE PROJECTION	11042	RELEASED	JADE	BJPU	BLR	11-22-16	00







CROSS SECTION



6

