

2




1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	STRANDED COPPER CONDUCTOR SIZE - AWG		NUMBER OF RIBS	DIMENSIONS - IN [ mm ]				COLOR CODE	WIRE STRIP LENGTH	PANDUIT DIE PART NUMBER DIE SET COLOR & INDEX NUMBER NUMBER OF CRIMPS ( )			
	RUN	TAP		$\pm .02$ [ 0.5 ] A	Q	T MATERIAL THICKNESS $\pm .01$ [ 0.3 ]	$\pm .014$ [ .4 ] V			CT-2001		CT-1700**	CT-920, CT-920CH, CT-2920, CT-930, CT-930CH, CT-940CH*, CT-2940*
CTAPF10-16-C	14 12 10	16-14 16-12 14	-	.41 [ 10.4 ]	.13 [ 3.3 ] $\pm .01$ [ 0.3 ]	.06 [ 1.5 ]	.19 [ 4.8 ]	RED	1/2 [ 12.7 ]	---	CD-2001-8 RED P21 (1)	RED P21 (2)	---
CTAPF8-12-C	10 8	10 12	-	.67 [ 17.0 ]	.20 [ 5.0 ] MAX	.07 [ 1.8 ]	.26 [ 6.6 ]	BLUE	11/16 [ 17.5 ]	---	CD-2001-6 BLUE P24 (1)	BLUE P24 (2)	---
CTAPF6-12-C	8 6	10-8 12-10	-	.67 [ 17.0 ]	.26 [ 6.7 ] MAX	.07 [ 1.8 ]	.32 [ 8.1 ]	GRAY	11/16 [ 17.5 ]	---	CD-2001-4 GRAY P29 (1)	GRAY P29 (2)	---
CTAPF4-12-C	6 5,4	8-6 12-8	1	1.25 [ 31.8 ]	.29 [ 7.3 ] MAX	.07 [ 1.8 ]	.40 [ 10.2 ]	BROWN	1-5/16 [ 33.3 ]	CDM-2001-2 BROWN P33M (1)	CD-2001-2 BROWN P33 (2)	BROWN P33 (4)	CDM-920-2 BROWN P33M (1)
CTAPF3-12-C	5,4 3	6-5 12-6	1	1.25 [ 31.8 ]	.32 [ 8.2 ] MAX	.08 [ 2.0 ]	.46 [ 11.7 ]	GREEN	1-5/16 [ 33.3 ]	CDM-2001-1 GREEN P37M (1)	CD-2001-1 GREEN P37 (2)	GREEN P37 (4)	CDM-920-1 GREEN P37M (1)
CTAPF2-12-C	4 3 2	4 5 12-6	1	1.25 [ 31.8 ]	.34 [ 8.7 ] MAX	.08 [ 2.0 ]	.51 [ 13.0 ]	PINK	1-5/16 [ 33.3 ]	CDM-2001-1/0 PINK P42M (1)	CD-2001-1/0 PINK P42 (2)	---	CDM-920-1/0 PINK P42M (1)
CTAPF1-12-C	3 2 1	4-3 5-4 12-5	2	1.82 [ 46.2 ]	.40 [ 10.2 ] MAX	.08 [ 2.0 ]	.57 [ 14.5 ]	BLACK	1-7/8 [ 47.6 ]	CDM-2001-2/0 BLACK P45M (1)	CD-2001-2/0 BLACK P45 (3)	---	CDM-920-2/0 BLACK P45M (1)
CTAPF1/0-12-L	2 1 1/0	4-2 4-3 12-4	2	1.82 [ 46.2 ]	.43 [ 10.9 ] MAX	.09 [ 2.3 ]	.63 [ 16.0 ]	ORANGE	1-7/8 [ 47.6 ]	CDM-2001-3/0 ORANGE P50M (1)	CD-2001-3/0 ORANGE P50 (3)	---	CDM-920-3/0 ORANGE P50M (1)
CTAPF2/0-12-Q	1 1/0 2/0	2-1 3-2 12-3	2	1.82 [ 46.2 ]	.49 [ 12.5 ] MAX	.09 [ 2.3 ]	.71 [ 18.0 ]	PURPLE	1-7/8 [ 47.6 ]	---	CD-2001-4/0 PURPLE P54 (3)	---	CDM-920-4/0 PURPLE P54M (1)
CTAPF3/0-12-Q	1/0 2/0 3/0	1-1/0 2-1 12-2	2	1.82 [ 46.2 ]	.55 [ 14.1 ] MAX	.09 [ 2.3 ]	.81 [ 20.6 ]	YELLOW	1-7/8 [ 47.6 ]	---	CD-2001-250 YELLOW P62 (3)	---	CDM-920-250 YELLOW P62M (1)

NOTES:

1. MATERIAL: COPPER
2. UL ISTD AND CSA CERTIFIED FOR APPLICATIONS UP TO 600V TEMPERATURE RATING 90°C
3. PACKAGING QUANTITY:  
-C = 100  
-L = 50  
-Q = 25



\*CT-940CH AND CT-2940 REQUIRE CD-940-DA ADAPTER FOR CDM-920 DIES  
\*\*CT-1700 CRIMP DIE POCKETS ARE INTEGRATED INTO TOOL HEAD



PART NUMBER		SEE TABLE	
TITLE		NON-INSULATED THIN WALL CTAP CONNECTORS CUSTOMER DRAWING	
ITEM REVISION NAME		N41172BA/06	
DATASET FILE NAME		N41172BA-DC/06A	
		THIRD ANGLE PROJECTION	
MATERIAL		SEE NOTES	
DRAWN BY		DATE	
JHNU		9-27-23	
CHK		JHNU	
SCALE		NONE	
DRAWING NUMBER		N41172BA-DC	
SHEET 1 OF 1		B	

06A	9-27-23	JHNU	JHNU	MRWA	C. REVISED DRAWING NUMBER: N41172BA-DC WAS C41172 B. ADDED TOLERANCES A. CONVERTED TO NX	135175
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

2



1