NetKey[®] Category 6A Punchdown Jack Module



specifications

Category 6A/Class E_A, 8-position keystone jack module shall terminate unshielded twisted 4-pair, 22 – 26 AWG, 100 ohm cable. Punchdown tool properly terminates each conductor for optimum performance. Universal label is color-coded T568A and T568B wiring schemes.



technical information

Category 6A/Class E _A channel and component	Exceeds ANSI/TIA-568.2-D Category 6A and ISO 11801 Class ${\rm E}_{\rm A}$ channel requirements at swept frequencies up to 500 MHz	
performance:	Exceeds ANSI/TIA-568.2-D Category 6A and ISO 11801 Class E_{A} standards at swept frequencies up to 500 MHz	
FCC and ANSI compliance:	Meets ANSI/TIA-1096-A; contacts plated with 50 microinches of gold for superior performance	
IEC compliance:	Meets IEC 60603-7 and IEC 60512-99-002	
PoE and PoH compliance:	Meets IEEE 802.3af/802.3at and 802.3bt type 3 and type 4. Supports Power over HDBaseT up to 100 watts.	
c(UL)us Listed:	UL 1863 (Use as communications circuit accessory); CSA standard C22.2	
	UL 2043 (Suitable for use in air-handling spaces)	
Operating temperature:	-10°C to 75°C (14°F to 167°F)	
RoHS compliance:	Compliant	

key features and benefits

100% performance tested	Confidence that each jack module delivers specified performance		
110 style punchdown termination	Utilizes industry standard termination style and includes wire retention cap		
Modular	Universal keystone jack modules snap in and out of all NetKey Faceplates, Modular Patch Panels, and Surface Mount Boxes for fast moves, adds, and changes		
Alien crosstalk suppression	Innovative MaTriX split foil technology provides superior alien crosstalk performance enabling high density applications		
Individually serialized	Marked with quality control number for future traceability		
Bulk packaging (optional)	25 jacks packaged in one easy to open container, eliminating the time to open each individual package and reducing on-site waste; ideal for high volume installations		

applications

NetKey Category 6A Punchdown Jack Modules provide a cost effective medium for ensuring that network bandwidth needs are easily met today and tomorrow. The NetKey Solution helps organizations efficiently and reliably meet data transmission needs. With certified performance to ISO 11801 and ANSI/TIA-568.2-D Category 6A component standards, this system will support high bandwidth applications such as those required by education, healthcare, finance, and banking.

NetKey Category 6A Jack Module			
Module:	NK6X88M*		
Bulk pack of 25 jack modules:	NK6X88M*-Q		
Termination and Cable	e Prep Tools		
Punchdown tool:	PDT110‡		
Punchdown base:	NKSPB		
JackRapid+ Termination Tool:	JR-PAN-2‡‡		
Cable snipping tool:	CWST		
Cable stripping tool:	CJAST		
Replacement retention cap:	DRWCIW-24		

*To designate a color, add suffix IW (Off White), EI (Electric Ivory), IG (Int'I Gray), WH (White), BL (Black), OR (Orange), RD (Red), BU (Blue), GR (Green), YL (Yellow), AW (Artic White), or VL (Violet).

Terminates the NetKey Keystone Punchdown Jack Module and NetKey Patch Panel. ##Terminates the NetKey Keystone

the second secon

+JackRapid is a trademark of Fluke Networks.


NetKey® Category 6A Punchdown Jack Module

test results


Mechanical Test	Test Method	Measurement	Typical Test Results
Normal Force	ANSI/TIA-1096-A	Load (grams)	>100
Vibration	IEC 512-6d	Circuit Resistance (mOhms)	<40
Shock	IEC 512-6c	Contact Disturbance (microseconds)	<5
Durability	IEC 512-9a	Circuit Resistance (mOhms)	<40
Mating/Unmating	IEC 512-13b	Mating Force (N)	<20
		Un-mating Force (N)	<20
Termination Cycles	IEC 352	Number of Cycles	>20
Mating Cycles	IEC 60603-7	Number of Plug Insertions	>2500


Electrical Test	Test Method	Measurement	Typical Test Results
Low Level Circuit Resistance	IEC 512-2a	Resistance (mOhms)	<20
Dielectric Withstand Voltage	IEC 512-4a	1000 VAC, 1 minute	Passed
Insulation Resistance	IEC 512-3a	Resistance (MOhms)	>500

Environmental Test	Test Method	Measurement	Typical Test Results
Temperature Life	IEC 512-9b	Circuit Resistance (mOhms)	<40
Humidity	IEC 512-11c	Circuit Resistance (mOhms)	<40
Thermal Shock	IEC 512-11d	Circuit Resistance (mOhms)	<40
Climatic Sequence	IEC 512-11a	Circuit Resistance (mOhms)	<40
Flowing Mixed Gas Corrosion	IEC 512-11g	Circuit Resistance (mOhms)	<40



Module
Housing





Dimensions are in inches. [Dimensions in brackets are metric].

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty



For more information Visit us at www.panduit.com Contact Customer Service by email: cs@panduit.com or by phone: 800.777.3300

© 2022 Panduit Corp. ALL RIGHTS RESERVED. NKDS52--WW-ENG 9/2022