

В

A

07-18-23

02-25-13

02-25-13

DATE

07A

06

05

REV

CUSTOMER

A-SIZE

DPOI

JBN

JBN

ΒY

JBN

MRJS

RTFI

СНК

APR

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOMINAL DUCT SIZE (W X H)	A IN (mm)	D IN (mm)	E IN (mm)	F IN (mm)	K IN (mm)	W IN (mm)	H IN (mm)	H TOL (±)	T IN (mm)	T TOL (<u>+</u>)
.5X.5	.63 (16.0)	.38 (9.7)	.37 (9.4)	.80 (20.3)	ON CENTERLINE	.51 (13.0)	.50 (12.7)	.06 (1.6)	.05	.02 (0.4)
.5X1	**	.75 (19.1)	.31 (7.9)	"		.51 (13.0)	1.00 (25.4)	**	.06 (1.4)	**
.75X.75	.88 (22.4)	.56 (14.2)	**	"		.76 (19.3)	.75 (19.1)	**	.05 (1.3)	**
.75X1	77	.75 (19.1)	**	"		**	1.00 (25.4)	**	.06 (1.4)	**
.75X1.5	**	1.20 (30.5)	**	"		**	1.50 (38.1)	**	.07 (1.7)	**
.75X2	**	1.63 (41.4)	**	"		**	2.00 (50.8)	**	.07 (1.8)	.02 (0.6)
1×1	1.14 (29.0)	.75 (19.1)	**			1.02 (25.9)	1.00 (25.4)	ŦŦ	.06 (1.4)	.02 (0.4)
1×1.5	**	1.20 (30.5)	**	"		**	1.50 (38.1)	**	.07 (1.7)	
1X2	**	1.63 (41.4)	**			**	2.00 (50.8)	**	.07 (1.8)	.02 (0.6)
1X3	**	2.63 (66.8)	vv	1.00 (25.4)		**	3.00 (76.2)	.10 (2.5)	.07 (1.8)	**
1×4	**	3.63 (92.2)	ΨŸ			TT	4.00 (101.6)	ŦŦ	.08 (1.9)	**
1.5X1.5	1.64 (41.7)	1.20 (30.5)	.31 (7.9)	.80 (20.3)		1.52 (38.6)	1.50 (38.1)	.06 (1.6)	.07 (1.7)	.02 (0.4)
1.5X2	**	1.63 (41.4)	**			**	2.00 (50.8)	**	.07 (1.8)	.02 (0.6)
1.5X3	**	2.63 (66.8)	**	1.00 (25.4)			3.00 (76.2)	.10 (2.5)	.07 (1.8)	**
1.5X4	**	3.63 (92.2)	**			TT	4.00 (101.6)	vv	.08 (1.9)	**
>= AVAIL,	ABLE	AS "N	S: S()LID V	VALL	DUCT				

EE TABLE - SHEETS 2&3 Α RING DUCT SPECIFICATIONS TYPES "NS", "NE" CUSTOMER DRAWING N NAME D34175BI/07 DATASET FILE NAME PANDUIT D34175BI_DC/07A MRWA SEE SHEET 1 OF 3 132351/00 THIRD ANGLE PROJECTION RGR0 SEE SHEET 1 OF 3 34175-08/06 DRAWING NUMBER MATERIAL RTFI SEE SHEET 1 OF 3 34175-08/05 34175-08 MODIFIED POLYPHENYLENE OXIDE DRAWN BY DATE SCALE SIZE СНК DESCRIPTION ECN BKR А DW 10-29-91 NONE SHEET 2 OF 3

1

В

2

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

	NOMINAL DUCT SIZE (W X H)	A IN (mm)	D IN (mm)	E IN (mm)	F IN (mm)	K IN (mm)	W IN (mm)	H I N (mm)	H TOL (±)	T IN (mm)	T TOL (±)
	2X1	2.14 (54.4)	.75 (19.1)	.31 (7.91)	.80 (20.3)	.50 (12.7)	2.02 (51.3)	1.00 (25.4)	.06 (1.6)	.06 (1.4)	.02 (0.4)
	2X1.5	**	1.20 (30.5)	**	**	**	**	1.50 (38.1)	**	.07 (1.6)	
>	2X2	77	1.63 (41.4)	77	77	ŢŢ	77	2.0 (50.8)	77	.07 (1.8)	.02 (0.6)
	2X3	**	2.63 (66.8)		1.00 (25.41)	ŶŸ	**	3.0 (76.2)	.10 (2.5)	.07 (1.8)	
	2X4	**	3.63 (92.2)	**	ŸŦ	ŸŸ	ŸŦ	4.0 (101.6)	ΥT	.08 (1.9)	
	2.5X3	**	2.63 (66.8)	**	۳۳	.75 (19.1)	2.52 (64.0)	3.0 (76.2)	**	.07 (1.8)	
	3X1	3.14 (79.8)	.75 (19.1)	**	.80 (20.3)	1.00 (25.4)	3.02 (76.7)	1.0 (25.4)	.06 (1.6)	.06 (1.4)	.02 (0.4)
>	3X1.25	**	1.00 (25.4)	۳T	ŤŤ	ŤŤ	ŤŤ	1.25 (31.8)	**	.06 (1.5)	
	ЗХ2	**	1.63 (41.4)	**	ŦŦ	Ť	ŦŦ	2.00 (50.8)	**	.07 (1.8)	.02 (0.6)
	ЗХЗ		2.63 (66.8)	**	1.00 (25.41)	**	**	3.00 (76.2)	.10 (2.5)	.07 (1.8)	
	3X4	**	3.63 (92.2)	**	**	**	**	4.0 (101.6)	**	.08 (1.9)	
	3X5		4.63 (117.6)	.38 (9.7)	1.33 (33.8)	**	**	5.00 (127.0)	T	.09 (2.31)	.03 (0.6)
	4X1.5	4.14 (105.2)	1.20 (30.5)	.31 (7.9)	.80 (20.3)	1.50 (38.1)	4.02 (102.1)	1.50 (38.1)	.06 (1.6)	.07 (1.6)	.02 (0.4)
	4X2	**	1.63 (41.4)	vr	**	**	**	2.0 (50.8)	**	.07 (1.8)	.02 (0.6)
>	4X3	**	2.63 (66.8)	vv	1.00 (25.4)	ΨŦ	ęτ	3.0 (76.2)	.10 (2.5)	.07 (1.8)	
	4X4	**	3.63 (92.2)	**	**	ŸŦ	**	4.0 (101.6)	ŦŦ	.08 (1.9)	**
	4X5	**	4.63 (117.6)	.38 (9.7)	1.33 (33.8)	**	**	5.0 (127.0)	**	.09 (2.3)	.03 (0.8)

>= AVAILABLE AS "NS: SOLID WALL DUCT

MRWA SEE SHEET 1 OF 3

RGR0 SEE SHEET 1 OF 3

RTFI SEE SHEET 1 OF 3

В

Α

07-18-23

02-25-13

02-25-13

DATE

07A

06

05

REV

CUSTOMER

-SIZE

DPOI

JBN

JBN

ΒY

JBN

MRJS

RTFI

СНК

APR

2

PART NUMBER SEE TABLE - SHEETS 2&3 TITLE WIRING DUCT SPECIFICATIONS TYPES "NS", "NE" CUSTOMER DRAWING ITEM REVISION NAME D34175BI/07 DATASET FILE NAME PANDUIT D34175BI_DC/07A 132351/00 THIRD ANGLE 34175-08/06 PROJECTION DRAWING NUMBER MATERIAL 34175-08/05 MODIFIED POLYPHENYLENE OXIDE 34175-08 SCALE SIZE DRAWN BY DATE СНК DESCRIPTION ECN BKR А DW 10-29-91 NONE SHEET 3 OF 3

1

В

А

2