



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT P/N	WEIGHT
SEE SHEET 2	SEE SHEET 2




LEFT VIEW




REAR VIEW



RIGHT VIEW



FRONT VIEW



BOTTOM VIEW

**SPECIFICATION:**


- STANDARD  
 UNIT TYPE: MONITORED SWITCHED  
 ORIENTATION: VERTICAL, 0U FULL  
 OUTLET QTY & TYPE: (18)C13, (6)C19  
 INPUT VOLTAGE: 200-240/346-415VAC  
 INPUT FREQUENCY: 50/60HZ  
 INPUT CURRENT: 16A  
 BREAKER QTY & TYPE: NONE  
 INPUT PHASE: THREE-PHASE(WYE)  
 RATED POWER: 11 kVA  
 INPUT PLUG: IEC 60309 3P+N+E 6H 16A  
 INPUT POWER CORD: SEE SHEET 2 PART NUMBER TABLE  
 REGULATORY STANDARD: RoHS COMPLIANT
- ADDITIONAL:  
 NONE
- ACCESSORIES:  
 DOCUMENTATION KIT  
 PRODUCT SAFETY WARNING SHEET

**NOTES:**

- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSIONS ARE IN [INCHES]
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
- VISIT OUR ON-LINE CATALOG AT [WWW.PANDUIT.COM](http://WWW.PANDUIT.COM) FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
- FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
- DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

**IDENTIFICATION:**

FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: E24E02M-XXYZ



**PLUG / RECEPTACLE BLOCK**



**PLUG**  
 IEC 60309 3P+N+E 6H  
 IP44 (SPASHPROOF)  
 16A, 346-415V MAX RATED INPUT



**RECEPTACLE**  
 IEC 60320 C13  
 10A, 250V MAX RATED OUTPUT



**RECEPTACLE**  
 IEC 60320 C19  
 16A, 250V MAX RATED OUTPUT

00A	08/29/2023	LL	MIM	MJD	INITIAL RELEASE	E24E02M
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		SIGN
		DATE
		PRINT
TITLE <b>INTELLIGENT SERIES PDU E24E02M</b> CONTROL DRAWING		
ITEM REVISION NAME:		<b>PANDUIT</b>
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR: <b>N/A</b>
Tolerance (mm) 0 < L ≤ 50 ±0.5 50 < L ≤ 250 ±1.0 250 < L ≤ 500 ±1.5 500 < L ≤ 1000 ±2.5 1000 < L ≤ 2000 ±4.0		DRAWING NUMBER: <b>E24E02M_DC</b>
THIRD ANGLE PROJECTION	DRAWN BY: LL DATE: 08/29/2023 CHK: MIM SCALE: NONE	SHT 1 OF 2 SCALE: <b>B</b>

2



1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


B

FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
E24E02M	MS PDU, 16A, (18)C13 (6)C19, IEC 60309 3P+N+E 6h IP44-3M, TOP-FED, BLACK	BLACK(RAL 9005)	3M(+254MM/-127MM)[10'(+10"/-5"']	7.2kg

B

A

00A	08/29/2023	LL	MIM	MJD	INITIAL RELEASE	E24E02M
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.				SIGN
				DATE
				PRINT
TITLE <b>INTELLIGENT SERIES PDU E24E02M</b> CONTROL DRAWING				
ITEM REVISION NAME:				<b>PANDUIT</b>
DATASHEET FILE NAME:				
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]				MATERIAL/COLOR: <b>N/A</b>
 Tolerance (mm) 0 < L ≤ 50 ±0.5 50 < L ≤ 250 ±1.0 250 < L ≤ 500 ±1.5 500 < L ≤ 1000 ±2.5 1000 < L ≤ 2000 ±4.0 THIRD ANGLE PROJECTION				DRAWING NUMBER: <b>E24E02M_DC</b>
DRAWN BY	DATE	CHK	SCALE	
LL	08/29/2023	MIM	NONE	SHT 2 OF 2
				SCALE <b>B</b>

A

2



1