







THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
GPB144-X	.36 LB/EACH (159 g/EACH)

- NOTES:
1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
 2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
 3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
 4. MATERIAL:
BASE - POLYCARBONATE
WIRE STRIP - POLYCARBONATE
 5. INSTALLATION REQUIRES SCREWS.



PART NUMBER		GPB144-X	
TITLE			
		GP6 PLUS HIGH DENSITY BASE 144 PAIR	
		CUSTOMER DRAWING	
ITEM REVISION NAME			
M00340BW/AA			
DATASET FILE NAME		MATERIAL : POLYCARBONATE	
M00340BW_DC32/00C			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .010 [.3] .XX ± .03 [.8] ANGLES ±		DRAWING NUMBER: 00340-32	
 THIRD ANGLE PROJECTION			
DRAWN BY	DATE	CHK	SCALE
JBA	4-12-99	WOT	NONE
SHT 1 OF 1			SIZE
			A

2	7-01-14	MDJR	REFR	MMR	B. UPDATED TITLE.	00340-32
1	6-04-14	MDJR	REFR	MMR	A. UPDATED TITLE BLOCK.	00340-32
R	4-12-99	JBA	WOT	CVM	RELEASED TO PRODUCTION	00340-32
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN