




PANDUIT PART #	WIRE RANGE		CYCLE TIME	CRIMPING LENGTH	COMPRESSED AIR SUPPLY	POWER	CAPACITY	DIMENSIONS in. [mm]	WEIGHT
	AWG	[mm ²]							
CP-991	24-12	0.25-4	1.3 s	6 - 12 mm	5 bar / 72 psi	100 - 240 VAC, 50/60 Hz	70 W	16'' x 9.5'' x 19.3'' (405 x 240 x 490 mm)	29kg / 64lb
CP-992	12-8	4-10	1.5 s	10 -12 mm	6 bar / 87 psi				



NOTES, UNLESS OTHERWISE SPECIFIED:

THE CP-991 AND CP-992 ARE AUTOMATIC WIRE STRIPPING AND FERRULE CRIMPING PRESSES THAT ARE INTENDED TO BE USED WITH LOOSE PIECE FERRULES.

GO TO PANDUIT.COM FOR A LIST OF PRODUCTS THAT ARE COMPATIBLE WITH THIS UNIT.

TECHNICAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: 59°F to 95°F (15°C to 35°C)

							TITLE				
							CP-991 & CP-992				
							BOWL FEEDER FERRULE CRIMP PRESS				
							CUSTOMER DRAWING				
							ITEM REVISION NAME				
							00090FAA/01				
							DATASET FILE NAME				
							00090FAA/01_DC/01A				
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]			MATERIAL:	
							.x ± .1 [2.54] .xxx ± .005 [.127]			N/A	
							.xx ± .01 [.25] ANGLES ± 5 °				
										DRAWING NUMBER:	
										00090FAA_DC	
01	10/25/2018	FCHE	BRHA	JADE	ADDED KIT INFORMATION	041964	 THIRD ANGLE PROJECTION				
00	08/28/2018	FCHE	TMR	FCHE	RELEASED	040535					
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SIZE
										N/A	B
									SHT 1 OF 2		

D10100DB/17

B

A


TOOLING KIT INFORMATION				
TOOL	CROSS SECTION AREA AWG (mm2)	DIN COLOR CODE	KIT PART NUMBER	KIT ORDER #
CP-991	24/22 (0.25/0.34)	yellow/ turquoise	CP-991-KIT025	6646
	20 (0.5)	white		INCIUED IN CP-991
	18 (0.75)	gray		
	(1)	red		
	16 (1.5)	black		
	14 (2.5)	blue	CP-991-KIT25	6645
	12 (4)	gray	CP-991-KIT4	6650
CP-992	12 (4)	gray	CP-992-KIT4	6630
	10 (6)	yellow	CP-992-KIT6	6813
	8 (10)	red	CP-992-KIT10	6814

NOTES, UNLESS OTHERWISE SPECIFIED:

EACH TOOLING KIT CORRESPONDS TO SPECIFIC WIRE GAGES
CP-991 BASIC TOOLING KIT COVERS WIRE GAGE SIZES 20-16 AWG (0.5-1.5 MM2), ADDITIONAL KITS MAY BE ORDERED SEPARATELY.
CP-992 DOES NOT INCLUDE A TOOLING KIT, THE REQUIRED KIT MUST BE ORDERED SEPARATELY

The CP-991 AND CP-992 RETROFIT KIT IS A CASE THAT CONTAINS

- FEEDER BOWL
- REVERSING BASE SLEEVE
- CORD-CENTERING FUNNEL
- SLEEVE RECEIVER
- SEPARATION PLATE
- STRIPPING BLADE (NOT REQUIRED FOR CP-991-KIT25)
- CRIMPING JAWS (NOT REQUIRED FOR CP-991-KIT25)

							TITLE					
							CP-991 & CP-992					
							BOWL FEEDER FERRULE CRIMP PRESS					
							CUSTOMER DRAWING					
							ITEM REVISION NAME					
							00090FAA/01					
							DATASET FILE NAME					
							00090FAA/01_DC/01A					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]			MATERIAL:		
							.x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °			N/A		
01	10/25/2018	FCHE	BRHA	JADE	ADDED KIT INFORMATION	041964				DRAWING NUMBER:		
00	08/28/2018	FCHE	TMR	FCHE	RELEASED	040535				00090FAA_DC		
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 2 OF 2	SIZE B

B

A