
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


		WIRE I	RANGE			DIME	NSIONS in. [mm]	TOOL CHART
PANDUIT PART #	TAB SIZE	ENGLISH	METRIC	HOUSING COLOR	MAX. WIRE INSUL. DIA.	.03	.02 W ±	H± .02	PRESSES: CP-851, CP-860, CP-861, CP-870, CP-862
		ENGLISH	INIETRIC			[0,8]	[0,5]	[0,5]	APPLICATOR DIES: CA-800, CA9
DV10-250C	.250 X .032 [6,4 X 0,8]	12-10	4,0-6,0	YELLOW	.23 [5,8]	.95 [24,1]	.29 [7,4]	.12 [3,1]	CD-800-3 CD9-3B

NOTES:

 ${\sf B}$

- 1. USED FOR:
 - A. STRANDED COPPER WIRE ONLY
 - B. 221°F [105°C] MAX. OPERATING TEMPERATURE
 - C. 600 V. MAX. VOLTAGE RATING
- 2. MATERIAL:
 - A. STAMPING: CDA-260 BRASS, TIN PLATED
 - B. HOUSING: VINYL
 - C. SLEEVE: BRASS
- 3. WIRE STRIP LENGTH: 11/32 +1/32 [8,7 +0,8]
- 4. SEE www.panduit.com FOR PACKAGE QUANTITIES INDICATED BY PART NUMBER SUFFIX
- 5. DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT







ZED CFRIFIE

RECOGNIZED E78522

LR31212

A								DISCO TM FEMALE DISCONNECTS, VINYL BARREL INSULATED, FUNNEL ENTRY
								CUSTOMER DRAWING
								N41654BA/04
								N41654BA/04 DATASET FILE NAME N41654BA_DC/04A
								UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]
								.x ± .1 [2.54] .xxx ± .005 [.127] SEE NOTES .xx ± .01 [.25] ANGLES ± 5 °
DA/12	04	10.22.12	JBN	LSM		ADDED METRIC EQUIVALENT. REVISED NOTES. UPDATED DRAWING TO CURRENT STANDARDS.	A41654	THIRD ANGLE PROJECTION A41654
010100	REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY DATE CHK SCALE JKD - N.T.S. SHEET 1 OF 1
_						2		1