

B

A

B

A


2

1


PANDUIT P/N	WEIGHT
P06B48M	5.5kg

20 AMP, DOUBLE - POLE ELECTRO
MECHANICAL SWITCH / BREAKER (3) PLACES


REAR VIEW



TOP VIEW




FRONT VIEW




SIDE VIEW

NOTES:

1. IDENTIFICATION:
- | | |
|--------------------|------------------------|
| UNIT TYPE: | BASIC |
| ORIENTATION: | HORIZONTAL, 1U |
| OUTLET QTY&TYPE: | (6) C19 |
| BREAKER QTY&TYPE: | (3) 20AMP, DOUBLE-POLE |
| INPUT VOLTAGE: | 200-240VAC |
| INPUT CURRENT: | 50A (40A DERATED) |
| INPUT PHASE: | SINGLE-PHASE |
| RATED POWER: | 8.3kVA |
| INPUT PLUG: | HUBBELL CS8265C |
| INPUT CORD LENGTH: | 3m [10'] |
2. ACCESSORIES:
- POCKET GUIDE
- QTY: (4) M6 X 12 PAN HEAD MACHINE SCREWS
- QTY: (4) M6 CAGED NUT
3. RoHS COMPLIANT
4. VISIT PANDUIT'S ON-LINE CATALOG AT WWW.PANDUIT.COM FOR ADDITIONAL PRODUCT INFORMATION CONTAINED IN THE SPECIFICATION SHEET AS WELL AS A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
5. MAXIMUM ALLOWABLE INPUT POWER = 8.3 kW
6. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES





PLUG
50 AMP, 250V
TWIST LOCK
NEMA CS-8265C



SIX (6)
RECEPTACLES
16 AMP, 250V
STRAIGHT BLADE
IEC 60320/C19

01B	08/21/2017	JIANG	MIM	EDM	REVISED TOLERANCES	P06B48M
01A	06/28/2017	JIANG	MIM	EDM	INITIAL RELEASE	P06B48M
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY		SIGN	
		DATE	
		PRINT	
TITLE			
BASIC SERIES PDU P06B48M CUSTOMER DRAWING			
ITEM REVISION NAME			
DATASHEET FILE NAME:			
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR:	
 THIRD ANGLE PROJECTION Tolerance(mm) 0<L<50 ±0.5 50<L<250 ±1.0 250<L<500 ±1.5 500<L<1000 ±2.5 1000<L<2000 ±4.0		N/A	
		DRAWING NUMBER:	
		P06B48M_DC	
DRAWN BY	DATE	CHK	SCALE
JIANG	05/24/2017	SEAN	NONE
		SHT 1 OF 1	
		SCALE B	

2

1