

PANDUIT <del>X</del> PART NO.	BUNDLI MIN (mm)	E DIA. MAX <sup>in</sup> (mm)	A in. (mm)	B in. (mm)	C in. (mm)	D in. (mm)	E in. (mm)	F in. (mm)	G ∅ in. (mm)	MIN. LOOP Ibs TENSILE (N)	CROSS- Section	TIP STYLE	WEIGHT Ibs/100pcs (g)
SC8-50-S10	.12 (3.0)	1.85 (47)	.051 (1.3)	.190 (4.8)	.811 (20.6)	.213 (5.4)	.335 (8.5)	7.87 (200)	.205 (5.2)	50 (222)	STANDARD	CURVED	.367 (166)
SC15-120-S25	.28 (7.0)	1.85 (47)	.071 (1.8)	.30 (7.6)	.929 (23.6)	.276 (7.0)	.496 (12.6)	14.96 (380)	.224 (5.7)	120 (534)	LIGHT HEAVY	STRAIGHT	1.371 (622)

NOTE:

SEE WWW.PANDUIT.COM FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL, PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE.

						2		1	-		
D10100	REV	DATE	BY	СНК	APR	DESCRIPTION	ECN	ACC 2-27-17 JSWA NONE SHT 1 OF 1			
DA/16	00	3/9/17	ACC	JSWA	JADE	DRAWING RELEASED	012502	THIRD ANGLE PROJECTION DOOD92FB0_DC			
	01A	05/21/2021	JBN	MRJS	JADE	CORRECTED MAX. BUNDLE DIA. TO 1.85/47 WAS 1.97/50	101539	.X ±XX ± .020(.51) NYLON 6.6			
								UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]			
								00092FB0/01			
								STRONGHOLD CLAMP TIE			
								TITLE			