


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	MATERIAL	LABELS PER SHEET	SHEET PER PKG	STD. PKG. QTY.
S100X400YAJ	GYM13 OR GYM6	14	72	1000



1.00 ± 0.062  
[25.4 ± 1.57]  
TYP. 7 PLCS.

1.00 ± 0.062  
[25.4 ± 1.57]  
TYP. 2 PLCS.

4.00 ± 0.062 [101.6 ± 1.6]  
TYP. 2 PLCS.

11.00 ± 0.062 [279.4 ± 1.6]

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
4	8/9/2022	JEFP	DAPE	MSAD	CHANGED TO GMY13 OR GMY6	GAECN06570
3	9/11/2020	RVU	RCMC	JHAC	GYM13 WAS GYM6. UPDATE LABELS. UPDATE TEMPLATE DWG.	GAECN05753
2	10/29/09	RVU			UPDATE ON TOLERANCES. ADD +/- .062.	5898
1	8/12/08	RVU			CHG. FORMAT FROM 'B' TO 'A' SIZE. TITLE AREA TOL. INCORRECT.	5516
0	6/29/06	RVU			DRAWING RELEASE. MATERIAL WAS GYM2.	4568
A	9/22/04	RVU			ENGINEERING RELEASE.	0000

TITLE					
OPTIMUM SELF-LAMINATING S100X400YAJ LASER INKJET PRINTABLE LABELS					
CUSTOMER DRAWING					
ITEM REVISION NAME		100472CG/08			
DATASET FILE NAME		100472CG_DC_C10207/08A			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]				<b>PANDUIT</b>  MATERIAL:  <b>SEE TABLE</b>  DRAWING NUMBER:  C10207	
.x ± .12 [ 3.05 ]		.xxx ± .025 [ .635 ]			
.xx ± .062 [ 1.57 ]		ANGLES ±			
		THIRD ANGLE PROJECTION			
DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	
RVU	9/22/04	JHAC	NTS	A	

D10100DA/20