
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER*	A DIA.	MT'G RIVET	MT'G SCREW	FOR USE WITH THE FOLLOWING PANDUIT CABLE TIES	WEIGHT lbs/100 pcs (g)/100 pcs
LHMS-S5-	0.125 0.135	1/8	#5	M = MINATURE	0.56 (254.24)
LHMS-S6-	0.140 0.150	9/64	#6	I = INTERMEDIATE	0.56 (254.24)
LHMS-S10-	0.190 0.195	3/16	#10	S = STANDARD	0.54 (245.16)

 B

NOTES:

- 1. SEE CURRENT PRICE SHEET, SEE www.panduit.com
 FOR CURRENT PART NUMBER SUFFIX DESIGNATION AND FOR
 PACKAGE SIZE AND PART COLOR.
- 2. CAN SUBSTITUTE #5 SCREW FOR A #6 SELF THREADING SCREW.
- 3. CAN SUBSTITUTE #6 SCREW FOR A #8 SELF THREADING SCREW.
- 34. BAG MAY CONTAIN EXTRA PIECES TO COMPENSATE FOR VARIANCE IN THE PACKAGING PROCESS. PANDUIT ASSURES MINIMUM PIECE COUNT AS STATED ON THE BAG.



								LHMS
Δ								LIGHTENING HOLE MOUNT
								CUSTOMER DRAWING
								G03597GG/02 DATASET FILE NAME C03507CC DC CP0330PT 03/03C
	3	1/18/2021	RVU	RMHI	JADE	REBUILD MODEL AND UPDATE DWGS. 1.100 WAS 1.084. ADDED NOTE 4. UPDATE NOTES.	GAECN05683	MATERIAL:
	2	6/26/01	LGG			CHG DIM ON 'A' FOR LHMS-S5 WAS .125/.130. ADD REF & & CHG DIM FROM 1.100 TO 1.084.	GB0239BT	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .05 [1.3] .xxx ± .010 [0.25] NYLON 6/6
	1	6/26/01	LGG			UPDATED FOR WEB.	GB0239BT	.XX ± .02 [0.5] ANGLES ± 5 °
JA/20	R	5/03/95	CBJ			INITIAL RELEASE.	GB0239BT	THIRD ANGLE PROJECTION GB0239BT
0101000	REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	CBJ 5/03/95 JHAC 1:1 SHT 1 OF 1
								4