

Pan-Steel® MS75 Metal Strapping System

Mechanical fastening applications demand high quality systems that can withstand harsh environments while maintaining a safe and secure physical infrastructure. Severe weather, intense UV rays, high vibration, and galvanic corrosion are all variables that can sacrifice performance and create safety hazards. Panduit offers innovative solutions that provide reliable fastening of critical components which allows businesses to minimize risk and enhance productivity.

The Pan-Steel® MS75 Metal Strapping System is now available in 201 and 316 stainless steel to deliver maximum performance, high strength, and enhanced job site safety, ideal for the Sign and Signal, Oil and Gas, and Industrial markets. Designed to work together in extreme conditions, the MS75 metal strapping, buckles, and installation tool reduce installation time by as much as 50%, when compared to competitive offerings. This system is part of the complete range of harsh environment solutions available from Panduit.



Hooked Clamping Tab Provides full coverage of cut end of strap for enhanced safety

> Buckle Screwdriver Slot Allows use of screwdriver for buckle closure for a simple quick installation

Buckle Locking Tabs Patented
Improved locking mechanism
for higher strength



Buckle Bridge Teeth Deliver additional body slip resistance for optimum strength

Key Features

Benefits

MS75 Strapping and Buckles								
Buckle locking tabs	Improved locking mechanism for higher strength							
Buckle screwdriver slot	Allows use of screwdriver for buckle closure for a simple, quick installation							
Hooked clamping tab	Provides full coverage of cut end of strap for enhanced safety							
Buckle bridge teeth	Deliver additional body slip resistance for optimum strength							
Fully assembled 201 stainless steel discrete lengths	Eliminates assembly, reducing installation time by as much as 50%, when compared to competitive designs							
Weather resistant packaging for coils	Maintains package integrity when compared to the traditional cardboard carton for improved water resistance and durability							
Smooth surfaces and rounded edges	Assures worker safety and bundle protection from abrasion during and after installation							
Compatible with industry standard tools	No new installation tools are required							
BT75SDT MS75 Strapping Installation T	001							
Screw drive tension mechanism	Provides high tension to secure bundle with minimal handle effort, for improved productivity							
Robust design	Heavy duty construction offers a long term service life							

Pan-Steel® MS75 Metal Strapping System

Simple 5-Step Installation Process Reduces Installation Time and Installed Costs



1) Place strap around the material, insert tail of strap through buckle. Pull strapping tight and bend up to hold in place.



2) Insert tail of strapping into tool nose section. Rotate handle to tension.



3) After tensioning, raise tool 90° – 120° over buckle and pull down on cutter lever, cutting strap.




4) Remove tool, press cut end down toward retaining tab.



5) Using a flathead screwdriver, bend retaining tab down and over cut end.



Ordering Information









MS75 Strapping in four Discrete Lengths

MS75 Strapping in Weather Resistant Packaging

MS75 Buckles

MS75 Installation Tool

	Max. Bundle Diameter Single Double Loop Loop			Length Strap Breaking Strength				Min. Bundle Diameter		Width		Thickness		Recommended	Std. Pkg.	
Part Number	ln.	mm	In.	mm	ln.	mm	Lbs. N		In.	mm	ln.	mm	ln.	mm	Installation Tool	Qty.^
MS75 Metal Strapp	ing –	Discre	ete L	engths	s (Stai	inless	Steel Type :	201 Only)								
MS4W75T30-Q2	4.0	102	2.0	51	20.2	513	2400	10656	2.0	51	0.75	19.1	0.03	0.76	BT75SDT	25
MS6W75T30-Q2	6.0	152	3.0	76	26.5	673	2400	10656	2.0	51	0.75	19.1	0.03	0.76	BT75SDT	25
MS8W75T30-Q2	8.0	203	4.0	102	32.7	831	2400	10656	2.0	51	0.75	19.1	0.03	0.76	BT75SDT	25
MS10W75T30-Q2	10.0	254	5.0	127	39.0	991	2400	10656	2.0	51	0.75	19.1	0.03	0.76	BT75SDT	25

		Length		Strap Breaking Strength		Min. Bundle Diameter		Width		Thickness		Recommended Installation	Used with	Std.
Part Number	Material	ln.	n. M Lbs. N		ln.	mm	ln.	mm	In. mm		Tool	Buckle	Qty.^	
MS75 Metal Stra													-	
MSW75T30-CR2	Stainless Steel Type 201	100	30.5	2400	10656	2.0	51	0.75	19.1	0.03	0.76	BT75SDT	MSBW75-C2	1
MSW75T30-CR6	Stainless Steel Type 316	100	30.5	2400	10656	2.0	51	0.75	19.1	0.03	0.76	BT75SDT	MSBW75-C6	1

		Width							
Part Number	Material	ln.	mm	Part Description	Pkg. Qty.^				
MS75 Metal Strapp	ing – Buckles								
MSBW75-C2	Stainless Steel Type 201	1.64	41.8	Individual buckles used with 3/4" custom length strapping.	100				
MSBW75-C6	Stainless Steel Type 316	1.64	41.8	Individual buckles used with 3/4" custom length strapping.	100				

BT75SDT Installation Tool for MS75 Strapping

				4
Part Num	ber	Part Description	Std. Pkg. Qtv.^	
BT75SDT		Installation tool for use with .75" width strapping only. Tensions and cuts strapping. Screwdriver required for buckle closure not included.	1	

^Order number of pieces required in multiples of Standard Package Quantity.

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA Markham, Ontario cs-cdn@panduit.com Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK cs-emea@panduit.com Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore cs-ap@panduit.com Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan cs-japan@panduit.com Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico cs-la@panduit.com Phone: 52.33.777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia cs-aus@panduit.com Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com or by phone: 800.777.3300 and reference SSCB26

© 2015 Panduit Corp. ALL RIGHTS RESERVED. Printed in the U.S.A. SSCB27--SA-ENG Replaces SA-SSCB26 12/2015

