


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES, UNLESS OTHERWISE SPECIFIED:

PANDUIT CT-1014 TOOL:

TOOL WEIGHT: 27.1 oz. [0.77] kg

**Crimps Panduit #20 - #14 AWG Disco-Lok
Locking Female Disconnects.**

**Provides UL Listed and CSA Certified
terminations with applicable Panduit terminals.**

**DIMENSIONS SHOWN IN BRACKETS [] ARE
METRIC, AND ARE FOR REFERENCE ONLY.**

CRIMP POCKET AWG / mm ²	ENGLISH GO / NO GO GAGE MEMBERS		METRIC GO / NO GO GAGE MEMBERS	
	"G" Dia. (GO)	"NG" Dia. (NO GO)	"G" Dia. (GO)	"NG" Dia. (NO GO)
22-18/0,5-1,5	.077"	.087"	1,96mm	2,21mm
16-14/1,5-2,5	.093"	.103"	2,36mm	2,62mm



NOTE: In the interest of higher quality and value, Panduit products are continually being improved and updated. Consequently, pictures shown may vary from the product received.

							CT-1014 Contour Crimp™ Crimping Tool CUSTOMER DRAWING	
							ITEM REVISION NAME:	
							TP28306B01_00	
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:	
							(.x) ± --- (.xxx) ± --- (.xx) ± --- ANGLES ± ---	
							THIRD ANGLE PROJECTION	
							DRAWN BY: BLR	
							DATE: 11-18-16	
							CHK BJPU	
							SCALE NONE	
							SHT 1 OF 1	
							SIZE B	
							DRAWING NUMBER: TP28306B01	
00	11-18-16	BLR	<i>BJPU</i>	<i>JADE</i>	RELEASED	10928		
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN		