



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




10.1
[257]

1.5
[38]

82.8
[2104]



DOOR ENGAGED



DOOR DISENGAGED

PANDUIT P/N

WEIGHT

PED10B1

13.3 LBS/EACH
6.0 Kg/EACH

NOTES:

1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
2. COMPONENTS:
1-HIGH CAPACITY VERTICAL DOOR-10"
2-PED DOOR BRACKET-10"
3. DIMENSIONS IN PARENTHESIS ARE METRIC.

TITLE		PATCHRUNNER HIGH CAPACITY VERTICAL DOOR-10" (PED10B1) CUSTOMER DRAWING	
ITEM REVISION NAME		11V235AG/02	
DATASET FILE NAME		11V235AG_DC/02A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL: STEEL	
DRAWN BY FGR		DATE 7/16/12	
CHK BAME		SCALE NONE	
THIRD ANGLE PROJECTION		DRAWING NUMBER: 11V235AG-DC	
SHT 1 OF 1		A	

02A	4/8/13	FGR	BAME	CMK	DRAWING RELEASED	11V235AG-DC
01A	2/5/13	FGR	BAME		DRAWING RELEASED	11V235AG-DC
00A	7-16-12	FGR	BAME		DRAWING RELEASED	11V235AG-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN