

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NUMBER*	WEIGHT bs/100 pcs (g)/100 pcs	USE WITH ANY OF THESE CABLE TIE CROSS-SECTIONS		
SGABM25-A ABM25		M, I, S		
SGABM25-AT ABM25B	0.30 (140)	SG100M, SG150I, SG200S, SG250S, SG300S, SG370S		
SGABM25-AV		303003, 303703		




ADHESIVE BACKING: (-A , -AT) RUBBER OR ACRYLIC BASED ADHESIVE PRESSURE SENSITIVE FOAM TAPE 0.04 [1.0] THICK WITH A PROTECTIVE SENSITIVE FUMM TAFE 0.04 II.01 HILD WITH A CLEAN LINER, MOUNT IS DESIGNED TO SUPPORT 0.50 lbs (227g) MAX.

WEIGHT ON A CLEAN DRY SMOOTH SURFACE.

* (-AV) HIGH BOND ACRYLIC BASED ADHESIVE PRESSURE SENSITIVE

FOAM TAPE 0.040 (1.0) THICK WITH A PROTECTIVE LINER. MOUNT IS DESIGNED TO SUPPORT 1.0 Ibs (453.0g) MAX. WEIGHT ON A CLEAN DRY SMOOTH SURFACE.

NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFOMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.



NOTES

- 1. SEE www.panduit.com FOR PART
 NUMBER SUFFIX DESIGNATION FOR
 PACKAGE SIZE AND COLOR.
 2. THE '-A' SUFFIX REPRESENTS RUBBER
- ADHESIVE. THE '-AT' SUFFIX REPRESENTS ACRYLIC ADHESIVE. THE '-AV' SUFFIX REPRESENTS HIGH BOND ACRYLIC ADHESIVE.
- 3. SUPPLIED IN STRIPS OF TWO.
- 4. THE'-A' MOUNT HAS A MAXIMUM CONTINUOUS OPERATING TEMPERATURE OF 120°F (49°C). THE '-AT' MOUNT HAS A MAXIMUM CONTINUOUS OPERATING TEMPERATURE OF 180°F (82°C). THE '-AV' MOUNT HAS A MAXIMUM CONTINUOUS OPERATING TEMPERATURE OF 200°F (93°C). 5. HOLE FOR STANDARD #6 FLAT HEAD SCREW.

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS

							cad filename/layers 10B015BE_DC_GB0239LS/06						
6	4/24/23	JEFP	KLN	ADDED "REF" NOMENCLATURE TO THE .40" REFERENCE DIMENSION	GAECN0675	6		MSAD			DUIT corp.	TINLEY PARK, ILLINO	ıIS
5	4/17/23	JEFP	KLN	CHANGED 0.42" DIMENSION TO .40" AND MADE IT A REFERENCE DIMENSION	GAECN06751	5		MSAD		SGABM25-A, SGABM25-AT, SGABM25-AV & ABM25, 25B FOUR-WAY MOUNT			
4	8/24/10	JADE	MJVE	ADDED PANDUIT WEBSITE TO NOTE 1; CHANGED PART NUMBER IN TITLE BLOCK AND CAD FILE NAME IN TITLE BLOCK	GB0239LS	4	MJVE			UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±0.05 [1.3] (.XXX) ±0.010 [0.25]		UNLESS OTHERWISE SPECIFIED,	
010	11-6-09	TMSA		ADDED PART NUMBER SGABM25-AV	GB0239LS	010						IN INCHES, THIRD ANGLE PROJECT	CTION.
018	12/16/08	PSG		UPDATED WEIGHT	GB0239LS	018				DRAWN BY TMSA	MAT'L:	scale NONE	
1	6/12/06	JAD		UPDATE CABLE TIE CALLOUTS	GB0239LS	1				DATE 8/24/05	NYLON 6/6	DRAWING NO.	DWG
REV	DATE	ВҮ	СНК	DESCRIPTION	ECN -	R	CUST	SUP		CHK 'D		GB0239LS	SIZE