

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	DIMENSIONS		
	'A' DIA	'B' DIA	'C' ± 0.130
RPBSC1-	.034	.429 .445	5/8
RPBSC3-			2 5/8
RPBSC6-			5 5/8
RPBSC12-			11 5/8



NOTES:

- 1. MATERIAL TO BE .035 DIA. HARD DRAWN SPRING STEEL. (C-1045 TO C-1065) TYP.
- 2. FINISH: RUSTPROOFING, PHOSPHATE COAT AND OIL.
- 3. PARTS MUST BE FREE OF BURRS, DIRT, GREASE AND EXCESSIVE OIL.
- 4. LOAD SPECS. (LENGTH OVER COILS "L")

 PRELOAD FORCE .3 LBS. @ 10% EXTENSION.

 2 LBS. FORCE MAX. @ 100% EXTENSION.
- 5. FOR COMPLETE INSPECTION INSTRUCTIONS SEE I.I. WA-172.

CAD FILENAME/LAYERS GI0145EA_PI_PBSC_01 CORP. TINLEY PARK, ILLINOIS RPBSC EXTENSION SPRING INSPECTION DRAWING UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION DRAWN BY JRL MAT'L: 5/17/04 JAD TOL FOR DIM C WAS +/- 1/32 GIO145EA 1 NONE DRAWING NO. DWG SPRING WIRE 4/19/93 |4/19/93|JRL INITIAL RELEASE GIO145EA R GI0145EA CHK 'D CHK DATE ВҮ DESCRIPTION ECN - R CUST SUP QC