

## Dura-Ty™ Cable Ties

Dura-Ty™ Cable Ties are used to secure and route cables in outdoor power and communication applications. The acetal material provides excellent ultraviolet resistance, strength, and durability for a long service life. The tie design includes double stainless steel locking bars to ensure consistent and reliable cable tie operation. Dura-Ty™ Cable Ties are available in two cross sections, a range of discrete lengths, and cut-to-size rolls for application flexibility. The Heavy cross section features a robust head design that allows the tie to be tightened over a wide range of angles for a safe and reliable installation, and it incorporates a textured strap surface that improves gripping ability. The Extra-Heavy cross section meets Telcordia TR-TSY-000789 guidelines for lashed cable supports. Dura-Ty™ Cable Ties along with Panduit cable tie installation tools and stackable aerial cable spacers are the ideal solution for outdoor bundling applications.



### Key Features


### Benefits

<b>Acetal material</b>	Provides twenty plus years weatherability life for tough outdoor applications; high impact resistance, and strength
<b>Double stainless steel locking bars</b>	Offer a durable locking mechanism for consistent cable tie operation; high tensile strength
<b>Robust head design*</b>	Allows tie to be tightened over a wide range of angles for application flexibility
<b>Textured strap surface*</b>	Improved grip makes it easier to handle and install the cable tie
<b>Flexible strap body*</b>	Permits cable tie to easily conform to irregular bundle shapes while maintaining loop tensile strength; easy to use
<b>Convenient reel dispenser pack</b>	Allows installer to cut-to-size for customized field applications; part number reduction contributes to reduced inventory costs
<b>Discrete length cable ties**</b>	Offers several pre-cut sizes for fast installation


\*Heavy cross section only  
 \*\*Extra-Heavy cross section only



**Heavy Cross Section**  
 Textured strap body and robust head design for reliable installations



**Dura-Ty™ Kit**  
 Recyclable dispenser pack has through-hole for attaching to belt plus storage area for bag of heads



**Stackable Aerial Cable Spacer**  
 Designed for use in parallel or perpendicular applications with Dura-Ty™ Cable Ties

# Dura-Ty™ Cable Ties

## Strapping, Heads, and Kit – Allows User to Customize Length

Standard Part Number	Description	Strap Length Ft. (mm)	Strap Width In. (mm)	Strap Thickness In. (mm)	Min. Loop Tensile Strength Lbs. (N)	Head Height In. (mm)	Head Width In. (mm)	Recommended Tools	Pkg.* Qty.
<b>Heavy Cross Section</b>									
<a href="#">DTRH-LR0</a>	Cable tie strapping (reel)	50.0 (15)	0.331 (8.40)	0.064 (1.63)	200 (890)	—	—	GTH-E, GS4EH-E, ST3EH, STHV, STH2	1
<a href="#">DTHH-Q0</a>	Cable tie heads (bag of 25)	—	—	—	—	0.393 (9.98)	0.557 (14.15)	—	25
<b>Extra-Heavy Cross Section</b>									
<a href="#">DTREH-LR0</a>	Cable tie strapping (reel)	50.0 (15)	0.500 (12.70)	0.059 (1.50)	250 (1112)	—	—	GS4EH-E, ST3EH	1
<a href="#">DTHEH-Q0</a>	Cable tie heads (bag of 25)	—	—	—	—	0.490 (12.45)	0.718 (18.24)	—	25
<a href="#">DTKEH-0</a>	Kit containing 50' reel of strapping and 25 cable tie heads	50.0 (15)	0.500 (12.70)	0.059 (1.50)	250 (1112)	0.490 (12.45)	0.718 (18.24)	GS4EH-E, ST3EH	1

## Discrete Lengths – Pre-Cut Sizes

Standard Part Number	Length In. (mm)	Width In. (mm)	Thickness In. (mm)	Head Height In. (mm)	Head Width In. (mm)	Max. Bundle Diameter In. (mm)	Min. Loop Tensile Strength Lbs. (N)	Recommended Tools	Pkg.* Qty.
<b>Extra-Heavy Cross Section</b>									
<a href="#">DT4EH-L0</a>	13.5 (343)	0.495 (12.57)	0.059 (1.50)	0.490 (12.45)	0.718 (18.24)	3.8 (98)	250 (1112)	GS4EH-E, ST3EH	50
<a href="#">DT8EH-Q0</a>	27.0 (686)					8.0 (203)			25
<a href="#">DT14EH-L0</a>	48.0 (1219)					14.0 (355)			50
<a href="#">DT28EH-C0</a>	96.0 (2438)					28.0 (711)			100
<a href="#">DT44EH-C0</a>	144.0 (3658)					44.0 (1117)			

## Stackable Aerial Cable Spacer – Weather Resistant Polypropylene



- Each spacer snaps into another to increase spacer heights by 1/2" increments
- Designed for use in parallel or perpendicular applications

Standard Part Number	Used with Cable Ties	Length In. (mm)	Width In. (mm)	Height In. (mm)	Pkg.* Qty.
<a href="#">SACSS0-T100</a>	All Dura-Ty™ Cable Ties	2.08 (52.8)	1.16 (29.5)	0.71 (18.0)	200

## Cable Tie Installation Tools

Part Number	Used with Cable Ties	Weight oz. (g)	Part Description	Pkg.* Qty.
<a href="#">GTH-E</a>	DTRH, DTKH	11.9 (337)	Tool controlled tension and cut-off. Ergonomic design.	1
<a href="#">STHV</a>		12.0 (341)	Installer controlled tension and cut-off. Steel construction.	
<a href="#">STH2</a>		2.5 (71)	Installer controlled tension and cut-off. Plastic construction.	
<a href="#">GS4EH-E</a>	DTRH, DTKH, DT4EH, DT8EH, DT14EH, DT28EH, DT44EH, DTREH, DTKEH	15.34 (435)	Tool controlled tension and cut-off. Ergonomic design.	
<a href="#">ST3EH</a>		9.0 (256)	Installer controlled tension and cut-off. Steel construction.	

\*Order the number of pieces required, in multiples of standard package quantity.

### WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA  
Markham, Ontario  
cs-cdn@panduit.com  
Phone: 800.777.3300

PANDUIT EUROPE LTD.  
London, UK  
cs-emea@panduit.com  
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.  
Republic of Singapore  
cs-ap@panduit.com  
Phone: 65.6305.7575

PANDUIT JAPAN  
Tokyo, Japan  
cs-japan@panduit.com  
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA  
Guadalajara, Mexico  
cs-la@panduit.com  
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.  
Victoria, Australia  
cs-aus@panduit.com  
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to [www.panduit.com/warranty](http://www.panduit.com/warranty)

For more information

Visit us at [www.panduit.com](http://www.panduit.com)

Contact Customer Service by email: [cs@panduit.com](mailto:cs@panduit.com)  
or by phone: 800.777.3300

**PANDUIT**®

©2023 Panduit Corp.  
ALL RIGHTS RESERVED  
CTCB61-WW-ENG  
Printed in the U.S.A.  
4/2023