# PanZone® TrueEdge Vertical Wall Mount Enclosure



## specifications

The wall mount enclosures shall mount active equipment vertically in a low profile, on-wall configuration. The enclosure shall be capable of mounting up to 36" of active equipment depth and have the capability of vertical patching. Equipment brackets shall be adjustable for accommodation of server and/or switch applications. Enclosure shall be engineered to allow proper ventilation for use with various networking equipment including, but not limited to, Power over Ethernet (PoE) Switches and Uninterrupted Power Supplies (UPS). The vertical wall mount enclosure shall have a perforated top and bottom, which can be removed, for optimal airflow, heat dissipation, and equipment access. The optional filter-kit shall provide a NEMA 1 rating.



### technical information

Part Number	Active RU	Passive RU	Height In. (mm)	Width In. (mm)	Depth In. (mm)	Load Capacity (Lbs.)
WME3BL	3 RU	3 RU	42 (1066.8)	28.6 (726.44)	9.5 (241.3)	200
WME6BL	6 RU	6 RU	42 (1066.8)	28.6 (726.44)	14.8 (375.92)	300
WME9BL	9 RU	9 RU	42 (1066.8)	28.6 (726.44)	19.9 (506)	400
Packaging:	Base, door, horizontal passive equipment brackets, E-rail equipment brackets, locking swing handle, (includes 2 Keys), edge grommet, Tak-Ty® Hook & Loop Cable Ties, door hinges					
Material:	16 gauge galvanized steel, power coated Black					
Filter-Kit:	Easy to retrofit on an existing TrueEdge enclosure. The filter kit provides a foam filter that wraps and covers the top perforations of the enclosure. This Filter-Kit eliminates any excess dust and debris from entering through the top of the enclosure. Filter-Kit does not add an IP or NEMA rating to the enclosure.					liminates any

# key features and benefits

Low profile:	Provides an efficient way to deploy switch and server systems in an open architecture environment		
Configurable:	Used as a telecommunications room, extension of the telecommunications room, micro data center, or edge deploy		
Thermal capacity:	Perforated top and bottom optimizes airflow for improved dissipation of heat generated from active equipment		
Adjustable equipment rails:	Increases usable enclosure depth to 36" of available space within the enclosure for active equipment while maintaining the ability to mount pate panels; provides user preferred installation capabilities and a variety of configurations based on application		
Removable and secure top cover and bottom plate:	Allows for easy installation and provides secure access to installed equipment		

# applications

The PanZone TrueEdge Vertical Wall Mount Enclosure provides a comprehensive architecture that allows up to 36" of active equipment depth to be mounted in a low-profile application. This low-profile wall mount enclosure houses traditional horizontal equipment vertically on a wall while minimizing network infrastructure investment to eliminating a rack or cabinet (TR in a BOX and Micro Data Center). The structurally engineered design provides for up to 36" of active equipment depth space. It has a premium static load rating with up to 400 lbs. and best-in-class thermal ratings to eliminate equipment failure.

- Scalable offering a variety of configurations for servers, switches, and edge computing
- Strong able to withstand optimum load capacity for deployments of server and switch configurations
- Configurable offered in 3 RU active (3 RU passive), 6 RU active (6 RU passive), or 9 RU active (9 RU passive) allowing customization opportunities to fit the needs of the user and deliver storage solutions that make a difference

#### Vertical Wall Mount Enclosure

3 RU enclosure: WME3BL 6 RU enclosure: WME6BL 9 RU enclosure: WME9BL

#### **Enclosure Accessories**

Filter Media

 Replacement:
 WME\*-FR

 Filter-Kit:
 WME\*BL-FKIT

 6 RU:
 WME6BL-FKIT

 9 RU:
 WME9BL-FKIT

Vertical 1 RU Bracket: WME0UB

Active Equipment Rails:

3 RU: WME3ERAIL
6 RU: WME6ERAIL
9 RU: WME9ERAIL
Horizontal 1 RU Bracket: WME\*1RU

Ground kit: WMEGK
Fan kit: PZAEFAN
Euro fan kit: PZAEFK-E

Mini-Com Modular

Patch Panel: CPP^FMWBLY

#### SmartZone™ Monitoring Equipment

PDU: P08D09M

**SmartZone** 

Security Handle: ACF05 ACF06


SmartZone Security
Handle Temperature and

Door Sensor: ACF10


\*Avaliable in lengths 3', 6', or 9. Replace special character with numeric value to search www.panduit.com.

^Available in 24 and 48 ports. Replace special character with numeric value to search www.panduit.com.


# **PanZone® TrueEdge Vertical Wall Mount Enclosure**



#### WME6BL





#### WME9BL




Dimensions are in **inches**. (Dimensions in **parenthesis** are metric).

# PanZone® TrueEdge Vertical Wall Mount Enclosure







# **WORLDWIDE SUBSIDIARIES AND SALES OFFICES**

PANDUIT US/CANADA Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575

PANDUIT JAPAN Tokyo, Japan Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty



or by phone: 800.777.3300