

TX6™ 10Gig™ Keyed UTP Patch Cords

SPECIFICATIONS

Category 6/Class E keyed UTP patch cords shall be constructed of 24 AWG stranded copper cable with a keyed modular plug on one end and a non-keyed modular plug on the other end. Keyed modular plugs shall be mechanically keyed with color-specific positive and negative keying features to prevent unintentional mating with unlike keyed or non-keyed jack modules. Copper conductors in patch cable shall be twisted in pairs and separated by a quadrant separator. All four pairs shall be surrounded by a flame retardant jacket. Patch cords shall be used in all work area outlets and patch panels and shall be compatible with both T568A and T568B wiring schemes.



TECHNICAL INFORMATION

Category 6/Class E_A channel and component performance:	Certified channel performance in a 4-connector configuration up to 100 meters and exceeds the requirements of ANSI/TIA/EIA-568-B.2-1 Category 6 and ISO 11801 Class E Standards Certified component performance to the ANSI/TIA/EIA-568-B.2-1 Category 6 and ISO 11801 Class E standards
IEC compliance:	IEC 60603-7, IEC 60529 (IP 20)
FCC:	Meets ANSI/TIA-968-A; contacts are plated with 50 microinches of gold for superior performance
PoE:	Meets IEEE 802.3af and draft requirements of IEEE 802.3at for PoE Plus
UL compliance:	UL 1863
Cable diameter:	0.280 in. (7.1mm) nominal

KEY FEATURES AND BENEFITS

100% performance tested:	Confidence that each patch cord delivers specified performance
Color-specific keys with positive and negative keying features:	Mechanically and visually distinguish connections to prevent unintentional insertion into unlike keyed or non-keyed ports, all network design flexibility and versatility, and accommodate more discrete networks
Center de-embedded plug:	Performs in center of ANSI/TIA/EIA 568-B.2-1 component range ensuring interoperability and superior performance
Integral pair manager:	Optimizes performance, consistency, and reliability by reducing untwist at plug
Slender strain relief boot:	Provides easy access in high-density applications
Robust construction:	Rated to 2500 mating cycles

APPLICATIONS

The TX6 PLUS Keyed UTP Patch Cords are a component of the TX6 PLUS UTP Copper Cabling System. Keyed connectivity enables a level of visual and mechanical differentiation, and physical layer security that conventional cabling systems cannot provide. Key applications include:

- Ethernet 10BASE-T, 100BASE-T (Fast Ethernet), 1000BASE-T (Gigabit Ethernet), 10GBASE-T (limited distances as specified in the industry standards)
- 155 Mb/s ATM, 622 Mb/s ATM, 1.2 Gb/s ATM
- Token Ring 4/16
- Digital video and broadband/baseband analog video

TX6 10Gig Keyed UTP Patch Cords

Keyed A (black):	UTPKSP*BL
Keyed B (red):	UTPKSP*RD
Keyed	UTPKSP*GR
C (green): Keyed D (yellow):	UTPKSP*YL
Keyed E (orange):	UTPKSP*OR
Keyed F (blue):	UTPKSP*BU

Mini-Com® TX6 PLUS Keyed UTP Jack Modules

Keyed A (black):	CJK688TGBL
Keyed B (red):	CJK688TGRD
Keyed C (green):	CJK688TGGR
Keyed D (yellow):	CJK688TGYL
Keyed E (orange):	CJK688TGOR
Keyed F (blue):	CJK688TGBU

Tools and Accessories

Patch cord removal tool:	PCRT1
Flashlight kit:	KPCRT1-FL
Patch cord color band:	PCBAND^~Q

*Feet lengths: 3, 5, 7, 10 feet

**Meter lengths: 1, 2, 3, 5, 7, 10 meters

^Colors: BU (Blue), BL (Black), GR (Green), RD (Red), or YL (Yellow)

** Replace with BU (Blue)




TX6™ 10Gig™ Keyed UTP Patch Cords are pre-labeled with the **RapidID™** Network Mapping System to enable faster tracing, placing, and network documentation. Learn more: www.panduit.com/rapid-id



All Part Numbers Compliant with the U.S. Trade Agreements Act (TAA) for purchases shipped to the United States.

TX6™ 10Gig™ Keyed UTP Patch Cords

ENGINEERING DRAWING



WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

PANDUIT®

For more information
Visit us at www.panduit.com
Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

© 2023 Panduit Corp.
ALL RIGHTS RESERVED.
COSP160-WW-ENG
10/2023