

3933 US ROUTE 11, CORTLAND, NEW YORK 13045 Phone Number: 1-800-345-3851 Fax Number: 607-758-3648

REPORT OF TEST

Panduit Corporation 10500 West 167th Street Orland Park, IL 60467

The products described in this Report were tested for compliance to the standard(s) listed below. The products listed below are not part of an Intertek Verification Program and the results are provided to the client as a one time performance test.

Reference Intertek Report No.: 101075436CRT-001

Date: March 13, 2013

Test:

Electrical performance testing of telecommunication patch cords to the requirements of ANSI/TIA-568-C.2 and ISO/IEC 11801 for Category 6 patch cords.

Standards used:

ANSI/TIA-568-C.2-2009: Balanced Twisted-Pair Telecommunications Cabling and Components Standards, dated August 2009

ISO/IEC 11801 Amendment 2 Information Technology - Generic cabling for customer premises, Second edition dated April 2010

Sections used:

Section 6.9, Cords and Jumpers Transmission Performance (6.9.1 to 6.9.2) of ANSI/TIA-568-C.2

Section 13, Balanced Cords of ISO/IEC 11801

Sample description:

The client supplied five (5) samples of 1 meter length patch cords, identified as part number, UTP28SP1M and five (5) samples of 20 feet length patch cords, identified as part number, UTP28SP20. The samples were received on March 13, 2013 and were in good condition.

Conclusion:

The telecommunication patch cords, as previously described and supplied by the client, were tested in accordance with the standard referred to above, and did comply with the indicated applicable transmission requirements. The testing was performed at Intertek located in Cortland, New York.

Reviewed and approved by:

John Cash Technician Global Cabling Products Testing

sive follotter Antoine Pelletier

Antoine Pelletier Engineer Global Cabling Products Testing

This report is for the exclusive use of Intertek's Client and is provided pursuant to the agreement between Intertek and its Client. Intertek's responsibility and liability are limited to the terms and conditions of the agreement. Intertek assumes no liability to any party, other than to the Client in accordance with the agreement, for any loss, expense or damage occasioned by the use of this report. Only the Client is authorized to copy or distribute this report and then only in its entirety. Any use of the Intertek name or one of its marks for the sale or advertisement of the tested material, product or service must first be approved in writing by Intertek. The observations and test results in this report are relevant only to the sample tested. This report by itself does not imply that the material, product, or service is or has ever been under an Intertek certification program.