




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT * PART NO.	USE WITH ANY OF THESE CABLE TIE CROSS-SECTIONS	WEIGHT lbs/ 100 pcs. (g)	SCREW OR RIVET SIZE
LPMM-S2	MINIATURE INTERMEDIATE STANDARD	0.031 [14.1]	#2 (M2) SCREW OR 0.088 [2.2] DIA. RIVET
LPMM-S5		0.025 [11.4]	#5 (M3) SCREW



* NOTE:

- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.







SECTION A-A

LPMM-S2

LPMM-S5

02B	9/14/2023	RVU	JEFP	MSAD	B. REMOVED QTY. COLUMN. A. REMOVED PN SUFFIX, -C AND -M FROM TABLE.	GAECN06908
02A	6/14/2023	RVU	JEFP	MSAD	M. +/- .010 WAS +/- .005. SEE DIMENSIONAL TOLERANCES. L. REMOVED 0.054 [1.8], 0.075 [1.9] AND 0.270 [6.9]. K. CHANGED FROM 0.048 TO 0.050, SEE LPMM-S5. J. REMOVE +/- .003 FROM LPMM-S2'S SLOT DEPTH. H. REDUCED FROM 0.110 [2.8] TO 0.105 [2.7] TO MATCH TOLERANCES DWGS. G. REMOVED COUNTERSUNK HOLES REF. NOTES. F. ADDED -C, & -M TO PN. E. ADDED 'P' LOGO ON THIS MODEL. D. ADDED ALL DIM. REF. EXCEPT SLOT WIDTH, SLOT DEPTH AND HOLES. C. CHANGED PART LENGTH FROM .400 TO .384 TO MATCH PARTS BEING PRODUCED. B. ADDED QTY. 100 AND 1000 TO TABLE. A. REBUILD MODEL AND RECREATED.	GAECN05601

TITLE					
LOW PROFILE MOUNTS LPMM					
CUSTOMER DRAWING					
ITEM REVISION NAME					
G03597HS/02					
DATASET FILE NAME					
G03597HS_DC/02B GB0239CR CUST DWG					
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]					
.X ± - .XX ± .020 [.5]					
			MATERIAL:		
			NYLON 6/6		
THIRD ANGLE PROJECTION			DRAWING NUMBER:		
			GB0239CR		
DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
MJK	5/15/95	JHAC	NONE		A