

PXE™ Mobile Printers and Labels



PANDUIT™

EPSON

PORTABLE LABELING SOLUTION PARTNERS

Panduit has partnered with Epson to deliver a best-in-class labeling solution.

Advanced labeling and software capabilities from Panduit, trusted across industries for their reliability and innovation, combine seamlessly with Epson industry-leading print technology, known for efficiency, compact design, and precision. Together, they provide unmatched performance in labeling solutions.

Through this strategic partnership with Seiko Epson Corporation, Panduit PXE™ Mobile Label Printers offer exceptional print quality, speed, and an extensive selection of label types designed for demanding environments.

This guide will walk you through the various labeling options available with Panduit PXE Mobile Printers, helping you choose the right solution for your specific application. Whether you are in construction, industrial manufacturing, or network infrastructure, you'll find the ideal labels to enhance efficiency and organization.

 Learn more about PXE Mobile Label Printers, visit panduit.com/mobile-printers

Table of Contents

- PXE™ Mobile Printer Comparison.....3
- Die-Cut Self Laminating Label Cassettes4
- LabelCore™ Fiber Optic Cable Identification System.....5
- Turn-Tell® Label Cassettes.....5
- Continuous Self-Laminating Labels.....6
- Marker Plate Label Cassettes.....6
- Flag Label Cassettes7
- Non-Laminated Label Cassettes7
- General Component Label Cassettes8
- Continuous Terminal Block Label Cassettes.....8
- Die-Cut Heat Shrink Label Cassettes9
- Continuous Heat Shrink Labels 10
- Network Component Label Cassettes11
- Continuous Tape Cassettes 12-13
- PXE Printers..... 14
- PXE Printer Accessories..... 15

Panduit PXE™ Mobile Printer Solutions deliver high quality products that help you do your job smarter, faster, and easier.

These solutions combine Epson world-class printing technology with Panduit industry-leading performance and field-tested durability. This full line of Electrical and Network label printers provides the solution that's best for you, from on-site smaller jobs to on-demand high volume label printing projects.



For service and technical support, call **800-777-3300**.



Part Number	MP75	MP100	MP200	MP300	MP500	MP550
FEATURES						
Price	\$	\$\$	\$\$	\$\$\$	\$\$\$\$	\$\$\$\$
Automatic Cutter	-	✓	✓	✓	✓	✓
Half-Cut Feature						
Replaceable Cutters		-	-	-		
Rewinder Compatible						
PC Interface and Printing for Easy-Mark™ Software	-	✓	✓	✓	✓	✓
Wireless Print Capability/ Mobile App			-	-		
Maximum Continuous Label Media Width	0.75 in.	1.0 in.	1.0 in.	1.5 in.	2.0 in.	2.0 in.
Print Speed (inches per second)	0.25	0.6	1.2	1.4	2.0	2.0
Weight	0.9 lbs.	1.3 lbs.	2.4 lbs.	2.7 lbs.	6.4 lbs	7.1 lbs
Size	4.4 in. W x 2.8 in. H x 6.7 in. L	2.36 in. W x 5.9 in. H x 5.4 in. L	5.4 in. W x 3.5 in. H x 11.6 in. L	5.4 in. W x 3.8 in. H x 11.6 in. L	7.6 in. W x 5.7 in. H x 7.8 in. L	7.6 in. W x 6.3 in. H x 7.8 in. L
Print Resolution	180 dpi	180 dpi	180 dpi	360 dpi	300 dpi	300 dpi

LABEL TYPES						
Continuous Vinyl & Polyester Tapes	✓	✓	✓	✓	✓	✓
Continuous Heat Shrink Tubing						
Continuous Self-Laminating Labels	-			✓	✓	✓
Continuous Magnetic Tape						
Die-Cut Self-Laminating Labels						
Die-Cut Component Labels						
Turn-Tell™ Labels	-	-	-	-		
Die-Cut Heat Shrink & Raised Panel						
Bulk Label Material Compatible						

Die-Cut Self Laminating Label Cassettes

- Fast-loading Label Cassette includes both label material and ribbon to make changing labels easy
- Self-laminating adhesive labels for wire/cable identification include a white print-on area and clear overlamine
- Use in wrap format application. Not recommended for flag format applications



Self-Laminating Vinyl (VAM)



-40°F to 150°F (-40°C to 66°C)

Part Number	Printer Compatibility					Print-on Area Color	Width In. (mm)	Length In. (mm)	Print-on Area Height In. (mm)	Min. Cable O.D. In. (mm)	Max. Cable O.D. In. (mm)	Wire/Cable Size Range	Labels Per Cassette	Std. Pkg. Qty.	Std. Ctn. Qty.
	MP75	MP100	MP200	MP300	MP500/MP550										
S050X075VAM						Black on White	0.5 (12.7)	0.75 (19.1)	0.25 (6.4)	0.08 (2.0)	0.16 (4.0)	Cat. 6 28 AWG/ 18 – 14 AWG	425	1	5
S050X125VAM				✓	–			1.25 (31.8)	0.38 (9.7)	0.12 (3.1)	0.28 (7.0)	Cat. 3 UTP/ 12 – 10 AWG	200		
S050X150VAM								1.5 (38.1)	0.50 (12.7)	0.16 (4.0)	0.32 (8.1)	Cat. 5e UTP/ Cat. 6 UTP/ Cat. 6A UTP/ Cat. 5e FTP/ 10 – 6 AWG	175		
S050X150VAM2				–	✓										
S100X075VAM						Black on White	1.0 (25.4)	0.75 (19.1)	0.25 (6.4)	0.08 (2.0)	0.16 (4.0)	Cat. 6 28 AWG/ 18 – 14 AWG	300		
S100X125VAM				✓	–			1.25 (31.8)	0.38 (9.7)	0.12 (3.1)	0.28 (7.0)	Cat. 3 UTP/ 12 – 10 AWG	200		
S100X150VAM								1.5 (38.1)	0.50 (12.7)	0.16 (4.0)	0.32 (8.1)	Cat. 5e UTP/ Cat. 6 UTP/ Cat. 6A UTP/ Cat. 5e FTP/ 10 – 6 AWG	175		
S100X150VAM2	–	–	–	–	✓								180		
S100X150VAMB				–	✓								1000		
S100X225VAM							1.0 (25.4)	2.25 (57.2)	0.75 (19.1)	0.24 (6.1)	0.48 (12.2)	Cat. 6 FTP/ Cat. 6A UTP/ Cat. 6A FTP/ 8 – 4 AWG	125		
S100X400VAM				✓	–			4.0 (101.6)	1.0 (25.4)	0.32 (8.1)	0.95 (24.3)	2 – 1 AWG	70		
S100X650VAM								6.5 (165.1)	1.5 (38.1)	0.48 (12.2)	1.59 (40.4)	1/0-250 MCM	45		
S150X150VAM2						Black on White	1.5 (38.1)	1.5 (38.1)	0.50 (12.7)	0.16 (4.0)	0.32 (8.1)	Cat. 5e UTP/ Cat. 6 UTP/ Cat. 6A UTP/ Cat. 5e FTP/ 10 – 6 AWG	175		
S150X150VAMB				–	✓								950		


Representative offering only, visit panduit.com for complete listing of products

Like what you see
and want more?

Visit [panduit.com/
mobile-printers](https://panduit.com/mobile-printers) for the full
offering of Panduit products

LabelCore™ Fiber Optic Cable Identification System

- Provides a larger labeling surface on small fiber cables and allows legends to be clearly seen
- Sleeves are made of flexible PVC material
- Locate sleeve on straight section of cable at least 2 inches from fiber boot



Part Number	Color	Cable Type	Length In. (mm)	Compatible With	Std. Pkg. Qty.
NWSLC-2Y	Yellow	2mm simplex fiber cable	1.0 (25.4)	S100X150YAJ (Laser/Inkjet); S100X150VAM (MP300 Hand-held Printer); S100X150VA1Y or S100X150VATY (Thermal Transfer Printer)	100
NWSLC-2Y-AQ	Aqua				
NWSLC-3Y	Orange	3mm simplex fiber cable		S100X225YAJ (Laser/Inkjet); S100X225VAM (MP300 Hand-held Printer); S100X225VA1Y or S100X225VATY (Thermal Transfer Printer)	
NWSLC-7Y	White	3mm duplex fiber cable			

Turn-Tell® Label Cassettes

- Fast-loading Label Cassette includes both label material and ribbon to make changing labels easy
- Innovative label design allows labels to rotate for visibility from any angle, and for repositioning on the wire/cable to align legends and improve aesthetics
- Labels can be easily installed on existing terminated wires and assemblies without disconnecting the wires/cables



Polymer Film (V1M)




-40°F to 150°F (-40°C to 65.6°C)


Part Number	Printer Compatibility					Print-on Area Color	Width In. (mm)	Length In. (mm)	Print-on Area Height In. (mm)	Min. Cable O.D. In. (mm)	Max. Cable O.D. In. (mm)	Wire/Cable Size Range	Labels per Cassette	Std. Pkg. Qty.	Std. Ctn. Qty.
	MP75	MP100	MP200	MP300	MP500/ MP550										
R100X075V1M						Black on White	1.0 (25.4)	0.75 (19.1)	0.25 (6.4)	0.12 (3.1)	0.16 (4.1)	Cat. 6 28 AWG/ 18 – 14 AWG	175	1	5
R100X125V1M				✓	–			1.25 (31.8)	0.38 (9.7)	0.16 (4.1)	0.22 (5.6)	Cat. 3 UTP/ 12 – 10 AWG	125		
★ R100X150V1M								1.5 (38.1)	0.50 (12.7)	0.22 (5.6)	0.28 (7.1)	Cat. 5e UTP/ Cat. 6 UTP/ Cat. 6A UTP/ 10 – 6 AWG	100		
★ R100X150V1M2				–	✓								250		
R100X150V1M3	–	–	–	–	✓										
▶ R100X225V1M				✓	–			2.25 (57.2)	0.75 (19.1)	0.28 (7.1)	0.39 (9.9)	Cat. 6 FTP/ 6A FTP/ 8 – 4 AWG	75		
R150X150V1M2				–	✓		1.5 (38.1)	1.5 (38.1)	0.5 (12.7)	0.22 (5.6)	0.28 (7.1)	Cat. 5e UTP/ Cat. 6 UTP/ Cat. 6A UTP/ 10 – 6 AWG	100		


Representative offering only, visit panduit.com for complete listing of products

Continuous Self-Laminating Labels

- Fast-loading Label Cassette includes both label material and ribbon to make changing labels easy
- Self-laminating adhesive labels for wire/cable identification include a white print-on area and clear over-laminate
- Use in wrap format application. Not recommended for flag format applications



 Self-Laminating Vinyl (VAM)

 -40°F to 150°F (-40°C to 66°C)

Part Number	Printer Compatibility					Print-on Area Color	Width In. (mm)	Length ft. (m)	Print-on Area Width In. (mm)	Min. Cable O.D. In. (mm)	Max. Cable O.D. In. (mm)	Wire/Cable Size Range	Std. Pkg. Qty.	Std. Ctn. Qty.
	MP75	MP100	MP200	MP300	MP500/MP550									
S000X100VAM		✓	✓		✓	White	0.945 (24)	26.2 (8.0)	0.315 (8)	0.10 (2.5)	0.20 (5.1)	12 – 10 AWG	1	5
S000X150VAM	–	–	–	✓	✓		1.417 (36)		0.512 (13.0)	0.16 (4.0)	0.32 (8.1)	Cat. 5e/Cat. 6		


Representative offering only, visit panduit.com for complete listing of products

Marker Plate Label Cassettes

- Fast-loading PXE Label Cassette includes both label material and ribbon to make changing labels easy
- Non-adhesive and halogen free; used to identify wires, cables, equipment, and many other applications
- Designed for use on larger diameter wire/cables and may be applied after all terminations are complete
- Attachable in horizontal or vertical orientation
- Meets requirements for MIL-STD-202G, Method 215K, Soutlion A, C and D
- Meets the outgassing requirements of ASTM E-595 suitable for use in air handling spaces



 Polyester/Polyolefin (Y6M, Y7M)

 -40°F to 180°F (-40°C to 82°C)

Part Number	Printer Compatibility					Print-on Area Color	Width In. (mm)	Length In. (mm)	Print-on Area Width In. (mm)	Recommended Cable Tie		Labels Per Cassette	Std. Pkg. Qty.	Std. Ctn. Qty.
	MP75	MP100	MP200	MP300	MP500/MP550					Vertical	Horizontal			
M300X050Y6M				✓	–	Black on Yellow	3.00 (76.2)	0.50 (12.7)	1.80 (45.7)	Intermediate Cross Section Cable Ties	Intermediate Cross Section Cable Ties	65	1	5
M300X050Y7M						Black on White								
M300X100Y6M2	–	–	–		✓	Black on Yellow	3.00 (76.2)	1.0 (25.4)	1.80 (45.7)	Standard Cross Section Cables Ties	Standard Cross Section Cables Ties	60	1	5
M300X100Y7M2						Black on White								

Representative offering only, visit panduit.com for complete listing of products



For service and technical support,
call **800-777-3300**.

Flag Label Cassette


- Fast-loading PXE Label Cassette includes both label material and ribbon to make changing labels easy
- Provides larger label area for small cables
- Innovative design allows flag labels to be applied in either adhesive or non-adhesive orientations



Polyester (AJM)



-40°F to 302°F (-40°C to 150°C)



Part Number	Printer Compatibility					Ribbon & Material Color	Width In. (mm)	Length In. (mm)	Min. Cable O.D. In. (mm)	Max. Wire O.D. In. (mm)	Wire Range	Labels Per Cassette	Std. Pkg. Qty.	Std. Ctn. Qty.
	MP75	MP100	MP200	MP300	MP500/MP550									
F100X150AJM	–	–	–	✓	–	Black on White	1.00 (25.4)	1.5 (38.1)	0.12 (3.1)	0.2 (5.1)	12 – 10 AWG	150	1	5

Representative offering only, visit panduit.com for complete listing of products

Non-Laminated Label Cassettes

- Fast-loading Label Cassette includes both label material and ribbon to make changing labels easy
- Non-laminated adhesive labels for wire/cable identification



Nylon Cloth (C1M)



-65°F to 275°F (-54°C to 135°C)



DIE-CUT NYLON CLOTH LABELS

Part Number	Printer Compatibility					Print-on Area Color	Width In. (mm)	Length In. (mm)	Min. Cable O.D. In. (mm)	Max. Wire O.D. In. (mm)	Wire Range	Labels Per Cassette	Std. Pkg. Qty.	Std. Ctn. Qty.
	MP75	MP100	MP200	MP300	MP500/MP550									
N050X075C1M	–	–	–	✔	–	Black on White	0.50 (12.7)	0.75 (19.1)	0.12 (3.1)	0.16 (4.1)	12 – 10 AWG	275	1	5
N100X075C1M							1.00 (25.4)							
N100X125C1M							1.25 (31.8)	0.2 (5.1)	0.32 (8.1)	10 – 6 AWG	180			

CONTINUOUS NYLON CLOTH TAPE

Part Number	Printer Compatibility					Print-on Area Color	Height In. (mm)	Length ft. (m)	Std. Pkg. Qty.	Std. Ctn. Qty.
	MP75	MP100	MP200	MP300	MP500/MP550					
T050X000C1M-BK	✓	–	✓	✓	✓	Black on White	0.465 (11.82)	19 (6)	1	5
T075X000C1M-BK							0.702 (17.82)			
T100X000C1M-BK	–						0.938 (23.82)			

Representative offering only, visit panduit.com for complete listing of products

General Component Label Cassettes

- Fast-loading PXE Label Cassette includes both label material and ribbon to make changing labels easy
- Multi-purpose labels for identifying flat surfaces such as components, control panels, circuit boards, and general labeling
- Die-cut labels designed to provide maximum aesthetic quality and appearance



Polyester (YJM)



-40°F to 302°F (-40°C to 150°C)



Part Number	Printer Compatibility					Ribbon & Material Color	Width In. (mm)	Height In. (mm)	Labels Per Cassette	Std. Pkg. Qty.	Std. Ctn. Qty.
	MP75	MP100	MP200	MP300	MP500/MP550						
C100X050YJM	-	-	-	✓	-	Black on White	1.00 (25.4)	0.50 (12.7)	420	1	5
C200X100YJM											
C200X100YJM2											
C190X400YJM2											

Representative offering only, visit panduit.com for complete listing of products

Continuous Terminal Block Label Cassettes

- Fast-loading Label Cassette includes both label material and ribbon to make changing labels easy
- Print terminal block labels ranging in size from 0.24 inches to 0.38 inches



Polyolefin (FJM)



-40°F to 180°F (-40°C to 82°C)



Part Number	Printer Compatibility					Print-on Area Color	Height In. (mm)	Length ft. (m)	Std. Pkg. Qty.	Std. Ctn. Qty.
	MP75	MP100	MP200	MP300	MP500/MP550					
T024X000FJM-BK	✓	✓	✓	✓	✓	Black on White	0.229 (5.82)	23 (7)	1	5
T038X000FJM-BK							0.347 (8.82)			

Representative offering only, visit panduit.com for complete listing of products

For service and technical support,
call **800-777-3300**.

Die-Cut Heat Shrink Labels

- Fast-loading label cassette includes both label material and ribbon to make changing labels easy
- Meets SAE-AS5942, MIL-STD-883F Method 2015.13, Solutions A, B and D, and MIL-STD-202G Method 215K, Solutions A,C and D
- Meets UL224 VW-1 requirement for flammability
- Shrink ratio 3:1
- Non-adhesive flattened heat shrinkable polyolefin for wire/cable identification



Heat Shrinkable Polyolefin
3:1 Heat Shrink Ratio (H1M, H2M)



-67°F to 275°F (-55°C to 135°C)

Part Number	Shrink Ratio	Mill Spec	Printer Compatibility					Ribbon & Material Color	Width In. (mm)	Length In. (mm)	Min. Cable O.D. In. (mm)	Max. Cable O.D. In. (mm)	Wire/Cable Size Range	Labels per Cassette	Std. Pkg. Qty.	Std. Ctn. Qty.
			MP75	MP100	MP200	MP300	MP500/MP550									
H100X025H1M2	3:1	✓	-	-	-	-	✓	Black on White	0.26 (6.6)	1.0 (25.4)	0.043 (1.1)	0.134 (3.4)	24 - 16 AWG	100	1	5
H100X025H1M3									0.26 (6.6)		0.043 (1.1)	0.134 (3.4)	24 - 16 AWG	540		
H100X034H1M2									0.37 (9.3)		0.075 (1.9)	0.212 (5.4)	18 - 12 AWG	100		
H100X034H1M3									0.37 (9.3)		0.075 (1.9)	0.212 (5.4)	18 - 12 AWG	530		
H100X044H1M2									0.47 (11.8)		0.095 (2.4)	0.279 (7.1)	16 - 8 AWG	70		
H100X044H1M3									0.47 (11.8)		0.095 (2.4)	0.279 (7.1)	16 - 8 AWG	520		
H100X064H1M2									0.71 (18.0)		0.146 (3.7)	0.425 (10.8)	8-2 AWG	70		
H100X084H1M2									0.89 (22.5)		0.189 (4.8)	0.547 (13.9)	4-1 AWG	55		
H100X134H1M2									1.34 (34.0)		0.276 (7.0)	0.807 (20.5)	1-250 MCM AWG	25		





Like what you see
and want more?


Visit [panduit.com/
mobile-printers](https://panduit.com/mobile-printers) for the full
offering of Panduit products


Continuous Heat Shrink Labels

- Fast-loading Label Cassette includes both label material and ribbon to make changing labels easy
- Non-adhesive flattened heat shrinkable polyolefin for wire/cable identification

 Heat Shrinkable Polyolefin
3:1 Heat Shrink Ratio (H1M, H2M)

 -67°F to 275°F (-55°C to 135°C)

 Heat Shrinkable Polyolefin
2:1 Heat Shrink Ratio (HPM, HXM)

 -67°F to 257°F (-55°C to 125°C)



	Printer Compatibility										Min. Cable O.D. In. (mm)	Max. Cable O.D. In. (mm)	Wire/ Cable Size Range	Std. Pkg. Qty.	Std. Ctn. Qty.		
	Part Number	Shrink Ratio	Mill Spec	MP75	MP100	MP200	MP300	MP500/ MP550	Ribbon & Material Color	Width In. (mm)						Length ft. (m)	
★	H000X025H1M	3:1	✓	✓	✓	✓	✓	✓	Black on White	0.26 (6.6)	8.2 (2.5)	0.043 (1.1)	0.134 (3.4)	24 - 16 AWG	1	5	
	H000X025H1M3			—	—	—	—				49.0 (15.0)						
	H000X025H2M			✓	✓	✓	✓			Black on Yellow	0.27 (6.8)	8.2 (2.5)	0.055 (1.4)	0.15 (3.8)			22 - 18 AWG
★	H000X034H1M			Black on White	0.37 (9.3)	49.0 (15.0)	0.075 (1.9)		0.212 (5.4)	18 - 12 AWG							
	H000X034H1M3										—	—	—	—			
	H000X034H2M										✓	✓	✓	✓			
★	H000X044H1M			Black on Yellow	0.47 (11.8)	49.0 (15.0)	0.095 (2.4)		0.279 (7.1)	16 - 8 AWG							
	H000X044H1M3										—	—	—				
	H000X044H2M																
▶	H000X064HPM			2:1	—	—	✓		✓	✓		Black on White	0.71 (18)	8.2 (2.5)			0.221 (5.6)
	H000X064HXM	Black on Yellow															
▶	H000X084HPM	Black on White	0.89 (22.5)					0.315 (8)				0.539 (13.7)	4 - 1 AWG				
	H000X084HXM	Black on Yellow															
	H000X134HPM	Black on White	1.34 (34)					0.433 (11)				0.787 (20)	1 - 250 MCM AWG				
	H000X134HXM	Black on Yellow															

Representative offering only, visit panduit.com for complete listing of products





For service and technical support,
call **800-777-3300**.

Network Component Label Cassettes


- Fast-loading PXE Label Cassettes include both label material and ribbon to make changing labels easy
- Use for identifying patch panels, faceplates, punchdown blocks, and other network systems hardware
- Die-cut labels designed to provide maximum aesthetic quality and appearance



 Polyolefin (FJM)

 -40°F to 180°F (-40°C to 82°C)

 Non-Adhesive Polyester (Y1M)

 -10°F to 311°F (-23°C to 155°C)



POLYOLEFIN COMPONENT LABELS

Part Number	Printer Compatibility					Ribbon & Material Color	Width In. (mm)	Height In. (mm)	Application	Labels Per Cassette	Std. Pkg. Qty.	Std. Ctn. Qty.
	MP75	MP100	MP200	MP300	MP500/MP550							
C061X030FJM						Black on White	0.61 (15.5)	0.3 (7.6)	1-port	370	1	5
C125X030FJM	-	-	-	✓	-		1.25 (31.8)		2-port	210		
C252X030FJM							2.52 (64.0)		4-port	110		
C379X030FJM							3.79 (96.3)		6-port	60		

Representative offering only, visit panduit.com for complete listing of products

NON-ADHESIVE POLYESTER COMPONENT LABELS

Part Number	Printer Compatibility					Ribbon & Material Color	Width In. (mm)	Height In. (mm)	Application	Labels Per Cassette	Std. Pkg. Qty.	Std. Ctn. Qty.
	MP75	MP100	MP200	MP300	MP500/MP550							
C195X040Y1M	-	-	-	✓	-	Black on White	1.95 (49.5)	0.4 (10.2)	Single-gang faceplate	125	1	5
C261X035Y1M							2.61 (66.3)	0.35 (8.9)	4-port	100		

Representative offering only, visit panduit.com for complete listing of products



Like what you see
and want more?

Visit [panduit.com/
mobile-printers](https://panduit.com/mobile-printers) for the full
offering of Panduit products

Continuous Tape Cassettes

- Fast-loading Label Cassette includes both label material and ribbon to make changing labels easy
- Print custom pipe markers, voltage markers, signs, bin markers, and network ID labels on demand
- For flat label applications only



Vinyl Material (VXM & VPM)



-40°F to 194°F (-40°C to 90°C)



Polyester Material
(BPM, BQM, BSM, BUM, BWM, BXM, BYM, YKM)



-40°F to 257°F (-40°C to 125°C)



Magnetic Material (MPM & MXM)



14°F to 104°F (-10°C to 40°C)



Part Number	Printer Compatibility					Ribbon & Material Color	Material	Width In. (mm)	Length ft. (m)	Std. Pkg. Qty.	Std. Ctn. Qty.
	MP75	MP100	MP200	MP300	MP500/MP550						
T024X000BPM-BK							Polyester	0.229 (5.8)	30 (9.1)		
★ T038X000VPM-BK						Black on White	Vinyl		23 (7.0)		
T038X000BPM-BK							Polyester		30 (9.1)		
T038X000VXM-BK						Black on Yellow	Vinyl	0.354 (9.0)	23 (7.0)		
T038X000BXM-BK									30 (9.1)		
T038X000YKM-BK						Black on Clear	Polyester		30 (9.1)		
T038X000BYM-WH						White on Black					
★ T050X000VPM-BK						Black on White	Vinyl		23 (7.0)		
T050X000BPM-BK							Polyester		30 (9.1)		
T050X000VXM-BK	✓					Black on Yellow	Vinyl	0.472 (12.0)	23 (7.0)		
T050X000BXM-BK		✓	✓	✓					30 (9.1)		
T050X000YKM-BK						Black on Clear	Polyester		30 (9.1)		
T050X000BYM-WH					✓	White on Black				1	5
★ T075X000VPM-BK						Black on White	Vinyl		23 (7.0)		
T075X000BPM-BK							Polyester		30 (9.1)		
T075X000VXM-BK						Black on Yellow	Vinyl	0.710 (18.0)	23 (7.0)		
T075X000BXM-BK									30 (9.1)		
T075X000YKM-BK						Black on Clear	Polyester		30 (9.1)		
T075X000BYM-WH						White on Black					
T100X000MPM-BK						Black on White	Magnetic		4.9 (1.5)		
T100X000MXM-BK						Black on Yellow					
★ T100X000VPM-BK									23 (7.0)		
T100X000VPMB-BK		-	-	-		Black on White	Vinyl	0.945 (24.0)	147 (45)		
T100X000BPM-BK		✓	✓	✓			Polyester		30 (9.1)		
▶ T100X000VXM-BK						Black on Yellow	Vinyl		23 (7.0)		

continued on next page

Continuous Tape Cassettes (continued)

Part Number	Printer Compatibility					Ribbon & Material Color	Material	Width In. (mm)	Length ft. (m)	Std. Pkg. Qty.	Std. Ctn. Qty.	
	MP75	MP100	MP200	MP300	MP500/MP550							
T100X000VXMB-BK	-	-	-	-	-	Black on Yellow	Vinyl	0.945 (24.0)	147 (45)	1	5	
T100X000BXM-BK							Polyester		30 (9.1)			
T100X000YKM-BK							Black on Clear	Polyester	0.945 (24.0)			30 (9.1)
T100X000BQM-WH							White on Blue					
T100X000BSM-WH		✓	✓				White on Green					
T100X000BUM-BK							Black on Orange					
T100X000BWM-WH							White on Red					
T100X000BYM-WH							White on Black					
T150X000MPM-BK						✓	Black on White	Magnetic				4.9 (1.5)
T150X000MXM-BK												
T150X000VPM-BK								Black on White	Vinyl			23 (7.0)
T150X000BPM-BK									Polyester			30 (9.1)
T150X000VXM-BK							Black on Yellow	Vinyl	23 (7.0)			
T150X000BXM-BK								Polyester	1.471 (36.0)			30 (9.1)
T150X000YKM-BK							Black on Clear					
T150X000BQM-WH							White on Blue					
T150X000BSM-WH							White on Green					
T150X000BUM-BK		-	-				Black on Orange					
T150X000BWM-WH							White on Red					
T150X000BYM-WH							White on Black					
T200X000VPM2-BK					-		Black on White	Vinyl	1.97 (50)			23 (7)
T200X000VPMB-BK												
T200X000VXM2-BK							Black on Yellow					23 (7)
T200X000VXMB-BK												147 (45)
T200X000BUM2-BK							Black on Orange	Polyester				26 (8)
T200X000BWM2-WH							White on Red					
T200X000BYM2-WH						White on Black						

Representative offering only, visit panduit.com for complete listing of products

For service and technical support,
call **800-777-3300**.

PXE Printers



MP550



MP500



MP300



MP200



MP100



MP75

Part Number	Description	Included Power Cord Plug Type
MP550	Includes MP550 printer, one (1) cassette of T200X000VPM2-BK continuous vinyl tape, rechargeable Li-Ion battery pack, AC power adapter, USB cable, roll stand and quick reference card. For use in North America	Type A
MP500	Includes MP500 printer, one (1) cassette of T200X000VPM2-BK continuous vinyl tape, AC power adapter, USB cable, roll stand and quick reference card. For use in North America	
MP300	Includes MP300 printer, one (1) cassette of S100X150VAM self-laminating labels, rechargeable Li-Ion battery pack, hard carrying case, AC power adapter, USB cable, magnetic attachments and quick reference card. For use in North America	
MP300/E	Includes MP300 printer, one (1) cassette of S100X150VAM self-laminating labels, rechargeable Li-Ion battery pack, hard carrying case, power adapter (MP300-ACS), USB cable and magnetic attachments. For use outside of North America	Types A, C, G & I
MP200	Includes MP200 printer, one (1) T100X000VPM-BK continuous vinyl tape cassette, and quick reference card. For use globally	–
MP200-KIT	Includes MP200-KIT printer, one (1) T100X000VPM-BK continuous vinyl tape cassette, hard carrying case, rechargeable battery pack, magnetic feet, USB cable, and power adapter (MP-ACS-1). For use in North America	Type A
MP200/E-KIT	Includes MP200-KIT printer, one (1) T100X000VPM-BK continuous vinyl tape cassette, hard carrying case, rechargeable battery pack, magnetic feet, USB cable, and power adapter (MP-ACS-1). For use outside of North America	Types A, C, G & I
MP100	Includes MP100 printer, one (1) T100X000VPM-BK continuous vinyl tape cassette, USB cable, protective impact bumper, AC power adapter (MP-ACS-1) and power cord, and quick reference card. For use in North America	Type A
MP100/E	Includes MP100 printer, one (1) T100X000VPM-BK continuous vinyl tape cassette, USB cable, protective impact bumper, power adapter (MP-ACS-1), and quick reference card. For use outside of North America	Types A, C, G & I
MP75	Compact entry level industrial printer that features custom label modes, a qwerty keyboard, backlit LCD screen, and a large library of barcodes and custom symbols. Includes the lightweight printer, one T075X000VPM-BK continuous label cassette and quick reference card. For use globally	–



Like what you see
and want more?

Visit [panduit.com/
mobile-printers](https://panduit.com/mobile-printers) for the full
offering of Panduit products

PXE Printer Accessories



MP300-ACS



MP300-CASE



MP100-IB



MP-ACS-1



MP-REWINDER

Part Number	Description	Printer Compatibility				
		MP75	MP100	MP200	MP300	MP500/ MP550
MP-REWINDER*	PXE Printer Accessory, attachable rewriter for winding bulk label jobs. For use with MP500 & MP550 printers. Comes 1 per package					
MP-HALFCUT	PXE Printer Accessory, replacement half cutter blade - For use in MP500 & MP550 printers. Comes 1 per package			-	-	✓
MP-FULLCUT	PXE Printer Accessory, replacement full cutter blade - For use in MP500 & MP550 printers. Comes 1 per package					
MP-BATT	The MP-BATT Li-Ion Rechargeable Replacement Battery Pack is designed for use with the MP550, MP300 and MP200 mobile printers. The battery pack is RoHS Compliant. The battery is gray and comes 1 per package			✓	✓	✓ MP550 only
MP300-ACS	Replacement 120-240 VAC universal power adapter module with power cord for North America for MP300 printer (plug type A)			-	✓	
MP-ACS-1	The MP-ACS-1 120-240 VAC Universal Power Adapter is designed for use with the MP100 and MP200 mobile printers. The universal power adapter is RoHS Compliant. The adapter is black and comes 1 per package. For use in North America (plug type A)		✓	✓	-	-
MP-CASE	Replacement Hard Carrying Case designed for the MP200 and MP300 mobile printers. The case is RoHS Compliant. The case is 15.57 in. L x 11.74 in. W (395.4mm x 298.4mm). It is black and comes 1 per package		-	✓	✓	
MP100-IB	Replacement impact bumper for MP100 and MP100/E printers		✓	-	-	
PTR-CLN	Printer cleaning kit — contains (1) cleaning pen, (8) cleaning solution soaked wipes, (8) foam swabs pre-saturated with cleaning solution, MSDS, and cleaning instructions	✓	✓	✓	✓	✓

*MP-REWINDER is compatible with continuous MP bulk materials 3/8 inch (9mm) and wider



EMPLUS

Part Number	Description
EMPLUS-CD	Easy-Mark™ Labeling Software, CD-ROM
EMPLUS-DL	Easy-Mark Labeling Software, online download
EMPLUS-2GO	Easy-Mark Labeling Software, USB flash drive
EMPLUS-SERVER	Easy-Mark Labeling Software, networking server based version

Use Easy-Mark Plus Labeling Software with the MP100, MP200, MP300, MP500 & MP550 PXE printers as well with all standard laser, inkjet, dot matrix and Panduit desktop printers. Easy-Mark Labeling Software is sold separately, not included with PXE printers

Making the connections that matter.

We have the knowledge and experience to help you make the most of your infrastructure investment.

panduit.com/mobile-printers



Let's connect
panduit.com/contact-us

PANDUIT®
infrastructure for a connected world

