
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

DIMENSIONS - in [mm] WIRE **PANDUIT** SIZE .03 .01 .01 .03 PART # С± A \pm $B \pm$ D± AWG [0,8][0,3][0,8] [0,3]BSN22 26-22 .79 [20,1] .08 [2,0] .04 [1,0] .47 [11,9]

	INSTALLATION TOOLS							
CT-520								
	CT-1525 (A POCKET)							
	CT-2500 (CT-2525CH: A PKT)							



 ${\sf B}$

NOTES:

 B

- 1. RECOMMENDED FOR:
 - A. #26-22 AWG SOLID OR STRANDED COPPER WIRE
 - B. 221°F [105°C] MAX TEMP. RATING
 - C. 600V MAX VOLTAGE RATING
- 2. MATERIAL:
 - A. STAMPING: .02" [0,5] THK COPPER, TIN PLATED
 - B. HOUSING: NYLON, YELLOW
- 3. SEE www.panduit.com FOR PACKAGE QUANTITIES
- 4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
- 5. WIRE STRIP LENGTH: 1/4" + 1/32 = [6,4mm + 0.8]

							BUTT SPLICE, NYLON INSULATED #26-22 AWG
							CONTROL DRAWING
							N41337BA/08 DATASET FILE NAME
							N41337BA_DC/08 UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]
08	4-27-15	JHNU	TMR	RGB	ADDED A POCKET NOTE, MAX INSUL DIA AND 600V RATING	A 41337	.x ± .1 [2.54] .xxx ± .005 [.127] SEE NOTES
07	04-25-13		RTFI		UPDATED DRAWING BORDER & TITLE BLOCK	A41337	.xx : .01 [.25] ANGLES : 5 ° THIRD ANGLE PROJECTION A41337
REV	/ DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY DATE CHK SCALE DAW - NONE SHT 1 OF 1

TITLE

A100101010

2