Pre-Configured Micro Data Center (MDC)

specifications

The pre-configured micro data center (MDC) shall be factory assembled to include the connectivity and cable management necessary to enable rapid installation of switch, server, and storage devices. The cabinet configuration shall be 24 or 42 RU and shall allow for installation of standard 29 inch (737mm) depth equipment. All metal elements within the cabinet shall be single-point bonded to ensure effective equipment grounding. The system shall meet EIA-310-E, TIA/EIA-942 and UL2416. Each MDC shall be easily expandable by purchasing add-on kits. Option for dynamic rated MDC shall be available to support IT equipment under typical shipping conditions.

technical information

	42 RU MDC 27.6 in. (700mm) X	24 RU MDC 23.9 in. (606mm) X
Dimensions:	48.0 in. (1200mm) X 79.8 in. (2026mm)	42.0 in. (1066mm) X 48.4 in. (1230mm)
Material:	Steel with durable black polyester epoxy powder coat finish	
Compliance:	EIA-310-E, TIA/EIA-942, UL2416	
Static load rating:	2500 lbs.	2000 lbs.
Packaging:	Cabinet ships assembled, one per pallet; Optional ramp shipped in upright position attached to pallet	

key features and benefits

Pre-configured solution	Includes the cabinet, connectivity and cable management in one part number to simplify specification and ordering and enable fast, repeatable integration	
Reference architecture	Provides a physical map of the logical network layer and follows recommended installation practices, such as the Rockwell Automation* and Cisco** Converged Plantwide Ethernet (CPwE) architecture, to improve debug processes and increase system reliability and uptime	
Dynamic rated	Incorporates reinforced structure and shipped on shock-proof pallet with ramp to allow for safe transport of IT equipment under typical shipping conditions	
Expansion ready configuration	Includes space for future expansion of server, storage, and related patching elements to allow for increased network capacity without requiring addition to control room footprint	
Bonded structure	Incorporates single-point bonded cabinet, ground bar system and ESD port to help ensure network reliability and prevent equipment failure	
Integrated cable management with bend radius control	Maintains bandwidth through the network for increased uptime	

applications

The pre-configured MDC allows industrial system integrators to quickly and reliably deploy rack mount equipment while protecting the critical physical media that makes up the industrial network. The MDC is supplied in an assembled form, ready to accept the servers, switches and storage in its state-of-the-art cabinet housing.

The dynamic rated cabinet is designed to allow the equipment to be installed at one facility and be safely shipped to another location. This is ideal for system integrators or Value Added Resellers (VARs), as it allows the equipment to be pre-installed, cabled and ready for quick deployment. The heavy duty reinforced frame and shock pallet have been tested and approved to support the additional weight of equipment. An optional re-useable ramp allows the cabinet to be easily unloaded from the pallet.

The system is aligned with the CPwE architecture for manufacturing, including a demilitarized zone (DMZ) with firewall appliances and redundant compute and switching resources.

*Rockwell Automation is registered by Rockwell Automation in the Patent and Trademark Office of the United States. **Cisco is a registered trademark of Cisco Technology Inc.



	Pre-Configured Micro Data Cent	ters (MDC)	
	42 RU, dynamic rated MDC:	MDC79D	
	24 RU, dynamic rated MDC:	MDC48D	
	42 RU MDC:	MDC79	
	42 RU MDC Add	-On Kits	
	4 RU din-rail conversion kit:	IABDIN4	
	Grounding jumper kit:	RGEJ660PF	
	Fiber shelf:	FCE1UA + 3 FAPs	
	(LC connector):	FAP12WAQDLCZ	
	LC to LC patch cord:	FX2ERLNLNSNM002	
	Mini-Com® TX6™ Jack Module:	PLUS UTP CJ688TGBL-24	
	28 AWG Shielde Category 6A Patch Cord:	d STP28X**xx	
	Network security		
iber on	RJ45	uevices.	
d	Blockout, Red: RJ45	PSL-DCJB	
bug	<i>Lock-in, Red</i> : Other colors av	PSL-DCPLX ailable.	
amp	PDUs: Q1L2B3J2M24AFA0		
IS	(NEMA L6-30) Q1L2B1L2N24AFA0		
ng n to	(IE	EC-60309-6H 2P+E)	
	24 RU MDC Add	On Kits	
rt	4 RU din-rail conversion kit:	IABDIN4	
	Grounding jumper kit:	RGEJ660PF	
	Fiber shelf: (LC connector):	FCE1UA + 3 FAPs FAP12WAQDLCZ	
nd '	LC to LC patch cord:	FX2ERLNLNSNM001	
n nal	28 AWG Shielded Category 6A		
e e	Patch Cord:	STP28X**xx	
ed	Network security devices: RJ45		
	Blockout, Red: RJ45	PSL-DCJB	
	<i>Lock-in, Red:</i> Other colors av	PSL-DCPLX ailable.	
	PDU:	HB1B1L4BT10M1	


www.panduit.com/mdc

Pre-Configured Micro Data Center (MDC)

A micro data center or MDC is a versatile combination of hardware, software and cabling that serves as an end-to-end networking hub, sized to serve the demands of a manufacturing environment. Panduit's pre-configured MDCs are designed and validated to allow a physical layout that facilitates deployment of best-in-class logical network architectures.

79" Micro Data Center (Full Rack)


The 42 RU MDC is designed for active hardware enabling up to 200 devices within the manufacturing floor. It is designed to house switches, firewalls, storage, servers, and UPS equipment.



- 1 Delivered with casters installed and on shock-absorbing pallet with ramp for safe shipping and fast integration.
- 24-port patch panel CPPL24WBLY pre-installed to enable structured cabling.
- 3 Vertical cable managers are pre-installed to route and protect data cabling.
- Space included for a vertical power outlet unit with 10 receptacles (sold separately).
- 5 Includes fiber optic patching enclosure FCE1UA with space for 3 FAPs.
- 6 Blanking panels included to optimize air flow within micro data center.
- Delivered with box which includes all necessary patch cords, jacks, and other accessories needed to finish integration of popular micro data center configurations.

48" MDC (Half Rack)


The 24 RU MDC is designed for active hardware enabling 30-50 devices within the manufacturing floor. It is designed to house switches, firewalls, storage, servers, and UPS equipment.



- 1 Delivered with casters installed and on shock-absorbing pallet with ramp for safe shipping and fast integration.
- 2 24-port patch panel CPPL24WBLY pre-installed to enable structured cabling.
- 3 Multiple horizontal cable managers are pre-installed to route and protect data cabling.
- Space included for rack-mount power outlet units (sold separately).
- 5 Includes fiber optic patching enclosure FCE1UA with space for 3 FAPs.
- Blanking panels included to optimize air flow within micro data center.
- Delivered with box which includes all necessary patch cords, jacks, and other accessories needed to finish integration of popular micro data center configurations.

42 RU 79" MDC

24 RU 48" MDC



Dimensions are in inches. (Dimensions in parentheses are metric).

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575 PANDUIT JAPAN PA Tokyo, Japan Gu Phone: 81.3.6863.6000 Ph

PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty



Visit us at www.panduit.com/mdc iai@panduit.com ©2016 Panduit Corp. ALL RIGHTS RESERVED. RKSP166--SA-ENG Replaces RKSP99--WW-ENG 2016-08-1