


2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART No.	BUNDLE DIA.		A in. (mm)	B in. (mm)	C in. (mm)	D in. (mm)	E in. (mm)	F in. (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	TIP STYLE	WEIGHT lbs. (g) / 100 pcs
	MIN. in. (mm)	MAX. in. (mm)										
PLT1M-*360	.06 (1.6)	.87 (22)	.043 (1.1)	.089 (2.5)	.169 (4.3)	.154 (3.9)	.180 (4.6)	3.9 (99)	12 (53)	MINIATURE	CURVED	.07 (16)
PLT1.5I-*360	.06 (1.6)	1.38 (35)	.045 (1.1)	.142 (3.6)	.206 (5.2)	.180 (4.6)	.240 (6.1)	5.6 (142)	26 (116)	INTERMEDIATE	CURVED	.14 (64)
PLT2S-*360	.06 (1.6)	1.88 (47.8)	.052 (1.3)	.190 (4.8)	.262 (6.7)	.220 (5.6)	.316 (8.0)	7.4 (188)	35 (156)	STANDARD	CURVED	.29 (132)
PLT3S-*360	.06 (1.6)	3.00 (76)	.052 (1.3)	.190 (4.8)	.262 (6.7)	.220 (5.6)	.337 (8.6)	11.5 (292)	35 (156)	STANDARD	CURVED	.45 (204)
PLT4S-*360	.06 (1.6)	4.00 (102)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	14.5 (368)	35 (156)	STANDARD	CURVED	.56 (254)
PLT4H-*360/147	.188 (4.8)	4.11 (104.5)	.060 (1.5)	.300 (7.6)	.338 (8.6)	.290 (7.4)	.480 (12.2)	14.5 (368)	75 (334)	HEAVY	STRAIGHT	1.03 (468)
PLT4H-*360	.188 (4.8)	4.00 (102)	.075 (1.9)	.300 (7.6)	.338 (8.6)	.290 (7.4)	.480 (12.2)	14.5 (368)	75 (334)	HEAVY	STRAIGHT	1.28 (581)
PLT7LH-*360	.188 (4.8)	7.00 (178)	.075 (1.9)	.300 (7.6)	.350 (8.8)	.330 (8.4)	.480 (12.2)	24.7 (627)	75 (334)	LIGHT HEAVY	STRAIGHT	2.09 (950)

*NOTE: SEE panduit.com FOR NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL, PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE

TITLE									
POST INDUSTRIAL RECYCLED (PIR) CABLE TIES									
CUSTOMER DRAWING									
ITEM REVISION NAME									
01234NBB/00									
DATASET FILE NAME									
01234NBB_DC r00A								MATERIAL:	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)								RECYCLED NYLON 6.6	
.X ± _____ .XXX ± .020 (.51) .XX ± .02 (.51) ANGLES ± _____								DRAWING NUMBER:	
								01234NBB-DC	
DRAWN BY		DATE		CHK		SCALE		SIZE	
BWG		8-12-25		DAEI		NONE		A	
SHT 1 OF 1									

00A	8-12-25	BWG	DAEI	DJSL	DRAWING RELEASED.				013106/00
REV	DATE	BY	CHK	APR	DESCRIPTION				ECN

2

1

XNGLOBAL-ASIZE