




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT PART NUMBER	CABLE TIE		DIMENSIONS					MATERIAL	WEIGHT grams/100pcs
	MIN TENSILE	MAX BUNDLE	'A'	'B'	'C'	'D'	'E'		
PUM-049-2S-*360	35 lbs (156 N)	1.88" (48)	.65 (16.5)	.26 (6.6)	.54 (13.8)	.28 (7.2)	7.4 (188)	RECYCLED, HEAT STABILIZED, IMPACT MODIFIED, UV STABILIZED NYLON 6.6 BLACK	155

NOTES:

- **SEE panduit.com FOR NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL, PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE.
- (*) DIMENSIONAL VARIANCE IS POSSIBLE DUE TO MOLDING PROCESS RELATED SINK MARKS.
- APPLICATION SPECIFICATION:
HOLE DIAMETER: 4.6 - 4.9 mm
PANEL THICKNESS: 0.7 - 3.0 mm




SCALE .75



SCALE .75

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	8.12.25	BWG	DAEI	DJSL	DRAWING RELEASED	013106/00

TITLE					
POST INDUSTRIAL RECYCLED (PIR) CABLE TIE MOUNT					
CUSTOMER DRAWING					
ITEM REVISION NAME					
01234NBC/00					
DATASET FILE NAME			MATERIAL:		
01234NBC_DC/00					
UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE METRIC TOLERANCE: ±0.5MM			RECYCLED NYLON 6.6		
.X ± ____ .XXX ± .020 [.51] .XX ± .02 [.5] ANGLES ± ____					
			DRAWING NUMBER:		
THIRD ANGLE PROJECTION					
DRAWN BY		DATE	CHK	SCALE	SIZE
BWG		8.12.25	DAEI	1:1 UNLESS NOTED	SHT 1 OF 1
					A