

X-863 CMP 200

Safety Data Sheet

According to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012 and the Hazardous Products Regulations (HPR) WHMIS 2015

Date of issue: 08/12/2019

Revision date: 08/12/2019

Version: 2.0

SECTION 1: Identification

1.1. Identification

Product name : X-863

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of the substance/mixture : Corrosion inhibitor

1.3. Details of the supplier of the safety data sheet

Supplier

CONTINENTAL PRODUCTS, INC.
#6 Midwest Drive, P.O. Box 338
Pacific, MO 63069 USA
636-257-4449

1.4. Emergency telephone number

Emergency number : CHEMTREC: 800-424-9300

SECTION 2: Hazard identification

2.1. Classification of the substance or mixture

GHS classification

Not classified.

2.2. Label elements

GHS labelling

No labelling applicable

2.3. Other hazards

No additional information available

2.4. Unknown acute toxicity

Not applicable

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%
Silicon carbide	(CAS-No.) 409-21-2	45.00
Zinc oxide (ZnO)	(CAS-No.) 1314-13-2	1.20

SECTION 4: First aid measures

4.1. Description of first aid measures

- First-aid measures after inhalation : Not a normal route of exposure. If symptoms develop, remove to fresh air. Get medical attention if condition worsens.
- First-aid measures after skin contact : If skin irritation occurs: Wash skin with plenty of water. Obtain medical attention if irritation persists.
- First-aid measures after eye contact : IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. This compound contains abrasive particles. If eye irritation persists: Get medical advice/attention.
- First-aid measures after ingestion : Do not induce vomiting without medical advice. Never give anything by mouth to an unconscious person. Get medical advice/attention if you feel unwell.

4.2. Most important symptoms and effects, both acute and delayed

- Symptoms/effects after inhalation : Not a normal route of exposure.
- Symptoms/effects after skin contact : May cause skin irritation. Symptoms may include redness, drying, and cracking of the skin.
- Symptoms/effects after eye contact : May cause eye irritation. Symptoms may include discomfort or pain, excess blinking and tear production, with possible redness and swelling.
- Symptoms/effects after ingestion : May be harmful if swallowed. May cause gastrointestinal irritation, nausea, vomiting and diarrhea.

X-863

Safety Data Sheet

According to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012 and the Hazardous Products Regulations (HPR) WHMIS 2015

4.3. Indication of any immediate medical attention and special treatment needed

Symptoms may be delayed. In case of accident or if you feel unwell, seek medical advice immediately (show the label where possible).

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media : Dry chemical. Foam. Carbon dioxide.
Unsuitable extinguishing media : None known.

5.2. Special hazards arising from the substance or mixture

Fire hazard : Products of combustion may include, and are not limited to: oxides of carbon.
Reactivity : No dangerous reactions known under normal conditions of use.

5.3. Advice for firefighters

Protection during firefighting : Keep upwind of fire. Wear full fire fighting turn-out gear (full Bunker gear) and respiratory protection (SCBA).

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

General measures : Use personal protection recommended in Section 8. Isolate the hazard area and deny entry to unnecessary and unprotected personnel.

6.1.1. For non-emergency personnel

No additional information available

6.1.2. For emergency responders

No additional information available

6.2. Environmental precautions

Prevent entry to sewers and public waters.

6.3. Methods and material for containment and cleaning up

For containment : Absorb and/or contain spill with inert material (sand, vermiculite or other appropriate material), then place in suitable container. Do not flush into surface water or sewer system. Wear recommended personal protective equipment.
Methods for cleaning up : Sweep or shovel spills into appropriate container for disposal.

6.4. Reference to other sections

For further information refer to section 8: "Exposure controls/personal protection"

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling : Avoid contact with skin and eyes. Avoid breathing dust/fume/gas/mist/vapours/spray. Do not swallow. Handle and open container with care. When using do not eat, drink or smoke.
Hygiene measures : Wash contaminated clothing before reuse. Always wash hands after handling the product.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Keep out of the reach of children. Keep container tightly closed.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Silicon carbide (409-21-2)		
ACGIH	ACGIH TWA (mg/m ³)	10 mg/m ³ (nonfibrous, inhalable particulate matter, particulate matter containing no asbestos and <1% crystalline silica) 3 mg/m ³ (nonfibrous, respirable particulate matter, particulate matter containing no asbestos and <1% crystalline silica) 0.1 fibers/cm ³ (as determined by the membrane filter method at 400-450X magnification (4-mm objective), using phase-contrast illumination.-respirable fibers, including whiskers, length >5 µm, aspect ratio ≥3:1)
OSHA	OSHA PEL (TWA) (mg/m ³)	15 mg/m ³ (total dust) 5 mg/m ³ (respirable fraction)

X-863

Safety Data Sheet

According to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012 and the Hazardous Products Regulations (HPR) WHMIS 2015

Silicon carbide (409-21-2)		
NIOSH	NIOSH REL (TWA) (mg/m ³)	10 mg/m ³ (total dust) 5 mg/m ³ (respirable dust)
Zinc oxide (ZnO) (1314-13-2)		
ACGIH	ACGIH TWA (mg/m ³)	2 mg/m ³ (respirable particulate matter)
ACGIH	ACGIH STEL (mg/m ³)	10 mg/m ³ (respirable particulate matter)
OSHA	OSHA PEL (TWA) (mg/m ³)	5 mg/m ³ (fume) 15 mg/m ³ (total dust) 5 mg/m ³ (respirable fraction)
IDLH	US IDLH (mg/m ³)	500 mg/m ³
NIOSH	NIOSH REL (TWA) (mg/m ³)	5 mg/m ³ (dust and fume)
NIOSH	NIOSH REL (STEL) (mg/m ³)	10 mg/m ³ (fume)
NIOSH	NIOSH REL (ceiling) (mg/m ³)	15 mg/m ³ (dust)

8.2. Exposure controls

Appropriate engineering controls	: Ensure good ventilation of the work station.
Hand protection	: Wear suitable gloves.
Eye protection	: Safety glasses or goggles are recommended when using product.
Skin and body protection	: Wear suitable protective clothing.
Respiratory protection	: None necessary under normal conditions of use. Use only in well-ventilated areas. In case of insufficient ventilation, wear suitable respiratory equipment.
Environmental exposure controls	: Avoid release to the environment.
Other information	: Handle in accordance with good industrial hygiene and safety procedures. Do not eat, drink or smoke when using this product.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Solid
Appearance	: Paste / thick grease
Colour	: Grey
Odour	: No data available
Odour threshold	: No data available
pH	: No data available
Melting point	: No data available
Freezing point	: No data available
Boiling point	: No data available
Flash point	: > 260 °C (> 500 °F)
Relative evaporation rate (butylacetate=1)	: No data available
Flammability (solid, gas)	: Not flammable
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: No data available
Solubility	: No data available
Partition coefficient n-octanol/water	: No data available
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive limits	: No data available
Explosive properties	: No data available
Oxidising properties	: No data available

9.2. Other information

No additional information available

X-863

Safety Data Sheet

According to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012 and the Hazardous Products Regulations (HPR) WHMIS 2015

SECTION 10: Stability and reactivity

10.1. Reactivity

No dangerous reactions known under normal conditions of use.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

10.4. Conditions to avoid

Heat.

10.5. Incompatible materials

None known.

10.6. Hazardous decomposition products

May include, and are not limited to: oxides of carbon.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity (oral) : Not classified.
Acute toxicity (dermal) : Not classified.
Acute toxicity (inhalation) : Not classified.

Zinc oxide (ZnO) (1314-13-2)	
LD50 oral rat	> 5000 mg/kg
Skin corrosion/irritation	: Not classified.
Serious eye damage/irritation	: Not classified.
Respiratory or skin sensitisation	: Not classified.
Germ cell mutagenicity	: Not classified.
Carcinogenicity	: Not classified.

Silicon carbide (409-21-2)	
IARC group	2A - Probably carcinogenic to humans
In OSHA Hazard Communication Carcinogen list	Yes
Reproductive toxicity	: Not classified.
STOT-single exposure	: Not classified.
STOT-repeated exposure	: Not classified.
Aspiration hazard	: Not classified.
Symptoms/effects after inhalation	: Not a normal route of exposure.
Symptoms/effects after skin contact	: May cause skin irritation. Symptoms may include redness, drying, and cracking of the skin.
Symptoms/effects after eye contact	: May cause eye irritation. Symptoms may include discomfort or pain, excess blinking and tear production, with possible redness and swelling.
Symptoms/effects after ingestion	: May be harmful if swallowed. May cause gastrointestinal irritation, nausea, vomiting and diarrhea.

SECTION 12: Ecological information

12.1. Toxicity

Ecology - general : Very toxic to aquatic life with long lasting effects.

12.2. Persistence and degradability

X-863	
Persistence and degradability	Not established.

12.3. Bioaccumulative potential

X-863	
Bioaccumulative potential	Not established.

12.4. Mobility in soil

No additional information available

X-863

Safety Data Sheet

According to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012 and the Hazardous Products Regulations (HPR) WHMIS 2015

12.5. Other adverse effects

Effect on the global warming : No known effects from this product.
Other information : No other effects known.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product/Packaging disposal recommendations : Dispose in a safe manner in accordance with local/national regulations.

SECTION 14: Transport information

Department of Transportation (DOT) and Transportation of Dangerous Goods (TDG)

In accordance with DOT/TDG
Not regulated

SECTION 15: Regulatory information

15.1. Federal regulations

All components of this product are listed, or excluded from listing, on the United States Environmental Protection Agency Toxic Substances Control Act (TSCA) inventory.

All components of this product are listed, or excluded from listing, on the Canadian DSL (Domestic Substances List) and NDSL (Non-Domestic Substances List) inventories.

15.2. International regulations

No additional information available

15.3. US State regulations

California Proposition 65 - This product does not contain any substances known to the state of California to cause cancer, developmental and/or reproductive harm

SECTION 16: Other information

Revision date : 05/11/2017
Other information : None.
Prepared by : Nexreg Compliance Inc.
www.Nexreg.com



SDS HazCom 2012 - WHMIS 2015 (NexReg)

Disclaimer: We believe the statements, technical information and recommendations contained herein are reliable, but they are given without warranty or guarantee of any kind. The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. It is the user's responsibility to satisfy oneself as to the suitability and completeness of this information for the user's own particular use.